## **SIEMENS**

3RW5076-2TB15 **Data sheet** 



SIRIUS soft starter 200-600 V 470 A, 110-250 V AC Spring-loaded terminals Thermistor input

| product brand name  | SIRIUS  |
|---|---|
| product category  | Hybrid switching devices                              |
| product designation   | Soft starter  |
| product type designation  | 3RW50   |
| manufacturer's article number   |   |
| <ul> <li>of standard HMI module usable</li> </ul>   | 3RW5980-0HS01   |
| <ul> <li>of high feature HMI module usable</li> </ul>   | 3RW5980-0HF00   |
| <ul> <li>of communication module PROFINET standard usable</li> </ul>                              | 3RW5980-0CS00   |
| <ul> <li>of communication module PROFIBUS usable</li> </ul>                                       | 3RW5980-0CP00   |
| <ul> <li>of communication module Modbus TCP usable</li> </ul>                                     | 3RW5980-0CT00   |
| <ul> <li>of communication module Modbus RTU usable</li> </ul>                                     | 3RW5980-0CR00   |
| <ul> <li>of communication module Ethernet/IP</li> </ul>   | 3RW5980-0CE00   |
| <ul> <li>of circuit breaker usable at 400 V</li> </ul>  | 3VA2580-6HN32-0AA0; Type of assignment 1, Iq = 65 kA  |
| <ul> <li>of circuit breaker usable at 500 V</li> </ul>  | 3VA2580-6HN32-0AA0; Type of assignment 1, Iq = 65 kA  |
| <ul> <li>of the gG fuse usable up to 690 V</li> </ul>   | 2x3NA3365-6; Type of coordination 1, Iq = 65 kA       |
| <ul> <li>of full range R fuse link for semiconductor protection<br/>usable up to 690 V</li> </ul> | 3NE1 436-2; Type of coordination 2, Iq = 65 kA        |
| <ul> <li>of back-up R fuse link for semiconductor protection<br/>usable up to 690 V</li> </ul>    | 3NE3 340-8; Type of coordination 2, Iq = 65 kA        |
| <ul> <li>of line contactor usable up to 480 V</li> </ul>  | <u>3RT1076</u>  |
| <ul> <li>of line contactor usable up to 690 V</li> </ul>  | <u>3RT1076</u>  |
| General technical data  |   |
| starting voltage [%]  | 30 100 %  |
| stopping voltage [%]  | 50 %; non-adjustable                                  |
| start-up ramp time of soft starter  | 0 20 s  |
| ramp-down time of soft starter  | 0 20 s  |
| current limiting value [%] adjustable   | 130 700 %   |
| accuracy class according to IEC 61557-12  | 5 %   |
| certificate of suitability  |   |
| CE marking  | Yes   |
| <ul> <li>UL approval</li> </ul>   | Yes   |
| CSA approval  | Yes   |
| product component   |   |
| HMI-High Feature  | No  |
| <ul> <li>is supported HMI-Standard</li> </ul>   | Yes   |
| is supported HMI-High Feature   | Yes   |
| product feature integrated bypass contact system  | Yes   |
| number of controlled phases   | 2   |
| trip class  | CLASS 10A / 10E (preset) / 20E; acc. to IEC 60947-4-2 |

| buffering time in the event of power failure   |   |
|--|---|
| for main current circuit   | 100 ms  |
| for control circuit  | 100 ms  |
| insulation voltage rated value   | 600 V   |
| degree of pollution  | 3, acc. to IEC 60947-4-2  |
| impulse voltage rated value  | 6 kV  |
| blocking voltage of the thyristor maximum  | 1 600 V   |
| service factor   | 1   |
| surge voltage resistance rated value   | 6 kV  |
| maximum permissible voltage for safe isolation   |   |
| between main and auxiliary circuit   | 600 V   |
| shock resistance   | 15 g / 11 ms, from 12 g / 11 ms with potential contact lifting                                    |
| vibration resistance   | 15 mm to 6 Hz; 2g to 500 Hz   |
| utilization category according to IEC 60947-4-2  | AC-53a  |
| reference code according to IEC 81346-2  | Q   |
| Substance Prohibitance (Date)  | 09/23/2019  |
| product function   |   |
| • ramp-up (soft starting)  | Yes   |
| • ramp-down (soft stop)  | Yes   |
| Soft Torque  | Yes   |
| adjustable current limitation  | Yes   |
| pump ramp down   | Yes   |
| intrinsic device protection  | Yes   |
| <ul> <li>motor overload protection</li> </ul>  | Yes; Full motor protection (thermistor motor protection and electronic motor overload protection) |
| <ul> <li>evaluation of thermistor motor protection</li> </ul>                            | Yes; Type A PTC or Klixon / Thermoclick   |
| • auto-RESET   | Yes   |
| manual RESET   | Yes   |
| • remote reset   | Yes; By turning off the control supply voltage  |
| <ul> <li>communication function</li> </ul>   | Yes   |
| <ul> <li>operating measured value display</li> </ul>                                     | Yes; Only in conjunction with special accessories   |
| <ul><li>error logbook</li></ul>  | Yes; Only in conjunction with special accessories   |
| <ul> <li>via software parameterizable</li> </ul>   | No  |
| <ul> <li>via software configurable</li> </ul>  | Yes   |
| PROFlenergy  | Yes; in connection with the PROFINET Standard communication module                                |
| <ul><li>voltage ramp</li></ul>   | Yes   |
| • torque control   | No  |
| analog output  | No  |
| Power Electronics  |   |
| operational current  |   |
| • at 40 °C rated value   | 470 A   |
| • at 50 °C rated value   | 416 A   |
| at 60 °C rated value   | 380 A   |
| operating voltage  | 200 200 1/  |
| • rated value  | 200 600 V   |
| relative negative tolerance of the operating voltage                                     | -15 %   |
| relative positive tolerance of the operating voltage                                     | 10 %  |
| operating power for 3-phase motors  • at 230 V at 40 °C rated value                      | 132 MM  |
| at 400 V at 40 °C rated value     at 400 V at 40 °C rated value                          | 132 kW<br>250 kW  |
| <ul> <li>at 400 V at 40 °C rated value</li> <li>at 500 V at 40 °C rated value</li> </ul> | 250 KW<br>315 kW  |
| Operating frequency 1 rated value  | 50 Hz   |
| Operating frequency 2 rated value  | 60 Hz   |
| relative negative tolerance of the operating frequency                                   | -10 %   |
| relative negative tolerance of the operating frequency                                   | 10 %  |
| adjustable motor current   | 10 /0   |
| at rotary coding switch on switch position 1   | 200 A   |
| at rotary coding switch on switch position 2   | 218 A   |
| at rotary coding switch on switch position 3   | 236 A   |
| - acrossing owner on owner position o  |   |

| <ul> <li>at rotary coding switch on switch position 4</li> </ul>                 | 254 A  |
|--|--|
| <ul> <li>at rotary coding switch on switch position 5</li> </ul>                 | 272 A  |
| <ul> <li>at rotary coding switch on switch position 6</li> </ul>                 | 290 A  |
| <ul> <li>at rotary coding switch on switch position 7</li> </ul>                 | 308 A  |
| <ul> <li>at rotary coding switch on switch position 8</li> </ul>                 | 326 A  |
| at rotary coding switch on switch position 9                                     | 344 A  |
| at rotary coding switch on switch position 10                                    | 362 A  |
|  | 380 A  |
| at rotary coding switch on switch position 11                                    |  |
| at rotary coding switch on switch position 12                                    | 398 A  |
| <ul> <li>at rotary coding switch on switch position 13</li> </ul>                | 416 A  |
| <ul> <li>at rotary coding switch on switch position 14</li> </ul>                | 434 A  |
| <ul> <li>at rotary coding switch on switch position 15</li> </ul>                | 452 A  |
| <ul> <li>at rotary coding switch on switch position 16</li> </ul>                | 470 A  |
| • minimum  | 200 A  |
| minimum load [%]   | 15 %; Relative to smallest settable le   |
| power loss [W] for rated value of the current at AC                              |  |
| <ul> <li>at 40 °C after startup</li> </ul>                                       | 56 W   |
| <ul> <li>at 50 °C after startup</li> </ul>                                       | 44 W   |
| at 60 °C after startup   | 37 W   |
| power loss [W] at AC at current limitation 350 %                                 |  |
| at 40 °C during startup  | 5 344 W  |
| at 50 °C during startup  | 4 438 W  |
| at 60 °C during startup  | 3 876 W  |
| type of the motor protection   | Electronic, tripping in the event of thermal overload of the motor   |
| Control circuit/ Control   | Electronic, tripping in the event of thermal eventual of the motor   |
|  | AC   |
| type of voltage of the control supply voltage                                    | AC   |
| control supply voltage at AC   | 440 050 1/   |
| • at 50 Hz   | 110 250 V  |
| • at 60 Hz   | 110 250 V  |
| relative negative tolerance of the control supply voltage at AC at 50 Hz         | -15 %  |
| relative positive tolerance of the control supply voltage at AC at 50 Hz         | 10 %   |
| relative negative tolerance of the control supply voltage at AC at 60 Hz         | -15 %  |
| relative positive tolerance of the control supply voltage at AC at 60 Hz         | 10 %   |
| control supply voltage frequency   | 50 60 Hz   |
| relative negative tolerance of the control supply voltage frequency              | -10 %  |
| relative positive tolerance of the control supply voltage frequency              | 10 %   |
| control supply current in standby mode rated value                               | 30 mA  |
| holding current in bypass operation rated value                                  | 105 mA   |
| locked-rotor current at close of bypass contact maximum                          | 2.2 A  |
| inrush current peak at application of control supply voltage maximum             | 12.2 A   |
| duration of inrush current peak at application of control supply voltage         | 2.2 ms   |
| design of the overvoltage protection   | Varistor   |
| design of short-circuit protection for control circuit                           | 4 A gG fuse (Icu=1 kA), 6 A quick-acting fuse (Icu=1 kA), C1 miniature circuit breaker (Icu= 600 A), C6 miniature circuit breaker (Icu= 300 A); Is not part of scope of supply |
| Inputs/ Outputs  |  |
| number of digital inputs   | 1  |
| number of digital outputs  | 3  |
| • not parameterizable  | 2  |
| digital output version   | 2 normally-open contacts (NO) / 1 changeover contact (CO)  |
|  | 0  |
| number of analog outputs   | U  |
| switching capacity current of the relay outputs  • at AC-15 at 250 V rated value |  |
|  | 3 A  |

| estallation/ mounting/ dimensions   |  |
|---|--|
| stallation/ mounting/ dimensions  |  |
| mounting position   | with vertical mounting surface +/-90° rotatable, with vertical mounting surface +/- 22.5° tiltable to the front and back |
| fastening method  | screw fixing   |
| neight  | 230 mm   |
| vidth   | 160 mm   |
| depth   | 282 mm   |
|   | 202  |
| required spacing with side-by-side mounting  • forwards   | 40   |
|   | 10 mm  |
| backwards   | 0 mm   |
| • upwards   | 100 mm   |
| • downwards   | 75 mm  |
| at the side   | 5 mm   |
| weight without packaging  | 7.3 kg   |
| onnections/ Terminals   |  |
| ype of electrical connection  |  |
| for main current circuit  | busbar connection  |
| for control circuit   | spring-loaded terminals  |
| vidth of connection bar maximum   | 35 mm; with connection cover 3RT1966-4EA1 maximum length 45 mm   |
| vire length for thermistor connection   |  |
| • with conductor cross-section = 0.5 mm² maximum  | 50 m   |
| • with conductor cross-section = 1.5 mm² maximum  | 150 m  |
| • with conductor cross-section = 2.5 mm² maximum  | 250 m  |
| ype of connectable conductor cross-sections   |  |
| for main contacts for box terminal using the front clamping point solid   | 95 300 mm²   |
| <ul> <li>for main contacts for box terminal using the front<br/>clamping point finely stranded with core end<br/>processing</li> </ul>    | 70 240 mm²   |
| <ul> <li>for main contacts for box terminal using the front<br/>clamping point finely stranded without core end<br/>processing</li> </ul> | 70 240 mm²   |
| for main contacts for box terminal using the front clamping point stranded  | 95 300 mm²   |
| <ul> <li>at AWG cables for main contacts for box terminal<br/>using the front clamping point</li> </ul>                                   | 3/0 600 kcmil  |
| <ul> <li>for main contacts for box terminal using the back<br/>clamping point solid</li> </ul>  | 120 240 mm²  |
| <ul> <li>at AWG cables for main contacts for box terminal<br/>using the back clamping point</li> </ul>                                    | 250 500 kcmil  |
| <ul> <li>for main contacts for box terminal using both<br/>clamping points solid</li> </ul>   | min. 2x 70 mm², max. 2x 240 mm²  |
| <ul> <li>for main contacts for box terminal using both<br/>clamping points finely stranded with core end<br/>processing</li> </ul>        | min. 2x 50 mm², max. 2x 185 mm²  |
| <ul> <li>for main contacts for box terminal using both<br/>clamping points finely stranded without core end<br/>processing</li> </ul>     | min. 2x 50 mm², max. 2x 185 mm²  |
| <ul> <li>for main contacts for box terminal using both<br/>clamping points stranded</li> </ul>  | min. 2x 70 mm², max. 2x 240 mm²  |
| <ul> <li>for main contacts for box terminal using the back<br/>clamping point finely stranded with core end<br/>processing</li> </ul>     | 120 185 mm²  |
| <ul> <li>for main contacts for box terminal using the back<br/>clamping point finely stranded without core end<br/>processing</li> </ul>  | 120 185 mm²  |
| <ul> <li>for main contacts for box terminal using the back<br/>clamping point stranded</li> </ul>   | 120 240 mm²  |
| ype of connectable conductor cross-sections   |  |
| <ul> <li>at AWG cables for main current circuit solid</li> </ul>  | 2/0 500 kcmil  |
| for DIN cable lug for main contacts stranded  | 50 240 mm²   |
| for DIN cable lug for main contacts finely stranded   | 70 240 mm²   |
| type of connectable conductor cross-sections  |  |
| for control circuit solid   | 2x (0.25 1.5 mm²)  |

| e for control circuit finally stranded with core and                             | 2x (0.25 1.5 mm²)   |
|--|---|
| <ul> <li>for control circuit finely stranded with core end processing</li> </ul> | 2x (0.25 1.5 IIIIII )   |
| at AWG cables for control circuit solid  | 2x (24 16)  |
| <ul> <li>at AWG cables for control circuit finely stranded with</li> </ul>       | 2x (24 16)  |
| core end processing  |   |
| wire length  | 000   |
| between soft starter and motor maximum   | 800 m   |
| at the digital inputs at AC maximum  | 1 000 m   |
| tightening torque  • for main contacts with screw-type terminals                 | 14 24 N·m   |
| for auxiliary and control contacts with screw-type                               | 0.8 1.2 N·m   |
| terminals  | 0.0 1.2 IV III  |
| tightening torque [lbf·in]   |   |
| <ul> <li>for main contacts with screw-type terminals</li> </ul>                  | 124 210 lbf·in  |
| <ul> <li>for auxiliary and control contacts with screw-type</li> </ul>           | 7 10.3 lbf·in   |
| terminals  |   |
| Ambient conditions   | F 000 my develop on of 4000 my and Administration   |
| installation altitude at height above sea level maximum                          | 5 000 m; derating as of 1000 m, see Manual  |
| ambient temperature  | 25 ±60 °C: Please observe denoting at temperatures of 40 °C an  |
| during operation   | -25 +60 °C; Please observe derating at temperatures of 40 °C or above   |
| during storage and transport   | -40 +80 °C  |
| environmental category   |   |
| <ul> <li>during operation according to IEC 60721</li> </ul>                      | 3K6 (no ice formation, only occasional condensation), 3C3 (no salt mist), 3S2 (sand must not get into the devices), 3M6 |
| <ul> <li>during storage according to IEC 60721</li> </ul>                        | 1K6 (only occasional condensation), 1C2 (no salt mist), 1S2 (sand must  |
|  | not get inside the devices), 1M4  |
| during transport according to IEC 60721  | 2K2, 2C1, 2S1, 2M2 (max. fall height 0.3 m)   |
| EMC emitted interference   | acc. to IEC 60947-4-2: Class A  |
| Communication/ Protocol  |   |
| communication module is supported  | V   |
| PROFINET standard     FthereNet/IP   | Yes   |
| EtherNet/IP     Modbus RTU   | Yes<br>Yes  |
| Modbus TCP   | Yes   |
| PROFIBUS   | Yes   |
| UL/CSA ratings   |   |
| manufacturer's article number  |   |
| • of the fuse  |   |
| <ul> <li>usable for Standard Faults up to 575/600 V according to UL</li> </ul>   | Type: Class L, max. 1600 A; Iq = 30 kA  |
| <ul> <li>usable for High Faults up to 575/600 V according to UL</li> </ul>       | Type: Class L, max. 1200 A; lq = 100 kA   |
| operating power [hp] for 3-phase motors  |   |
| • at 200/208 V at 50 °C rated value  | 150 hp  |
| • at 220/230 V at 50 °C rated value  | 150 hp  |
| • at 460/480 V at 50 °C rated value  | 350 hp  |
| at 575/600 V at 50 °C rated value  | 450 hp  |
| Safety related data  | IDOO IDOO III   |
| protection class IP on the front according to IEC 60529                          | IP00; IP20 with cover   |
| touch protection on the front according to IEC 60529                             | finger-safe, for vertical contact from the front with cover   |
| ATEX   |   |
| certificate of suitability   | V   |
| • ATEX   | Yes   |
| IECEX     hardware fault telegrapse according to IEC 61508                       | Yes   |
| hardware fault tolerance according to IEC 61508 relating to ATEX                 | 0   |
| PFDavg with low demand rate according to IEC 61508 relating to ATEX              | 0.09  |
| PFHD with high demand rate according to EN 62061 relating to ATEX                | 9E-6 1/h  |

| Safety Integrity Level (SIL) according to IEC 61508 relating to ATEX                     | SIL1 |
|--|------|
| T1 value for proof test interval or service life according to IEC 61508 relating to ATEX | 3 y  |
|  |      |

Certificates/ approvals

**General Product Approval** 

For use in hazardous locations





Confirmation







For use in hazardous locations Declaration of Conformity

**Test Certificates** 

Marine / Shipping





Type Test Certificates/Test Report







other

Confirmation

## **Further information**

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RW5076-2TB15

Cax online generator

http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RW5076-2TB15

Service&Support (Manuals, Certificates, Characteristics, FAQs,...) <a href="https://support.industry.siemens.com/cs/ww/en/ps/3RW5076-2TB15">https://support.industry.siemens.com/cs/ww/en/ps/3RW5076-2TB15</a>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax\_de.aspx?mlfb=3RW5076-2TB15&lang=en

Characteristic: Tripping characteristics, I2t, Let-through current

https://support.industry.siemens.com/cs/ww/en/ps/3RW5076-2TB15/char

Characteristic: Installation altitude

http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3RW5076-2TB15&objecttype=14&gridview=view1

Simulation Tool for Soft Starters (STS)

https://support.industry.siemens.com/cs/ww/en/view/101494917

last modified: 4/11/2022 🖸