


| REVISIONS | | | | | | |
|-----------|-----|-----|----------------|-------------|-------|-------|
| | REV | ECO | DESCRIPTION | DATE | BY | APPR |
| | A1 | | FIRST RELEASED | Jun-15-2018 | Blink | Tommy |







PURCHASED SEPARATELY

NOTES: (UNLESS OTHERWISE SPECIFIED)

1. MATERIAL:


SHELL: THERMOPLASTIC, UL94 V-0. INSERT: THERMOPLASTIC, UL94 V-0. O-RING: NBR OR SILICONE RUBBER. SEAL GASKET: NBR OR SILICONE RUBBER. END CAP: THERMOPLASTIC, UL94 V-0. PLASTIC RING:THERMOPLASTIC, UL94 V-0.

WIRE SEAL: SILICONE RUBBER.

- 2. SPECIFICATIONS:
 - 2.1 RATED CURRENT: 23A (MAX).
 - 2.2 RATED VOLTAGE: 500V(AC/DC).
 - 2.3, OPERATING TEMPERATURE: SEE TABLE.
 - 2.4, DIELECTRIC WITHSTANDING VOLTAGE: LESS THAN 2 MILLIAMPS CURRENT LEAKAGE@2000 VOLTS AC.
 - 2.5, INSULATION RESISTANCE: 5000 MEGOHMS MIN.
 - 2.6, IP-CLASS: IP67 AND IP69K IN THE MATED CONDITION,

WIRE SEALS FULLY POPULATED.

- 2.7, MATING CYCLES DURABILITY: 500 CYCLES MIN.
- 2.8, RoHS COMPLIANT.
- 3. SUITABLE CONTACTS: 2.5mm CONTACT.
- 4. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.



| PANFI | CUT | OUT F | RFFFR | PENCE |
|-------|-----|-------|-------|-------|

| | KFY | PART NUMBER | |
|-----|-----|---------------|----------------|
| KET | | -40°C ~ 105°C | -40°C ~ 125°C |
| | N | RTS714N4PHEC | RTS714N4PHEC03 |

| QUANTITY | PART N | NUMBER | | | DE | SCRIPTION | | ITEM |
|--|---------------------------------------|--|--|------------|-------------|---|------------|--------|
| | MATERI | | | | | ST | | |
| UNLESS OTHERWISE SPECIFIED | | SIGNATUR | ES I | Amphenol | | | | |
| 1) All dimensions a 2) Tolerances are a 1 PL DEC +0.30 | | DRAWN: Blink | Ju | un-15-2018 | | пірпе | | |
| 2 PL DEC ±0.15 3 PL DEC ±0.08 | Angles ±1° | CHECKED: Tod | Ju | un-15-2018 | | e Systems - www.a | mphenol-si | ne.com |
| 3) Note reference = X MATERIAL SPECIFICATIONS: | | ENGINEER: | | | | 24 Morley Drive ton Township, MI 48036 | | |
| | | APPROVAL: Tommy | Ju | un-15-2018 | | 1, | | |
| | WATERIAL OF EOI TOATIONO. | | | | | IATE, RECEPTACL | , | 4P, |
| | | THIS DRAWING IS SUPPINFORMATION ONLY. DE | | | JU | M NUT, SIZE 14, 4 | POS, PIN | |
| PROCESS SPECIFICATIONS: SPECIFICATIONS AND PERFORM SHOWN HEREON ARE THE PRO THE AMPHENOL CORPORATION OF REPRODUCTION ARE IMPLIE DIMENSIONS ARE SUBJECT TO | | ERFORMA HE PROPE PRATION. N E IMPLIED. ECT TO NO | ANCE DATA ERTY OF NO RIGHTS ALL | B C- | RTS714*4P | HECxx | A1 | |
| NEXT MOSTY: | NEXT ASS'Y: MANUFACTURING VARIATIONS. | | ATIONS. | | SCALE: NONE | | SHEET 1 | of 1 |

ecomate® RM/RSSM/Aquarius™ - Contact Size 12 Options

| Crimp Contacts, Machined | | | | | |
|--------------------------|--|-----|------------------|----------|--|
| Part Number Male Female | | | M/2 D (2) | Dietie e | |
| | | AWG | Wire Range (mm²) | Plating | |
| N/A | | | | | |

| | Tooling, Machined | | |
|-------------|-------------------|--|--|
| Part Number | Description | | |
| N/A | N/A | | |
| N/A | N/A | | |

| Plating Options, All | | |
|----------------------|---------|--|
| Symbol | Plating | |
| N/A | N/A | |

| Crimp Contacts, Stamped & Formed | | | | | |
|----------------------------------|---------|-------|------------|----------|--|
| Part Number | | AWG | Wire Range | Plating | |
| Male | Female | | (mm²) | r idinig | |
| SP12A1T | SS12A1T | 14-12 | 2.5-3.5 | Tin | |

| | Tooling, Stamped & Formed Part Number Description | | | |
|-------------|---|--|--|--|
| Part Number | | | | |
| QXRT12S | Contact Extraction Tool, 2.5mm Contact | | | |
| MFX-3962 | MFX-3962 Hand Tool, Stamped & Formed Contact, 2.5mm Contact | | | |

| | Misc Tooling, All | | |
|-------------|-------------------------|--|--|
| Part Number | Part Number Description | | |
| CA-4012-59 | ealing Plug, Size 12 | | |

| Standard Quantity Order Options | | |
|---------------------------------|-------------------|--|
| Machined | Stamped & Formed | |
| N/A | Reel, 1000 Pieces | |