

23 mm Miniature Speaker - 8 Ohm Part No: SPKM.23.8.A

Description:

23mm Miniature Speaker - 8 Ohm 500mW RMS Compact design for integration in a wide range of products

Features:

8 Ohm Impedance Rated Input Power 800mW RMS Max Input Power 1W peak High Sensitivity Dimensions: Ø23 x 6 mm Connector: Wire Lead RoHS & Reach Compliant

www.taoglas.com



	Changelog	10
6.	Packaging	9
5.	Mechanical Drawing	8
4.	Speaker Characteristics	7
3.	Speaker Measurement Conditions	6
2.	Specifications	4
1.	Introduction	3

Taoglas makes no warranties based on the accuracy or completeness of the contents of this document and reserver make changes to specifications and product descriptions at any time without notice. Taoglas reserves all rights to this uccurrent and the information contained herein. Reproduction, use or disclosure to third parties without express permission is strictly prohibited.

Copyright © Taoglas Ltd.





1. Introduction

Featuring a compact design, enabling ease of integration in a wide range of electronics products, including IoT devices, with high levels of long-term reliability and best in class performance Taoglas products are known for.

Our 23 mm Miniature Speaker offers a frequency response of 100 Hz - 10 kHz and high sensitivity, with 8 Ohm impedance and power handling of 0.5W RMS and 1W peak. Proven performance in demanding applications where the accurate reproduction of voice communications is required. Taoglas added miniature speakers to our product portfolio to provide both reliable connectivity and high-quality audio solutions from one trusted company.

Please contact your regional Taoglas customer support team for more information or installation guidelines.

The table below shows a guide to help select the best speaker for your application based on size requirements:

Part Number	Dimensions
SPKM.10.8.A	Ø10 x 3.5 mm
SPKM.15.8.A	Ø15 x 3.7 mm
SPKM.17.8.A	Ø17 x 4.4 mm
SPKM.20.8.A	Ø20 x 4.3 mm
SPKM.23.8.A	Ø23 x 6 mm
SPKM.28.8.A	Ø28 x 5.1 mm
SPKM.2030.8.A	30 x 20 x 5.1 mm
SPKM.2413.8.A	24 x 13 x 8.7 mm
SPKM.289.8.A	28 x 9 x 3.8 mm
SPKM.50.8.A	Ø50 x 8.3 mm



Specifications

Electroacoustic			
Sound Pressure Level	86 dB SPL (±3Db) @1000Hz (0 dB SPL = 20 μ Pa) Measuring Condition: 0.5W (Sine wave) @ 0.1 m measured with baffle		
Impedance	8Ω (±15%) @ 2 kHz with 1 V input signal and without baffle in place		
Frequency Response	100 Hz - 10KHz		
Resonant Frequency	1000 Hz (±20%) Typical frequency @ 1 V		
Nominal Input Power	500 milliwatts		
Maximum Input Power	1 Watt		
Distortion	Less than 10% @ 1 kHz , with input levels up to 2 V RMS		
Mechanical			
Height	6 mm		
Diameter	23 mm		
Weight	0.007 Kg		
Connector	Wire leads - AWG#32 (UL1571)		
Material	PEI diaphragm with Neodymium Magnet, (without enclosure)		
	Environmental		
Temperature Range	-40°C to 80°C		
Humidity	Non-condensing up to 95% Relative Humidity @ up to 65°C		



Reliability Testing			
High Temperature Test	High Temp	+80°C (±2°C)	
night remperature rest	Duration	96 Hours	
Low Temperature Test	Low Temp	-40°C (±2°C)	
Low remperature rest	Duration	96 Hours	
	High Temp	+75°C (±2°C)	
	Low Temp	-40°C (±2°C)	
Heat Shock Test	Changeover time	<30 Seconds	
	Duration	1 hour	
	Cycle	100 cycles	
	Temp	+40°C (±2°C)	
Humidity Test	Relative humidity	90 ~ 95%	
	Duration	96 Hours	
	Тетр	-40°C to +75°C	
Temperature Cycle Test	Duration	45 minutes	
remperature cycle rest	Temperature gradient	1°C to 3°C / minute	
	Cycle	25 cycles	
	Mounted with dummy set mass	10 g	
Drop Test	Height	1 m	
	Cycle	6 cycles	
Load Test	White noise (EIA filter) for 96 h	ours @ 0.5 W (2 V) input power	
	White noise (EIA filter) for 1 minute @ 0.8 W (2.5 V) input power		

* SPL (Sound Pressure Level) as specified did not deviate more than ±3 dB from initial value, with no significant damage after testing.








Standard Test Fixture Conditions			
Input Power	0.5 Watts (2 V)		
Mode	TSR		
Potentiometer Range	50 dB		
Sweep Time	0.5 seconds		


3.2 Measurement Fixture Diagram








Speaker Characteristics








	Name	Material	Finish	QTY
1	ø23mm Frame	Fe	Zinc Plated-Blue White	1
2	8Ω Voice coil	Cu	Natural	1
3	ø9.5x1.3mm Magnet	Nd-Fe-B	Zinc Plated	1
4	50 μ Diaphragm	PET	Natural	1
5	Gasket	T=1mm(Fe)	Zinc Plated—Blue White	1
6	UL1571 32AWG Lead wire	PVC	Black	1
7	UL1571 32AWG Lead wire	PVC	Red	1





6. Packaging


1 pcs SPKM.23.8.A per Blister Dimensions – 95 x 42 x 14mm





200 pcs SPKM.23.8.A per EPE Tray 6 Trays SPKM.23.8.A per Carton 7 pcs SPKM.23.8.A per Layer Board

1200 pcs SPKM.23.8.A per Carton Dimensions – 560 x 450 x 330mm





Changelog for the datasheet

SPE-22-8-007 – SPKM.23.8.A

Date:	18-11-2022
Changes:	Mechanical Drawings Updated to Rev D02
Changes Made by:	Carlos Gomes

Previous Revisions

Revision: A		Revision: I	3	
Date:	18-02-2022		Date:	17-05-2022
Changes:			Changes:	Sound Pressure Level Updated
Changes Made by:	Jack Conroy	Changes	Made by:	Paul Doyle

Revision: C		
Date:	12-08-2022	
Changes:	Cover updated Introduction updated Specifications updated Reliability test updated Seesker measurement conditions updated	
Changes Made by:	Carlos Gomes	



www.taoglas.com