## SIEMENS

## Data sheet

## US2:17GUG92WH15



Non-reversing motor starter, Size 2 1/2, Three phase full voltage, Solidstate overload relay, OLR amp range 25-100A, Combination type, 100A fusible disconnect, 100A/600V fuse clip, Encl NEMA type 4X 304 S-Steel, Water/dust tight noncorrosive, Standard width enclosure

-	-			11
-	au	res	sim	ilar
	-			

product brand name	Class 17	
design of the product	Non-reversing motor starter with fusible disconnect	
special product feature	ESP200 overload relay; Half-size controller	
General technical data		
weight [lb]	49 lb	
Height x Width x Depth [in]	24 × 20 × 8 in	
touch protection against electrical shock	NA for enclosed products	
installation altitude [ft] at height above sea level maximum	6560 ft	
ambient temperature [°F]		
<ul> <li>during storage</li> </ul>	-22 +149 °F	
during operation	-4 +104 °F	
ambient temperature		
<ul> <li>during storage</li> </ul>	-30 +65 °C	
<ul> <li>during operation</li> </ul>	-20 +40 °C	
country of origin	USA	
Horsepower ratings		
yielded mechanical performance [hp] for 3-phase AC motor		
• at 200/208 V rated value	0 hp	
• at 220/230 V rated value	0 hp	
• at 460/480 V rated value	30 hp	
• at 575/600 V rated value	0 hp	
Contactor		
size of contactor	Controller half size 2 1/2	
number of NO contacts for main contacts	3	
operating voltage for main current circuit at AC at 60 Hz maximum	600 V	
operational current at AC at 600 V rated value	60 A	
mechanical service life (switching cycles) of the main contacts typical	1000000	
Auxiliary contact		
number of NC contacts at contactor for auxiliary contacts	0	
number of NO contacts at contactor for auxiliary contacts	1	
number of total auxiliary contacts maximum	7	
contact rating of auxiliary contacts of contactor according to UL	10A@600VAC (A600), 5A@600VDC (P600)	
Coil		
type of voltage of the control supply voltage	AC	
control supply voltage		

<ul> <li>at AC at 50 Hz rated value</li> <li>at AC at 60 Hz rated value</li> </ul>	380 440 V 440 480 V	
	440 480 V	
holding power at AC minimum	8.6 W	
apparent pick-up power of magnet coil at AC	218 VA	
apparent holding power of magnet coil at AC	25 VA	
operating range factor control supply voltage rated value of magnet coil	0.85 1.1	
percental drop-out voltage of magnet coil related to the input voltage	50 %	
ON-delay time	19 29 ms	
OFF-delay time	10 24 ms	
Overload relay		
product function		
<ul> <li>overload protection</li> </ul>	Yes	
<ul> <li>phase failure detection</li> </ul>	Yes	
<ul> <li>asymmetry detection</li> </ul>	Yes	
<ul> <li>ground fault detection</li> </ul>	Yes	
test function	Yes	
external reset	Yes	
reset function	Manual, automatic and remote	
trip class	CLASS 5 / 10 / 20 (factory set) / 30	
adjustable current response value current of the current- dependent overload release	25 100 A	
tripping time at phase-loss maximum	3 s	
relative repeat accuracy	1 %	
product feature protective coating on printed-circuit board	Yes	
number of NC contacts of auxiliary contacts of overload relay	1	
number of NO contacts of auxiliary contacts of overload relay	1	
operational current of auxiliary contacts of overload relay		
• at AC at 600 V	5 A	
• at DC at 250 V	1 A	
contact rating of auxiliary contacts of overload relay according to UL	5A@600VAC (B600), 1A@250VDC (R300)	
insulation voltage (Ui)		
<ul> <li>with single-phase operation at AC rated value</li> </ul>	600 V	
<ul> <li>with multi-phase operation at AC rated value</li> </ul>	300 V	
Disconnect Switch		
response value of switch disconnector	100A / 600V	
design of fuse holder	Class R fuse clips	
operating class of the fuse link	Class R	
Enclosure		
	AV 204 steipless steel	
degree of protection NEMA rating	4X, 304 stainless steel	
design of the housing	dustproof, waterproof & resistant to corrosion	
Mounting/wiring		
mounting position	vertical	
fastening method	Surface mounting and installation	
type of electrical connection for supply voltage line-side	Box lug	
tightening torque [lbf·in] for supply	120 120 lbf·in	
type of connectable conductor cross-sections at line-side at AWG cables single or multi-stranded	1x (14 1/0 AWG)	
temperature of the conductor for supply maximum permissible	75 °C	
material of the conductor for supply	AL or CU	
type of electrical connection for load-side outgoing feeder	Box lug	
tightening torque [lbf·in] for load-side outgoing feeder	45 45 lbf·in	
type of connectable conductor cross-sections at AWG cables for load-side outgoing feeder single or multi-stranded	1x (14 2 AWG)	
temperature of the conductor for load-side outgoing feeder maximum permissible	75 °C	

	-			
material of the conductor for load-side outgoing feeder	AL or CU			
type of electrical connection of magnet coil	Screw-type terminals			
tightening torque [lbf·in] at magnet coil	5 12 lbf·in			
type of connectable conductor cross-sections of magnet coil at AWG cables single or multi-stranded	2x (16 12 AWG)			
temperature of the conductor at magnet coil maximum permissible	75 °C			
material of the conductor at magnet coil	CU			
type of electrical connection for auxiliary contacts	Screw-type terminals			
tightening torque [lbf·in] at contactor for auxiliary contacts	10 15 lbf·in			
type of connectable conductor cross-sections at contactor at AWG cables for auxiliary contacts single or multi- stranded	1x (12 AWG), 2x (16 14 AWG), 2x (18 16 AWG)			
temperature of the conductor at contactor for auxiliary contacts maximum permissible	75 °C			
material of the conductor at contactor for auxiliary contacts	CU			
type of electrical connection at overload relay for auxiliary contacts	Screw-type terminals			
tightening torque [lbf·in] at overload relay for auxiliary contacts	7 10 lbf·in			
type of connectable conductor cross-sections at overload relay at AWG cables for auxiliary contacts single or multi- stranded	2x (20 14 AWG)			
temperature of the conductor at overload relay for auxiliary contacts maximum permissible	75 °C			
material of the conductor at overload relay for auxiliary contacts	CU			
Short-circuit current rating				
design of the fuse link for short-circuit protection of the main circuit required	10kA@600V (Class H or K); 100kA@600V (Class R or J)			
certificate of suitability	NEMA ICS 2; UL 508; CSA 22.2, No.14			
Further information				
Industrial Controls - Product Overview (Catalogs, Brochures,) www.usa.siemens.com/iccatalog Industry Mall (Online ordering system) https://mall.industry.siemens.com/mall/en/us/Catalog/product?mlfb=US2:17GUG92WH15 Service&Support (Manuals, Certificates, Characteristics, FAQs,) https://support.industry.siemens.com/cs/US/en/ps/US2:17GUG92WH15 Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros,)				
http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=US2:17GUG92WH15⟨=en Certificates/approvals https://support.industry_siemens_com/cs/US/en/ps/US2:17GUG92WH15/certificate				

https://support.industry.siemens.com/cs/US/en/ps/US2:17GUG92WH15/certificate

last modified:

1/25/2022 🖸