

6	5	4	3	2	1	
						J
			20 FEE <sup>-</sup>	T ± 4.0 IN		I
<del></del>			<u>}</u>	<u></u>		Н
10-3 SOW	CORD					

ITEM	DESCRIPTION	MATERIAL	
1	#10-3 BLACK CABLE	SOW/COPPER	
2	MOLDED SOCKETS BLACK	NITRILE/PVC	
3	EYELET	BRASS	D
4	BUTTON WHITE	PORCELAIN	
5	RIVET	BRASS	
6	SCREWSHELL	COOPER	
7	1 CONDUCTOR WIRE BLACK	NEOPRENE	
8	1 CONDUCTOR WIRE WHITE	NEOPRENE	C
9	GROUND RING	BRASS	

G

F

Е

IERAL TOLERANCES		DIMENSION STYLE		SCALE	DES	SIGN UNITS		THIRD	) ANGLE			
NLESS SPECIFIED)		INCH		NTS		INCH	$ \odot \square$	PROJ	) ANGLE ECTION	В		
	mm	INCH	DRAWN		DATE							
CES	±	±	DNGL	JYEN6	2015/09/0							
CES	±	±.005	CHECK	ED BY	DATE	<u> </u>	•	3 MOL			,	
CES	±	±.010	HKNE	EELAN	2015/09/0	)4	3' 3	SPC, 3'	' LDR, 2	20' TL		
CE	<u>±</u>	±.020	APPRO		DATE	molex	MO				FD	
ANGULAR ±.5°		JFMU	JRPHY	2015/09/1								
DRAFT WHERE		MATERI	-		DOCUMENT N	10.				SHEET NO.	A	
APPLICABLE			1301	060188		SD-	130106	-042		1 0F 1		
		SIZE THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX										
THIN DIMENSIONS				C INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION								
6 5		5			4	2			ר		1	$\backslash$
		5 4		4	3				1		$\sim$	