






STRAIGHT PUSH PULL PLUG SOLDER TYPE FOR 1/4" SPIRAL SUPERFLEXIBLE

PAGE 1/3 ISSUE 20-07-17B SERIES NEX10 PART NUMBER R180060007







All dimensions are in mm. Tolerances according ISO 2768 m-H



COMPONENTS	MATERIALS	PLATING (μm)		
Body	BRASS.	BBR		
Center contact	BRASS.	SILVER		
Outer contact	BERYLLIUM COPPER	SILVER		
Insulator	PTFE			
Gasket	SILICONE RUBBER			
Others parts	BRASS,BRONZE	BBR		
-	-	-		
-	-	-		



Technical Data Sheet

STRAIGHT PUSH PULL PLUG SOLDER TYPE FOR 1/4" SPIRAL SUPERFLEXIBLE

PAGE 2/3	ISSUE 20-07-17B	SERIES NEX10	PART NUMBER R180060007
-----------------	------------------------	---------------------	-------------------------------

PACKAGING

50	Contact us	Contact us
Standard	Unit	Other

ELECTRICAL CHARACTERISTICS

Impedance 50 Frequency 0-20 GHz **VSWR** 1.02 0.0200 x F(GHz) Maxi Insertion loss 0.05 √F(GHz) dB Maxi RF leakage NA - F(GHz)) dB Maxi - (Voltage rating 500 Veff Maxi 1500 Dielectric withstanding voltage Veff mini Insulation resistance 5000 $M\Omega$ mini

MECHANICAL CHARACTERISTICS

Center contact retention Axial force - Mating End

NA N mini Axial force - Opposite end NA N mini NA N.cm mini Torque

Recommended torque

NA Mating N.cm Panel nut NA N.cm Clamp nut N.cm NA 0.0000 A/F clamp nut mm

Mating life 100 Cycles mini 12.8640 g

Weight

ENVIRONMENTAL

Operating temperature -55~+125 °С Hermetic seal NA Atm.cm3/s Panel leakage NA

SPECIFICATION

CABLE ASSEMBLY

Stripping	а	b	С	d	е	f
mm	5.3	9	0	0	0	0

Assembly instruction: NA

Recommended cable(s)

HCF 1/4" Cu2Y AlCu

Characteristics indicated on this data sheet are those that can be achieved with the highest performance cable. Intrinsic limitations of the cable may diminish the performance of the assembly

Cable retention

- pull off 250 N mini - torque N.cm

TOOLING

Part Number	Description	Hexagon

OTHER CHARACTERISTICS

IP68(1m,24h) mated condition PIM3≤-123dBm, 2 carriers of +43dBm







STRAIGHT PUSH PULL PLUG SOLDER TYPE FOR 1/4" SPIRAL SUPERFLEXIBLE

PAGE 3/3 ISSUE 20-07-17B SERIES NEX10 PART NUMBER R180060007


COMPONENTS






1

- Strip the cable.
- Do not damage the outer conductor.
- The end surface of inner conductor should be chamfered.
- Remove impurities such as copper scraps and burrs on the end surface of the cable.



3

- Push the cable into the connector body, until it stops.
- Use the reserved solder wire to wrap the cable to fill the space between cable and connector.
- Solder the connector body with cable.



2

- Insert insulator clip on the cable.
- Insert center contact until the insulator clip.
- Solder center contact.
- Wrap the cable by solder wire (Dia 0.8 mm).

