





COAXIAL TERMINATION N MALE 6 GHZ 150W

PAGE 1/2 ISSUE 10-08-20C SERIES TERMINATION PART NUMBER R404780000





All dimensions are in mm. Tolerances according ISO 2768 m-H



COMPONENTS	MATERIALS	PLATING (μm)
Body Center contact Outer contact Insulator	STAINLESS STEEL BERYLLIUM COPPER STAINLESS STEEL PTFE	PASSIVATED GOLD 0.5 OVER NICKEL PHOSPHORUS 2 PASSIVATED
Gasket Substrate	SILICONE RUBBER ALUMINIUM NITRIDE	
Resistor Others parts	THICK FILM ALUMINIUM	BLACK ANODIZATION





COAXIAL TERMINATION N MALE 6 GHZ 150W

PAGE 2/2	ISSUE 10-08-20C	SERIES TERMINATION	PART NUMBER R404780000
-----------------	-----------------	-----------------------	-------------------------------

ELECTRICAL CHARACTERISTICS

Frequency (GHz)	DC - 3	3 - 6
V.S.W.R (≤)	1.20	1.40

50	Ω
50	Ω ± 5%
2000	W
150	W (Free Air Cooled)
	W (Conduction Cooled)
	50 2000


MECHANICAL CHARACTERISTICS

Connectors	N	Male	MIL C39012
Weight	1902,62 g		

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range	-55/+125	°C
Storage temperature range	-55/+125	°C

Power derating Versus temperature



SPECIFICATION

OTHER CHARACTERISTICS

MOUNTED WITH VERTICAL COOLING FINS AND NATURAL CONVECTION