






PAGE 1/2 ISSUE 10-02-15A SERIES ATTENUATOR PART NUMBER **R414403150**





Scale 1:1



All dimensions are in mm.



COMPONENTS	MATERIALS	PLATING (μm)
Body Male center contact Female center contact	STAINLESS STEEL BERYLLIUM COPPER BERYLLIUM COPPER	PASSIVATED GOLD OVER NICKEL GOLD OVER NICKEL
Outer contact Insulator	BRASS PTFE	NICKEL
Gasket Substrate Resistor	SILICONE RUBBER ALUMINA CERAMIC THIN FILM	
Others parts	-	-



Technical Data Sheet

BNC ATTENUATOR 3 DB 4 GHZ 2W

PAGE 2/2	ISSUE 10-02-15A	SERIES ATTENUATOR	PART NUMBER R414403150
-----------------	-----------------	----------------------	-------------------------------

ELECTRICAL CHARACTERISTICS

Operating Frequency Range	DC - 4	DC - 4 GHz	
Impedance	50	Ω	
Nominal Attenuation	3	dB	
Peak power at 25°C (1µs, 1‰)	50	W	
Average power at 25°C	2	W (Free Air Cooled)	
		W (Conduction Cooled)	


MECHANICAL CHARACTERISTICS

Connectors	BNC	Male Female	MIL-C 39012
Weight	26,9000 g		

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range	-55/+125	°C
Storage temperature range	-55/+125	°C

Power derating Versus temperature



SPECIFICATION

OTHER CHARACTERISTICS