# SIEMENS

Data sheet for SINAMICS G120X

#### Article No. :

#### 6SL3220-2YE28-0AF0



Figure simila

Client order no. :
Order no. :
Offer no. :
Remarks :

Rated data		
Input		
Number of phases	3 AC	
Line voltage	380 480 V +10 9	% -20 %
Line frequency	47 63 Hz	
Rated voltage	400V IEC	480V NEC
Rated current (LO)	29.50 A	26.00 A
Rated current (HO)	24.50 A	21.30 A
Output		
Number of phases	3 AC	
Rated voltage	400V IEC	480V NEC <sup>1)</sup>
Rated power (LO)	15.00 kW	20.00 hp
Rated power (HO)	11.00 kW	15.00 hp
Rated current (LO)	32.00 A	27.00 A
Rated current (HO)	26.00 A	21.00 A
Rated current (IN)	33.00 A	
Max. output current	43.00 A	
Pulse frequency	4 kHz	
Output frequency for vector control	0 200 Hz	
Output frequency for V/f control	0 550 Hz	
Overlaged equability		

#### **Overload capability**

Low Overload (LO)

110% base load current IL for 60 s in a 300 s cycle time

High Overload (HO)

150% x base load current IH for 60 s within a 600 s cycle time

General tech. specifications		
Power factor $\lambda$	0.70 0.85	
Offset factor $\cos \phi$	0.96	
Efficiency η	0.98	
Sound pressure level (1m)	67 dB	
Power loss <sup>3)</sup>	0.438 kW	
Filter class (integrated)	RFI suppression filter for Category C2	
EMC category (with accessories)	Category C2	
Safety function "Safe Torque Off"	without	

Communication

Communication

PROFINET, EtherNet/IP

ltem no. : Consignment no. : Project :

Inputs / outputs		
Standard digital inputs		
Number	6	
Switching level: $0 \rightarrow 1$	11 V	
Switching level: $1 \rightarrow 0$	5 V	
Max. inrush current	15 mA	
Fail-safe digital inputs		
Number	1	
Digital outputs		
Number as relay changeover contact	2	
Output (resistive load)	DC 30 V, 5.0 A	
Number as transistor	0	
Analog / digital inputs		
Number	2 (Differential input)	
Resolution	10 bit	
Switching threshold as digital input		
0 → 1	4 V	
$1 \rightarrow 0$	1.6 V	
Analog outputs		
Number	1 (Non-isolated output)	
PTC/ KTY interface		
1 motor temperature sensor input, sensors that can be connected PTC, KTY and Thermo-Click, accuracy $\pm 5~^\circ\text{C}$		

Closed-loop control techniques	
V/f linear / square-law / parameterizable	Yes
V/f with flux current control (FCC)	Yes
V/f ECO linear / square-law	Yes
Sensorless vector control	Yes
Vector control, with sensor	No
Encoderless torque control	No
Torque control, with encoder	No

## SIEMENS

#### Data sheet for SINAMICS G120X

#### Article No. :

#### 6SL3220-2YE28-0AF0

Ambient conditions		
Standard board coating type	Class 3C2, according to IEC 60721-3-3: 2002	
Cooling	Air cooling using an integrated fan	
Cooling air requirement	0.018 m³/s (0.653 ft³/s)	
Installation altitude	1,000 m (3,280.84 ft)	
Ambient temperature		
Operation	-20 45 °C (-4 113 °F)	
Transport	-40 70 °C (-40 158 °F)	
Storage	-25 55 °C (-13 131 °F)	
Relative humidity		
Max. operation	95 % At 40 $^\circ C$ (104 $^\circ F), condensation and icing not permissible$	
Connections		
Signal cable		
Conductor cross-section	0.15 1.50 mm² (AWG 24 AWG 16)	
Line side		
Version	screw-type terminal	
Conductor cross-section	1.50 16.00 mm² (AWG 16 AWG 6)	
Motor end		
Version	Screw-type terminals	
Conductor cross-section	1.50 16.00 mm² (AWG 16 AWG 6)	
DC link (for braking resistor)		
PE connection	On housing with M4 screw	
Max. motor cable length		
Shielded	150 m (492.13 ft)	

Mechanical data		
Degree of protection	IP20 / UL open	type
Frame size	FSC	
Net weight	7.66 kg (16.89	9 lb)
Dimensions		
Width	140 mm (5.51	in)
Height	295 mm (11.6	1 in)
Depth	218 mm (8.58	in)
	Standards	
Compliance with standards	UL, cUL, CE, C- SEMI F47, REA	Tick (RCM), EAC, KCC, CH
CE marking		2004/108/EC, Low- ive 2006/95/EC
Converter losses to IEC61800-9-2*		
Efficiency class	IE2	
Comparison with the reference converter (90% / 100%)	39.1 %	
■ 279.0 W (1.3 %)	338.0 W (1.5 %)	438.0 W (2.0 %)
174.0 W (0.8 %)	195.0 W (0.9 %)	227.0 W (1.0 %)
138.0 W (0.6 %)	147.0 W (0.7 %)	<b>\</b>
25% •	•	

The percentage values show the losses in relation to the rated apparent power of the converter.

50%

90% **f** 

The diagram shows the losses for the points (as per standard IEC61800-9-2) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter without options/components.

\*converted values

<sup>1)</sup>The output current and HP ratings are valid for the voltage range 440V-480V

<sup>3)</sup>Typical value. More information can be found in the element group "Converter losses to IEC 61800-9-2" in this datasheet.

## SIEMENS

### Data sheet for SINAMICS G120X

#### Article No. :

#### 6SL3220-2YE28-0AF0

#### Operator panel: Basic Operator Panel (BOP-2)

Screen		
LCD, monochrome		
Mechanical data		
IP55 / UL type 12		
0.140 kg (0.31 lb)		
70.00 mm (2.76 in)		
106.85 mm (4.21 in)		
19.60 mm (0.77 in)		

Ambient conditions		
Ambient temperature		
Operation	0 50 °C (32 122 °F)	
Storage	-40 70 °C (-40 158 °F)	
Transport	-40 70 °C (-40 158 °F)	
Relative humidity at 25°C during	I	
Max. operation	95 %	
Approvals		
Certificate of suitability	CE, cULus, EAC, KCC, RCM	