


| 10           | 9        | 8                         | 7                     | 6                          | 5                      | 4     | 3      | 2         | 19006          |                |                    |                |                |
|--------------|----------|---------------------------|-----------------------|----------------------------|------------------------|-------|--------|-----------|----------------|----------------|--------------------|----------------|----------------|
| MATERIAL NO. | ENG. NO. | MATERIAL NO. TAPE MOUNTED | ENG. NO. TAPE MOUNTED | MATERIAL NO. STRIP MOUNTED | ENG. NO. STRIP MOUNTED | AWG   | COLOR  | MWID      | "L" ±.015/.381 | "E" ±.015/.381 | "C" DIA ±.015/.381 | "G" ±.015/.381 | "H" ±.015/.381 |
| 190060001    | AA-5220  | 190060003                 | AA-5220T              | 190060004                  | AA-5220Z               | 22-18 | RED    | .150/3.81 | .620/15.75     | .512/13.00     | .222/5.64          | .690/17.53     | .196/4.98      |
| 190060011    | BB-5221  | 190060013                 | BB-5221T              | 190060014                  | BB-5221Z               | 16-14 | BLUE   | .170/4.32 | .500/12.70     | .242/6.15      | .690/17.53         | .196/4.98      |                |
| 190060019    | C-5211   | 190060020                 | C-5211T               | 190060070                  | C-5211Z                | 12-10 | YELLOW | .245/6.22 | .667/16.94     | .511/12.98     | .311/7.90          | .677/17.20     | .246/6.25      |



# SALES DRAWING

- NOTES:
1. MATERIAL: BRASS.  
PLATING: ELECTROPLATE TIN.
  2. INSULATION: NYLON.
  3. MWID=MAXIMUM WIRE INSULATION DIA.
  4. ALL DIMENSIONS IN INCHES (MM).

|  |                                   |   |                       |                          |                      |                             |                              |  |  |
|--|-----------------------------------|---|-----------------------|--------------------------|----------------------|-----------------------------|------------------------------|--|--|
| EC NO: ETC2004-0126<br>DRWN: DMYRICK 2004/01/06<br>CHKD: SBEITZEL 2004/01/06<br>APPR: RDEROSS 2004/01/07 | QUALITY SYMBOLS<br>▽ - 0<br>∇ - 0 | GENERAL TOLERANCES (UNLESS SPECIFIED)   |                       | SCALE<br>NTS             | DESIGN UNITS<br>INCH | THIRD ANGLE PROJECTION      | REVISE ON CAD ONLY           |  |  |
|  |                                   | mm  | INCH                  | DIMENSION STYLE<br>IN/MM |                      |                             |                              |  |  |
|  |                                   | 4 PLACES ± --- ± ---  | 3 PLACES ± --- ± .005 | 2 PLACES ± 0.13 ± .01    | 1 PLACE ± 0.25 ± --- | DRAWN BY<br>DMYRICK         | DATE<br>03/12/26             | AVIKRIMP FLAG<br>FULLY INSULATED<br>.250 TAB WIDTH |  |
|  |                                   | ANGULAR ±1/2°<br>DRAFT WHERE APPLICABLE<br>MUST REMAIN WITHIN DIMENSIONS  |                       |                          |                      | CHECKED BY<br>SBEITZEL      | DATE<br>03/12/26             | MOLEX INCORPORATED                                 |  |
| B  | REV                               | THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION |                       | APPROVED BY<br>RDEROSS   | DATE<br>03/12/26     | MATERIAL NO.<br>(SEE CHART) | DOCUMENT NO.<br>SD-19006-001 | SHEET NO.<br>1 OF 1                                |  |