

# **MLFB-Ordering data**

6SL3220-2YE42-0UP0



Client order no. : Order no. :

Offer no. : Remarks:

Item no.: Consignment no. : Project :

Rated data			General tech.	General tech. specifications	
nput			Power factor λ	0.90 0.95	
Number of phases	3 AC		Offset factor cos φ	0.99	
Line voltage	380 480 \	/ +10 % -20 %	Efficiency η	0.98	
Line frequency	47 63 Hz		Sound pressure level (1m)	72 dB	
Rated voltage	400V IEC	480V NEC	Power loss	1.230 kW	
Rated current (LO)	144.00 A	120.00 A	Filter class (integrated)	Unfiltered	
Rated current (HO)	117.00 A	102.00 A	Titler class (integrated)	ommered	
Output			EMC category (with accessories)	without	
Number of phases	3 AC				
Rated voltage	400V IEC	480V NEC	Ambient conditions		
Rated power (LO)	75.00 kW	100.00 hp	Standard board coating type	Class 3C2, according to IEC 60721-3 3: 2002	
Rated power (HO)	55.00 kW	60.00 hp			
Rated current (LO)	145.00 A	124.00 A	Cooling	Air cooling using an integrated fan	
Rated current (HO)	110.00 A	96.00 A			
Rated current (IN)	149.00 A		Cooling air requirement	0.153 m³/s (5.403 ft³/s)	
Max. output current	196.00 A		Installation altitude	1000 m (3280.84 ft)	
Pulse frequency	4 kHz		Ambient temperature		
Output frequency for vector control	0 200 Hz		Operation	-20 45 °C (-4 113 °F)	
			Transport	-40 70 °C (-40 158 °F)	
Output frequency for V/f control	0 550 Hz		Storage	-25 55 °C (-13 131 °F)	
			Relative humidity		
Overload capability			Max. operation	95 % At 40 °C (104 °F), condensatio and icing not permissible	

# O

## Low Overload (LO)

110% base load current IL for 60 s in a 300 s cycle time

# High Overload (HO)

150% x base load current IH for 60 s within a 600 s cycle time



# **MLFB-Ordering data**

6SL3220-2YE42-0UP0



Mechanical	data	Closed-loop co	ntrol techniques	
Degree of protection	IP20 / UL open type		1	
Size	FSF	V/f linear / square-law / parameter	<b>rizable</b> Yes	
Net weight	61 kg (134.48 lb)	V/f with flux current control (FCC)	Yes	
Width	305 mm (12.01 in)	V/f ECO linear / square-law	Yes	
Height	709 mm (27.91 in)	Sensorless vector control	Yes	
Depth	369 mm (14.53 in)	Vector control, with sensor	No	
Inputs / out		Encoderless torque control	Yes	
Standard digital inputs	puts			
		Torque control, with encoder	No	
Number	6	Commu	ınication	
Switching level: 0→1	11 V	Communication	PROFIBUS DP	
Switching level: 1→0	5 V	Conne	ections	
Max. inrush current	15 mA	Signal cable		
Fail-safe digital inputs			0.15 1.50 mm²	
Number	1	Conductor cross-section	(AWG 24 AWG 16)	
Digital outputs		Line side		
Number as relay changeover contact	2	Version	M10 screw	
Output (resistive load)	DC 30 V, 5.0 A	Conductor cross-section	35.00 120.00 mm² (AWG 1 AWG 4/0)	
Number as transistor	0	Motor end		
Analog / digital inputs		Version	M10 screw	
Number	2 (Differential input)	Conductor cross-section	35.00 120.00 mm² (AWG 1 AWG 4/0)	
Resolution	10 bit	DC link (for braking resistor)	,	
Switching threshold as digital inp	out	PE connection	M10 screw	
0→1	4 V	Max. motor cable length	Wife screw	
1→0	1.6 V	Shielded	300 m (984.25 ft)	
Analog outputs		Unshielded	450 m (1476.38 ft)	
Number	1 (Non-isolated output)			
PTC/ KTY interface				
1 motor temperature sensor input, sensor and Thermo-Click, accuracy ±5 °C	rs that can be connected: PTC, KTY			

Page 2 of 3



### MLFB-Ordering data

#### 6SL3220-2YE42-0UP0



Converter losses to EN 50598-2*					
Efficiency class			IE2		
Comparison with the reference converter (90% / 42.10 % 100%)					
11	<b>`</b>				
100% -	1393.0 W (1.39 %)	1609.9 W (1.60 %)	1970.2 W (1.96 %) <b>&gt;</b>		
		1 	1 		
50% →	789.7 W (0.79 %)	870.7 W (0.87 %)	988.3 W (0.98 %)		

# **Standards**

UL, cUL, CE, C-Tick (RCM), EAC, KCC, SEMI Compliance with standards F47, REACH

EMC Directive 2004/108/EC, Low-Voltage **CE** marking Directive 2006/95/EC

620 W (0.62 %) 585.4 W (0.58 %) 50% 90%

The percentage values show the losses in relation to the rated apparent power of the converter.

The diagram shows the losses for the points (as per standard EN 50598) of the relative torque generating current (I) over the relative motor stator frequency(f). The values are valid for the basic version of the converter without options/components.

# Operator panel: Basic Operator Panel (BOP-2)

Screen		Ambient conditions	
Display design	LCD, monochrome	Ambient temperature during	
		Operation	0 50 °C (32 122 °F)
Mechanical data		Storage	-40 70 °C (-40 158 °F)
Degree of protection	IP55 / UL type 12	Transport	-40 70 °C (-40 158 °F)
Net weight	0.14 kg (0.31 lb)	Relative humidity at 25°C d	uring
Width	70.0 mm (2.76 in)	Max. operation	95 %
Height	106.85 mm (4.21 in)		Approvals
Depth	19.60 mm (0.77 in)		
- <b> </b>	15100 (6177)	Certificate of suitability	CE, cULus, EAC, KCC, RCM

<sup>\*</sup>converted values