

## SPECIFICATIONS:

**ELECTRICAL:** 

**CURRENT RATING:** 1 AMPS

1,000 MΩ MIN. @ 500 VDC INSULATION RESISTANCE: DIELECTRIC WITHSTANDING VOLTAGE: 1,000 VAC FOR 1 MINUTE

CONTACT RESISTANCE:  $30 \text{ m}\Omega \text{ MAX}.$ **OPERATING TEMPERATURE:** -55°C TO +105°C


**MATERIALS:** 

INSULATION: PBT, UL 94 V-O RATED CONTACTS: PHOSPHOR BRONZE

**CONTACT PLATING:** GOLD FLASH IN MATING AREA

BRIGHT TIN IN SOLDER AREA

SHELL: STEEL, NICKEL PLATED



WILL ACCEPT 26-20 AWG WIRE

## ROHS COMPLIANT

DESCRIPTION: 0.085 RIBBON - SOLDER CUP

THESE DRAWINGS AND SPECIFICATIONS ARE APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN: WAYNE ROBBINS

DATE: 09/15/2005 UNITS = mm

SHEET 1

DO NOT SCALE FROM DRAWING

REV

NorComp NTS DWG NO.

SCALE:

111-YYY-103L101

OF