SIEMENS

Data sheet 3RW5227-3AC05



SIRIUS soft starter 200-600 V 93 A, 24 V AC/DC spring-type terminals Analog output

product brand name	SIRIUS
product category	Hybrid switching devices
product designation	Soft starter
product type designation	3RW52
manufacturer's article number	
 of standard HMI module usable 	3RW5980-0HS00
 of high feature HMI module usable 	3RW5980-0HF00
 of communication module PROFINET standard usable 	3RW5980-0CS00
 of communication module PROFIBUS usable 	3RW5980-0CP00
 of communication module Modbus TCP usable 	3RW5980-0CT00
 of communication module Modbus RTU usable 	3RW5980-0CR00
 of communication module Ethernet/IP 	3RW5980-0CE00
 of circuit breaker usable at 400 V 	3VA2216-7MN32-0AA0; Type of coordination 1, Iq = 15 kA, CLASS 10
 of circuit breaker usable at 500 V 	3VA2216-7MN32-0AA0; Type of coordination 1, Iq = 10 kA, CLASS 10
 of circuit breaker usable at 400 V at inside-delta circuit 	3VA2220-7MN32-0AA0; Type of coordination 1, Iq = 15 kA, CLASS 10
 of circuit breaker usable at 500 V at inside-delta circuit 	3VA2220-7MN32-0AA0; Type of coordination 1, Iq = 10 kA, CLASS 10
 of the gG fuse usable up to 690 V 	3NA3136-6; Type of coordination 1, Iq = 65 kA
 of the gG fuse usable at inside-delta circuit up to 500 V 	3NA3136-6; Type of coordination 1, Iq = 65 kA
 of full range R fuse link for semiconductor protection usable up to 690 V 	3NE1224-0; Type of coordination 2, Iq = 65 kA
 of back-up R fuse link for semiconductor protection usable up to 690 V 	3NE4124; Type of coordination 2, Iq = 65 kA

General technical data	
starting voltage [%]	30 100 %
stopping voltage [%]	50 %; non-adjustable
start-up ramp time of soft starter	0 20 s
current limiting value [%] adjustable	130 700 %
certificate of suitability	
CE marking	Yes
 UL approval 	Yes
CSA approval	Yes
product component	
HMI-High Feature	No
 is supported HMI-Standard 	Yes
 is supported HMI-High Feature 	Yes
product feature integrated bypass contact system	Yes
number of controlled phases	3

Auto alasa	OLACO 40A (1-5!) / 40E / 00E: t- IEO 00047 4 0		
trip class	CLASS 10A (default) / 10E / 20E; acc. to IEC 60947-4-2		
buffering time in the event of power failure			
for main current circuit	100 ms		
for control circuit	100 ms		
insulation voltage rated value	600 V		
degree of pollution	3, acc. to IEC 60947-4-2		
impulse voltage rated value	6 kV		
blocking voltage of the thyristor maximum	1 800 V		
service factor	1		
surge voltage resistance rated value	6 kV		
maximum permissible voltage for safe isolation			
between main and auxiliary circuit	600 V		
shock resistance	15 g / 11 ms, from 12 g / 11 ms with potential contact lifting		
vibration resistance	15 mm to 6 Hz; 2g to 500 Hz		
utilization category according to IEC 60947-4-2	AC 53a		
reference code according to IEC 81346-2	Q		
Substance Prohibitance (Date)	02/15/2018		
product function			
ramp-up (soft starting)	Yes		
• ramp-down (soft stop)	Yes		
Soft Torque	Yes		
adjustable current limitation	Yes		
pump ramp down	Yes		
intrinsic device protection	Yes		
motor overload protection	Yes; Electronic motor overload protection		
 evaluation of thermistor motor protection 	No		
• inside-delta circuit	Yes		
auto-RESET	Yes		
manual RESET	Yes		
• remote reset	Yes; By turning off the control supply voltage		
communication function	Yes		
operating measured value display	Yes; Only in conjunction with special accessories		
error logbook	Yes; Only in conjunction with special accessories		
via software parameterizable	No		
via software configurable	Yes		
PROFlenergy	Yes; in connection with the PROFINET Standard communication		
£	module		
• firmware update	Yes		
removable terminal for control circuit	Yes		
• torque control	No		
analog output	Yes; 4 20 mA (default) / 0 10 V (parameterizable with High Feature HMI)		
Power Electronics			
operational current			
at 40 °C rated value	93 A		
at 50 °C rated value	83 A		
• at 60 °C rated value	76 A		
operational current at inside-delta circuit			
at 40 °C rated value	161 A		
at 50 °C rated value	143 A		
at 60 °C rated value	131 A		
operating voltage			
• rated value	200 600 V		
at inside-delta circuit rated value	200 600 V		
relative negative tolerance of the operating voltage	-15 %		
relative negative tolerance of the operating voltage	10 %		
relative negative tolerance of the operating voltage at	-15 %		
inside-delta circuit			
relative positive tolerance of the operating voltage at inside-delta circuit	10 %		
operating power for 3-phase motors			

at 220 V at 40 °C rated value	20 144
• at 230 V at 40 °C rated value	22 kW
at 230 V at inside-delta circuit at 40 °C rated value	45 kW
• at 400 V at 40 °C rated value	45 kW
 at 400 V at inside-delta circuit at 40 °C rated value 	90 kW
• at 500 V at 40 °C rated value	55 kW
at 500 V at inside-delta circuit at 40 °C rated value	110 kW
Operating frequency 1 rated value	50 Hz
Operating frequency 2 rated value	60 Hz
relative negative tolerance of the operating frequency	-10 %
relative positive tolerance of the operating frequency	10 %
adjustable motor current	
 at rotary coding switch on switch position 1 	40.5 A
 at rotary coding switch on switch position 2 	44 A
 at rotary coding switch on switch position 3 	47.5 A
 at rotary coding switch on switch position 4 	51 A
 at rotary coding switch on switch position 5 	54.5 A
 at rotary coding switch on switch position 6 	58 A
 at rotary coding switch on switch position 7 	61.5 A
 at rotary coding switch on switch position 8 	65 A
 at rotary coding switch on switch position 9 	68.5 A
 at rotary coding switch on switch position 10 	72 A
 at rotary coding switch on switch position 11 	75.5 A
 at rotary coding switch on switch position 12 	79 A
 at rotary coding switch on switch position 13 	82.5 A
 at rotary coding switch on switch position 14 	86 A
 at rotary coding switch on switch position 15 	89.5 A
 at rotary coding switch on switch position 16 	93 A
• minimum	40.5 A
adjustable motor current	
 for inside-delta circuit at rotary coding switch on switch position 1 	70.1 A
 for inside-delta circuit at rotary coding switch on switch position 2 	76.2 A
 for inside-delta circuit at rotary coding switch on switch position 3 	82.3 A
 for inside-delta circuit at rotary coding switch on switch position 4 	88.3 A
 for inside-delta circuit at rotary coding switch on switch position 5 	94.4 A
 for inside-delta circuit at rotary coding switch on switch position 6 	100 A
 for inside-delta circuit at rotary coding switch on switch position 7 	107 A
for inside-delta circuit at rotary coding switch on switch position 8 for inside delta circuit at retery coding switch on	113 A
for inside-delta circuit at rotary coding switch on switch position 9 for inside delta circuit at rotary coding switch on	119 A
for inside-delta circuit at rotary coding switch on switch position 10 for inside delta circuit at rotary coding switch on	125 A
for inside-delta circuit at rotary coding switch on switch position 11 for inside delta circuit at rotary coding switch on	131 A
for inside-delta circuit at rotary coding switch on switch position 12	137 A
 for inside-delta circuit at rotary coding switch on switch position 13 	143 A
 for inside-delta circuit at rotary coding switch on switch position 14 	149 A
for inside-delta circuit at rotary coding switch on switch position 15	155 A
for inside-delta circuit at rotary coding switch on switch position 16	161 A
at inside-delta circuit minimum	70.1 A
minimum load [%]	15 %; Relative to smallest settable le
power loss [W] for rated value of the current at AC	

 at 40 °C after startup 	40 W		
 at 50 °C after startup 	37 W		
at 60 °C after startup	35 W		
power loss [W] at AC at current limitation 350 %			
 at 40 °C during startup 	1 270 W		
at 50 °C during startup	1 077 W		
at 60 °C during startup	959 W		
Control circuit/ Control	000 **		
	10.00		
type of voltage of the control supply voltage	AC/DC		
control supply voltage at AC			
 at 50 Hz rated value 	24 V		
at 60 Hz rated value	24 V		
relative negative tolerance of the control supply voltage at AC at 50 Hz	-20 %		
relative positive tolerance of the control supply voltage at AC at 50 Hz	20 %		
relative negative tolerance of the control supply voltage at AC at 60 Hz	-20 %		
relative positive tolerance of the control supply voltage at AC at 60 Hz	20 %		
control supply voltage frequency	50 60 Hz		
relative negative tolerance of the control supply voltage frequency	-10 %		
relative positive tolerance of the control supply voltage frequency	10 %		
control supply voltage			
at DC rated value	24 V		
relative negative tolerance of the control supply voltage at DC	-20 %		
relative positive tolerance of the control supply voltage at DC	20 %		
control supply current in standby mode rated value	160 mA		
holding current in bypass operation rated value	380 mA		
locked-rotor current at close of bypass contact maximum	7.6 A		
inrush current peak at application of control supply voltage maximum	3.3 A		
duration of inrush current peak at application of control supply voltage	12.1 ms		
design of the overvoltage protection	Varistor		
design of short-circuit protection for control circuit	4 A gG fuse (Icu=1 kA), 6 A quick-acting fuse (Icu=1 kA), C1 miniature circuit breaker (Icu= 600 A), C6 miniature circuit breaker (Icu= 300 A); Is not part of scope of supply		
Inputs/ Outputs			
number of digital inputs	1		
number of digital outputs	3		
not parameterizable	2		
digital output version	2 normally-open contacts (NO) / 1 changeover contact (CO)		
number of analog outputs	1		
switching capacity current of the relay outputs			
• at AC-15 at 250 V rated value	3 A		
at DC-13 at 24 V rated value	1A		
	1.0		
Installation/ mounting/ dimensions			
mounting position	with vertical mounting surface +/-90° rotatable, with vertical mounting surface +/- 22.5° tiltable to the front and back		
fastening method	screw fixing		
height	306 mm		
width	185 mm		
depth	203 mm		
required spacing with side-by-side mounting			
	40		
forwards	10 mm		
forwardsbackwards	0 mm		

downwards	75 mm		
at the side	5 mm		
weight without packaging	6.9 kg		
Connections/ Terminals			
type of electrical connection			
for main current circuit	box terminal		
for control circuit	spring-loaded terminals		
width of connection bar maximum	25 mm		
type of connectable conductor cross-sections			
 for main contacts for box terminal using the front clamping point solid 	1x (2.5 16 mm²)		
 for main contacts for box terminal using the front clamping point finely stranded with core end processing 	1x (2.5 50 mm²)		
 for main contacts for box terminal using the front clamping point stranded 	1x (10 70 mm²)		
using the front clamping point	1x (10 2/0)		
 for main contacts for box terminal using the back clamping point solid 	1x (2.5 16 mm²)		
using the back clamping point	1x (10 2/0)		
for main contacts for box terminal using both clamping points solid	2x (2.5 16 mm²)		
 for main contacts for box terminal using both clamping points finely stranded with core end processing 	2x (2.5 35 mm²)		
for main contacts for box terminal using both clamping points stranded	2x (6 16 mm²), 2x (10 50 mm²)		
 for main contacts for box terminal using the back clamping point finely stranded with core end processing 	1x (2.5 50 mm²)		
for main contacts for box terminal using the back clamping point stranded	1x (10 70 mm²)		
type of connectable conductor cross-sections			
for control circuit solid	2x (0.25 1.5 mm²)		
processing	2x (0.25 1.5 mm²)		
	2x (24 16)		
 at AWG cables for control circuit finely stranded with core end processing 	2x (24 16)		
wire length			
 between soft starter and motor maximum 	800 m		
at the digital inputs at AC maximum	100 m		
at the digital inputs at DC maximum	1 000 m		
tightening torque			
21	4.5 6 N·m		
	0.8 1.2 N·m		
terminals			
tightening torque [lbf-in]	40 53 lhf-in		
 for main contacts with screw-type terminals for auxiliary and control contacts with screw-type 	40 53 lbf·in 7 10.3 lbf·in		
terminals	7 10.0 IDI III		
Ambient conditions			
installation altitude at height above sea level maximum	5 000 m; Derating as of 1000 m, see catalog		
ambient temperature			
during operation	-25 +60 °C; Please observe derating at temperatures of 40 °C or above		
during storage and transport	-40 +80 °C		
environmental category			
	3K6 (no ice formation, only occasional condensation), 3C3 (no salt mist), 3S2 (sand must not get into the devices), 3M6		
	1K6 (only occasional condensation), 1C2 (no salt mist), 1S2 (sand must not get inside the devices), 1M4		
during transport according to IEC 60721	2K2, 2C1, 2S1, 2M2 (max. fall height 0.3 m)		

EMC emitted interference	acc. to IEC 60947-4-2: Class A		
Communication/ Protocol			
communication module is supported			
PROFINET standard	Yes		
• EtherNet/IP	Yes		
Modbus RTU	Yes		
Modbus TCP	Yes		
PROFIBUS	Yes		
UL/CSA ratings			
manufacturer's article number			
of circuit breaker			
 usable for Standard Faults at 460/480 V according to UL 	Siemens type: 3VA51, max. 125 A; Iq = 10 kA		
 usable for High Faults at 460/480 V according to UL 	Siemens type: 3VA51, max. 125 A; lq max = 65 kA		
 usable for Standard Faults at 460/480 V at inside-delta circuit according to UL 	Siemens type: 3VA51, max. 125 A; Iq = 10 kA		
 usable for High Faults at 460/480 V at insidedelta circuit according to UL 	Siemens type: 3VA51, max. 125 A; Iq max = 65 kA		
 usable for Standard Faults at 575/600 V according to UL 	Siemens type: 3VA51, max. 125 A; Iq = 10 kA		
 usable for Standard Faults at 575/600 V at inside-delta circuit according to UL 	Siemens type: 3VA51, max. 125 A; Iq = 10 kA		
• of the fuse			
 usable for Standard Faults up to 575/600 V according to UL 	Type: Class RK5 / K5, max. 300 A; Iq = 10 kA		
 — usable for High Faults up to 575/600 V according to UL 	Type: Class J / L, max. 250 A; Iq = 100 kA		
 usable for Standard Faults at inside-delta circuit up to 575/600 V according to UL 	Type: Class RK5 / K5, max. 300 A; Iq = 10 kA		
 usable for High Faults at inside-delta circuit up to 575/600 V according to UL 	Type: Class J / L, max. 250 A; Iq = 100 kA		
operating power [hp] for 3-phase motors			
 at 200/208 V at 50 °C rated value 	25 hp		
at 220/230 V at 50 °C rated value	30 hp		
• at 460/480 V at 50 °C rated value	60 hp		
• at 575/600 V at 50 °C rated value	75 hp		
at 200/208 V at inside-delta circuit at 50 °C rated value	40 hp		
 at 220/230 V at inside-delta circuit at 50 °C rated value 	50 hp		
 at 460/480 V at inside-delta circuit at 50 °C rated value 	100 hp		
at 575/600 V at inside-delta circuit at 50 °C rated value	125 hp		
contact rating of auxiliary contacts according to UL	R300-B300		
Safety related data			
protection class IP on the front according to IEC 60529	IP00; IP20 with cover		
touch protection on the front according to IEC 60529	finger-safe, for vertical contact from the front with cover		
electromagnetic compatibility	in accordance with IEC 60947-4-2		
Certificates/ approvals			
General Product Approval		EMC	





Confirmation







Declaration of Conformity Test Certificates Marine / Shipping





Type Test Certificates/Test Report







Marine / Shipping

other





Confirmation

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RW5227-3AC05

Cax online generator

http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RW5227-3AC05

 ${\bf Service \& Support~(Manuals,~Certificates,~Characteristics,~FAQs,...)}$

https://support.industry.siemens.com/cs/ww/en/ps/3RW5227-3AC05

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RW5227-3AC05&lang=en

Characteristic: Tripping characteristics, I2t, Let-through current

https://support.industry.siemens.com/cs/ww/en/ps/3RW5227-3AC05/char

Characteristic: Installation altitude

http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3RW5227-3AC05&objecttype=14&gridview=view1

Simulation Tool for Soft Starters (STS)

https://support.industry.siemens.com/cs/ww/en/view/101494917

last modified: 4/10/2022 🖸