SIEMENS

Data sheet

3RA2120-1DD23-0AP6



Fuseless motor starter Direct start 600VAC Size S0 2.2-3.2A 220/240VAC 50/60HZ screw connection For snapping onto 60 mm busbar systems Type of coordination 2 IQ = 150 KA Also full fills type Of coordination 1 1NO+1NC (contactor)

product brand name	SIRIUS				
product designation	non-fused motor starter 3RA2				
design of the product	direct starter				
manufacturer's article number					
 of the supplied contactor 	<u>3RT2023-1AP60</u>				
 of the supplied circuit-breakers 	<u>3RV2011-1DA10</u>				
 of the supplied busbar adapter 	8US1251-5NT10				
 of the supplied link module 	<u>3RA2921-1AA00</u>				
General technical data					
size of the circuit-breaker	S00				
size of load feeder	SO				
product extension auxiliary switch	Yes				
insulation voltage with degree of pollution 3 at AC rated value	690 V				
degree of pollution	3				
surge voltage resistance rated value	6 kV				
shock resistance according to IEC 60068-2-27	6g / 11 ms				
mechanical service life (switching cycles) of contactor typical	10 000 000				
type of assignment	2				
Ambient conditions					
ambient temperature					
 during operation 	-20 +60 °C				
 during storage 	-50 +80 °C				
 during transport 	-55 +80 °C				
Main circuit					
number of polos for main surrent sireuit					
number of poles for main current circuit	3				
design of the switching contact	3 electromechanical				
	•				
design of the switching contact adjustable current response value current of the	electromechanical				
design of the switching contact adjustable current response value current of the current-dependent overload release	electromechanical				
design of the switching contact adjustable current response value current of the current-dependent overload release operating voltage	electromechanical 2.2 3.2 A				
design of the switching contact adjustable current response value current of the current-dependent overload release operating voltage • rated value	electromechanical 2.2 3.2 A 690 V				
design of the switching contact adjustable current response value current of the current-dependent overload release operating voltage • rated value • at AC-3 rated value maximum	electromechanical 2.2 3.2 A 690 V 690 V				
design of the switching contact adjustable current response value current of the current-dependent overload release operating voltage • rated value • at AC-3 rated value maximum operating frequency rated value	electromechanical 2.2 3.2 A 690 V 690 V 50 60 Hz				
design of the switching contact adjustable current response value current of the current-dependent overload release operating voltage • rated value • at AC-3 rated value maximum operating frequency rated value operational current at AC-3 at 400 V rated value	electromechanical 2.2 3.2 A 690 V 690 V 50 60 Hz				
design of the switching contact adjustable current response value current of the current-dependent overload release operating voltage • rated value • at AC-3 rated value maximum operating frequency rated value operational current at AC-3 at 400 V rated value operating power at AC-3	electromechanical 2.2 3.2 A 690 V 690 V 50 60 Hz 2.7 A				
design of the switching contact adjustable current response value current of the current-dependent overload release operating voltage • rated value • at AC-3 rated value maximum operating frequency rated value operating power at AC-3 at 400 V rated value operating power at AC-3 • at 400 V rated value	electromechanical 2.2 3.2 A 690 V 690 V 50 60 Hz 2.7 A 1 100 W				

a at 50 Hz rated value	220 V			
 at 50 Hz rated value at 50 Hz rated value 				
at 50 Hz rated value at 60 Hz rated value	176 242 V 240 V			
at 60 Hz rated value	240 V 192 264 V			
apparent holding power of magnet coil at AC	7.2 VA			
inductive power factor with the holding power of the	0.28			
coil	0.20			
Auxiliary circuit				
number of NC contacts for auxiliary contacts	1			
number of NO contacts for auxiliary contacts	1			
Protective and monitoring functions				
trip class	CLASS 10			
design of the overload release	thermal (bimetallic)			
response value current of instantaneous short-circuit trip unit	41.6 A			
UL/CSA ratings				
full-load current (FLA) for 3-phase AC motor				
 at 480 V rated value 	2.8 A			
• at 600 V rated value	3.16 A			
yielded mechanical performance [hp]				
 for single-phase AC motor 				
— at 110/120 V rated value	0.1 hp			
— at 230 V rated value	0.25 hp			
 for 3-phase AC motor 				
— at 200/208 V rated value	0.5 hp			
— at 220/230 V rated value	0.75 hp			
— at 460/480 V rated value	1.5 hp			
— at 575/600 V rated value	2 hp			
Short-circuit protection				
product function short circuit protection	Yes			
design of the short-circuit trip	magnetic			
 conditional short-circuit current (Iq) at 400 V according to IEC 60947-4-1 rated value 	152,000 4			
Installation/ mounting/ dimensions	153 000 A			
	vertical			
fastening method	_ vertical for snapping onto 60 mm busbar systems			
height	260 mm			
width	45 mm			
depth	155 mm			
required spacing				
 for grounded parts 				
— forwards	10 mm			
— backwards	0 mm			
— upwards	30 mm			
— at the side	9 mm			
— downwards	10 mm			
 for live parts 				
— forwards	10 mm			
— backwards	0 mm			
— upwards	30 mm			
— downwards	10 mm			
— at the side	9 mm			
Connections/ Terminals				
type of electrical connection for main current circuit	screw-type terminals			
type of connectable conductor cross-sections	$1 10 \text{ mm}^2 2 \text{ y} (2 \text{ F} 6 \text{ mm}^2)$			
 for main contacts stranded at AWG cables for main contacts 	1 10 mm ² , 2x (2.5 6 mm ²) 2x (16 12) 2x (14 8)			
at AWG cables for main contacts connectable conductor cross-section for main contacts	2x (16 12), 2x (14 8) 1 6 mm ²			
finely stranded with core end processing				
Safety related data				

B10 value with high demand rate according to SN 31920			1 000 000			
proportion of dangerous failures with high demand rate according to SN 31920		73 %				
protection class IP on the front according to IEC 60529		IP20				
touch protection on the front according to IEC 60529		finger-safe, for vertical contact from the front				
Certificates/ approvals						
General Product Approv	al	For use in ha		Declaration of Conformity	other	
<u>Confirmation</u>	EAC	(Ex)		CE EG-Konf,	<u>Confirmation</u>	

Further information

Information- and Downloadcenter (Catalogs, Brochures,...) https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RA2120-1DD23-0AP6

Cax online generator

http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RA2120-1DD23-0AP6

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)


https://support.industry.siemens.com/cs/ww/en/ps/3RA2120-1DD23-0AP6

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RA2120-1DD23-0AP6&lang=en

Characteristic: Tripping characteristics, I²t, Let-through current

https://support.industry.siemens.com/cs/ww/en/ps/3RA2120-1DD23-0AP6/char Further characteristics (e.g. electrical endurance, switching frequency)

http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3RA2120-1DD23-0AP6&objecttype=14&gridview=view1



last modified:

12/15/2020 🖸