SIEMENS

Data sheet

3RE4122-4AA31-1GY0



STARTER, FVNR, S0, 3PH, THOLR, 120VAC, NEMA 1

Fi	gure	esir	nila	ir i

product brand name	Siemens			
product designation	Non-reversing motor starter			
special product feature	No factory installed accessories			
General technical data				
weight [lb]	8 lb			
Height x Width x Depth [in]	11 × 7 × 5 in			
touch protection against electrical shock	NA for enclosed products			
installation altitude [ft] at height above sea level maximum	6 560 ft			
ambient temperature [°F] during storage	-22 +149 °F			
ambient temperature [°F] during operation	-4 +104 °F			
ambient temperature during storage	-30 +65 °C			
ambient temperature during operation	-20 +40 °C			
country of origin	Germany			
Power and control electronics				
number of poles for main current circuit	3			
type of voltage of the control supply voltage	AC			
control supply voltage				
 at AC at 50 Hz rated value 	110 V			
• at AC at 60 Hz rated value	120 V			
disconnector functionality	No			
yielded mechanical performance [hp] for 3-phase AC motor				
• at 200/208 V rated value	3 hp			
 at 220/230 V rated value 	3 hp			
• at 460/480 V rated value	7.5 hp			
• at 575/600 V rated value	10 hp			
Contactor				
number of NO contacts for main contacts	3			
operating voltage for main current circuit at AC at 60 Hz maximum	600 V			
operating voltage at AC-3 rated value maximum	600 V			
mechanical service life (switching cycles) of the main contacts typical	10 000 000			
Auxiliary contact				
number of NC contacts for auxiliary contacts	1			
number of NO contacts for auxiliary contacts	1			
number of total auxiliary contacts maximum	8			
contact rating of auxiliary contacts of contactor according to UL	10A@600V(A600), 2.5A@600V(Q600)			

Coil				
apparent pick-up power of magnet coil at AC	67 VA			
apparent holding power of magnet coil at AC	6.5 VA			
operating range factor control supply voltage rated value of magnet coil	0.8 1.1			
ON-delay time	9 38 ms			
OFF-delay time	4 16 ms			
Overload relay				
product function				
 overload protection 	Yes			
test function	Yes			
external reset	Yes			
reset function	Manual, automatic and remote (with optional accessory)			
adjustment range of thermal overload trip unit	4.5 6.3			
number of NC contacts of auxiliary contacts of overload relay	1			
number of NO contacts of auxiliary contacts of overload relay	1			
contact rating of auxiliary contacts of overload relay according to UL	5A@600VAC (B600), 1A@250VDC (R300)			
Enclosure				
degree of protection NEMA rating of the enclosure	NEMA 1 standard size enclosure			
design of the housing	indoors, usable on a general basis			
Mounting/wiring				
mounting position	vertical			
fastening method	Surface mounting and installation			
type of electrical connection for supply voltage line-side	Screw-type terminals			
tightening torque [lbf·in] for supply	18 21 lbf·in			
type of connectable conductor cross-sections at line-side at AWG cables single or multi-stranded	2x (16 12), 2x (14 8)			
temperature of the conductor for supply maximum permissible	60 °C			
material of the conductor for supply	CU			
type of electrical connection for load-side outgoing feeder	Screw-type terminals			
tightening torque [lbf·in] for load-side outgoing feeder	18 21 lbf·in			
type of connectable conductor cross-sections at AWG cables for load-side outgoing feeder single or multi- stranded	2x (16 12), 2x (14 8)			
temperature of the conductor for load-side outgoing feeder maximum permissible	60 °C			
material of the conductor for load-side outgoing feeder	CU			
type of electrical connection of magnet coil	Screw-type terminals			
tightening torque [lbf·in] at magnet coil	7 10 lbf·in			
type of connectable conductor cross-sections of magnet coil at AWG cables single or multi-stranded	2x (16 12), 2x (14 8)			
temperature of the conductor at magnet coil maximum permissible	75 °C			
material of the conductor at magnet coil	CU			
type of electrical connection for auxiliary contacts	Screw-type terminals			
tightening torque [lbf·in] at contactor for auxiliary contacts	7 10 lbf·in			
type of connectable conductor cross-sections at contactor at AWG cables for auxiliary contacts single or multi- stranded	2x (20 16), 2x (18 14)			
temperature of the conductor at contactor for auxiliary contacts maximum permissible	75 °C			
material of the conductor at contactor for auxiliary contacts	CU			
type of electrical connection at overload relay for auxiliary contacts	Screw-type terminals			
tightening torque [lbf·in] at overload relay for auxiliary contacts	7 10 lbf·in			
type of connectable conductor cross-sections at overload relay at AWG cables for auxiliary contacts single or multi- stranded	2x (20 16), 2x (18 14)			
temperature of the conductor at overload relay for auxiliary	70 °C			

	_		
contacts maximum permissible			
material of the conductor at overload relay for auxiliary contacts	CU		
Short-circuit current rating			
design of the fuse link for short-circuit protection of the main circuit required	Class J		
design of the short-circuit trip	Thermal magnetic circuit breaker		
breaking capacity maximum short-circuit current (Icu)			
• at 240 V	5 kA		
• at 480 V	5 kA		
• at 600 V	5 kA		
certificate of suitability	UL 60947-4-1		

Further information

Industrial Controls - Product Overview (Catalogs, Brochures,...)

www.usa.siemens.com/iccatalog

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/us/Catalog/product?mlfb=3RE4122-4AA31-1GY0


Search Datasheet in Service&Support (Manuals)

https://support.industry.siemens.com/cs/US/en/ps/3RE4122-4AA31-1GY0/man

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RE4122-4AA31-1GY0&lang=en

Certificates/approvals

https://support.industry.siemens.com/cs/US/en/ps/3RE4122-4AA31-1GY0/certificate



last modified:

1/25/2022 🖸