


т	۵	н п	m	O







LAYOUT SHOWN AS

Keying Shown as example

CHARACTERISTICS

BASIC SERIES:

SHELL SIZE : 13

PLATING : M = Nickel

Н

SHELL TYPE : Square Flange Receptacle

CONTACT TYPE : Standard Crimp Contact

ယ

 \sim

-Standard : Based on MIL-DTL-38999 Series III

-Shell Material : Composite : Nickel -Shell Plating -Insulator : Thermoplastic -Contacts : Copper Alloy -Seals & Grommet : Silicon Elastomer -Contact Plating : Gold over copper Alloy $0.8 \mu m$ minimum -Durability : 500 Mating cycles -Delivered with Souriau contacts and Accessories : -65°C to +200°C -Temperature Range : 2000 hours -Salt Spray -Mass : 13.7 g ± 10%

8D 0

G

13

Μ

04

А


F

А

Connector dimension		
Dim	Nominal	
Р	3.25±0.2	
PP	4.93±0.2	
R1	23.01	
R2	20.62	
S	28.6±0.3	
V'	19.5+1.4/-0	
W'	2.1/3.65	
Ζ'	32 Max	
VV THREAD	M18x1-6g	

Е

SOURIAU shall not be liable for due to a use of the Products the Specifications issued by either (professional recomment



ω		A			
	-			4	
1° (§					
	J.				
10					
1					
S EXAMPLE				3	
any non-confor which does not		e			
which does not comply with or of the Parties or by a third party dation, technical notice.)					
	risdiction & Co	ntrol List			
R	Not Listed			2	
3M04AA					
	CUSTOM	ER DRAWING	MOD N°		
ite Poconta					
	e Receptacle 8D series				
ar		8 / PROJECT 859		1	
	This document is the property of SOURIAU				
	.COM it must not be reproduced or communicated without permission				
			SHEET		
M04AA-C	-	A	1/2	J	

-	Т	۵	н т	m		0	
		Contact Layout					Panel Cutout
4		x $(\begin{array}{c} \begin{array}{c} \begin{array}{c} \end{array} \\ \begin{array}{c} \end{array} \\ \end{array} \\ \begin{array}{c} \end{array} \\ \end{array} \\ \begin{array}{c} \end{array} \\ \begin{array}{c} \end{array} \\ \end{array} \\ \end{array} \\ \end{array} \\ \begin{array}{c} \end{array} \\ \end{array} $			A	SQUARE FLANGE RECEPTACLE (TYPE REAR MOUNTING	. 0)
	Controposition position A B C D Shell Arrangement N size no. 13 -4	n ID (mm) (mm) +.000 (0.00) +.150 (3.81) +.146 (3.71) +.035 (0.89) +.000 (0.00) 083 (2.11) 146 (3.71) +.035 (0.89)			₩ ₩		ØT_
ω						<u>s</u>	Dim ØA ØAA R1 ØT
	F					SOURIAU shall not due to a use of t the Specifications issu (professiona	he Products whi
N						PN:	Country FR : 8D013N
					A 15-10-20 ISS DATE Designed By:	16 First Release Latest modification - Date:	by
<u> </u>					TITLE SCALE NA		Composite General linear Tolerances: ±
					SOURIA		OURIAU.CO
					FORMAT A3		OURIAU 8D013M0
L	Н	G	F	E	D	С	

