	TT .	m	D	0			
	ØS						
	I			LAY	OUT SHOWN AS EXAMPLE		
	Keying Shown as e	example					
CHARACTERISTICS -Standard : Based on MIL-DTL-38999 Series III	F	Connector dimension Dim Nominal					
-Shell Material : Composite -Shell Plating : Olive drab Cadmium -Insulator : Thermoplastic -Contacts : Copper Alloy		ØS 25 Max Z' 31.5 Max VV THREAD M15x1-6g		due to a use the Specifications	not be liable for any non-confo of the Products which does no issued by either of the Parties onal recommendation, technic	t comply with or by a third party	
-Seals & Grommet : Silicon Elastomer -Contact Plating : Gold over copper Alloy 0.8µm minimum					Country Ju FR	risdiction & Control List Not Listed	
-Durability : 500 Mating cycles -Delivered with Souriau contacts and Accessories				F	PN: 8D511J22BA		
-Temperature Range _: -65°C to +175°C			A 15	-10-2016 First Release			
-Salt Spray : 2000 hours - Mass : 13.8 g ± 10%			ISS Designed By	DATE Latest modificatio y: Date:	n - by	CUSTOMER DRAWING	MOD N°
			тіт	LE	Composite Plug	g 8D series	
BASIC SERIES: 8D 5 - 11 J SHELL TYPE : Plug with RFI Shielding	22 B A		SCALE		General linear Tolerances: ±	NPRDS / PROJECT 859	
CONTACT TYPE : Standard Crimp Contact SHELL SIZE : 11		ORIENTATION : A CONTACT TYPE : SOCKET(500 Matings)	SOU	RIAU WWW	SOURIAU.COM	This document is the pro- SOURIAU it must not be reproduced to the second secon	uced or
PLATING : J = Olive drab Cadmium		CONTACT TYPE : SOCKET(SOU Matings)	FORMAT A3		SOURIAU DRG N	l°	SHEET 1/2
					8D511J22BA-C		1/2

		۵	гт —	m	D	0	
4		Contact Layout 22*					
	Ctc A B	4#22D 11-22 X Υ 1.905 1.905 1.905 -1.905					
ω	D	-1.905 -1.905 -1.905 1.905					
						the Specifications i	f the Products v
N						Р	Coun FR N: 8D511
					A 15-10-2 ISS DAT Designed By:	2016 First Release E Latest modification Date:	- by
_					TITLE SCALE NA		Comp General linear Tolerances: ±
					FORMAT		SOURIAU.

G

Н


F

Е

A3

D

С



ω