		т (Г		0			
HARCTERSTCS -Shell Material : Composite : Shell Material : Shell Material Material : Shell Material <							
CHARACTERISTICS -Standard : Based on MIL-DT-38999 Series III -Shell Material ::::::::::::::::::::::::::::::::::::				LATOUT	SHOWIN AS EXAMPLE		
 -Mass : 26.1 g ± 10% -Mass : 26.1 g ± 10%	 -Standard : Based on MIL-DTL-38999 Series III -Shell Material : Composite -Shell Plating : Olive drab Cadmium -Insulator : Thermoplastic -Contacts : Copper Alloy -Seals & Grommet : Silicon Elastomer -Contact Plating : Gold over copper Alloy 0.8µm minimum -Durability : 500 Mating cycles -Delivered without Souriau contacts -Temperature Range : -65°C to +175°C 	Connector dimensionDimNomirØS35.7 MZ'31.5 M	ax ax 6g	due to a use of th the Specifications issue (professional PN:	e Products which does not comp ed by either of the Parties or by a recommendation, technical notion Country Jurisdict FR N	oly with a third party ce.) ion & Control List	
BASIC SERIES: 8D 5 17 J 99 S B L SCALE SCALE Scale Scale State State <td< td=""><td></td><td></td><td></td><td></td><td></td><td></td><td>D N°</td></td<>							D N°
BASIC SERIES. ab 3 - 17 1 99 3 b 1 1 99 3 b 1			т	ITLE	Composite Plug 8D	series	
	SHELL TYPE : Plug with RFI Shielding CONTACT TYPE : Standard Crimp Contact SHELL SIZE : 17	CONTACT TYPE : SOC	red W/O Contacts NA ORIENTATION : B SOL CKET(500 Matings) Image: Contact of the second	JRIAU WWW.SO	URIAU.COM	859 This document is the property of SOURIAU it must not be reproduced or communicated without permission	n
	PLATING : J = Olive drab Cadmium	CONTA	1 LATOOT . 17-55				

r	Ŧ	ര	н г	m		0
		Contact Layout				
4	-x	$\begin{array}{c} +Y \\ R \overset{\bullet}{ } $				
	B + 131 (3.3) C + 239 (6.07) D 306 (7.75) E + 319 (8.10) F + 2.78 (7.06) G + 189 (4.80) H + 0.67 (1.70) J - 0.67 (1.70) K 189 (4.80) L 278 (7.26)	Contacts (Insert arrangement 17-99) Contact location Vaxis (mm) Contact location Vaxis (mm) Vaxis (mm) Y-axis (mm) 231 (8.15) N -336 (7.75) +099 (2.51) +233 (7.44) P -239 (6.07) +214 (5.44) x214 (8.15) N -336 (7.75) +099 (2.51) -239 (7.44) P -239 (6.07) +214 (5.44) x214 (3.56) O.70 (1.70) +177 (4.50) -034 (0.86) T +070 (1.78) +177 (4.50) -161 (4.09) U +175 (4.45) +094 (2.39) -260 (6.60) V +150 (3.81) -075 (1.91) -314 (7.96) W +1000 (0.00) +161 (4.09) -314 (7.96) X -150 (3.81) -075 (1.91) -260 (6.60) Y -175 (4.45) +094 (2.39) -161 (4.09) Z +000 (0.00) +025 (0.64) -034 (0.86) X -150 (3.81) -075 (1.91)				
ω	17 00	mber of ontacts Size contact Service rating Contact position ID Supersedes 2 16 I W, Z MS20053-99 21 20 I All others MS20053-99				
	Ļ					
						SOURIAU shall not be liable for an due to a use of the Products w the Specifications issued by either o (professional recommenda
N					[Counti FR
					A 14-10-20	PN: 8D517J
					ISS DATE Designed By:	Latest modification - by Date:
					TITLE	Compo
→					SCALE NA	General linear Tolerances:
					SOURIA	U WWW.SOURIAU.C
					FORMAT A3	SOURIAU 8D517J9
L	Н	G	F	E	D	C

