

ACMP-Q7040

Request Samples



Check Inventory (>)



7.0 x 6.0 x 3.8 mm **RoHS/RoHS II Compliant** MSL Level = 1

Features

- AEC-Q200 compliant, Grade 1
- PPAP ready and supported
- Manufactured in TS/IATF 16949 production lines
- Excellent impedance characteristics
- Rated current up to 15A
- Extremely low DCR

Applications

- DC power line common mode noise suppression.
- Multimedia devices
- Automotive power train
- Automotive infotainment

Electrical Specifications

Part Number	Impedance (Ω) @100MHz		DCR (mΩ)	Rated Current (A)	Rated Voltage (Vdc)	Insulation Resistance $(M\Omega)$	
	Min	Тур.	Max	Max	Max	Min	
ACMP-Q7040-700	40	70	5	15	80	10	
ACMP-Q7040-141	100	140	10	9	80	10	
ACMP-Q7040-301	225	300	10	5	80	10	
ACMP-Q7040-501	400	500	10	5	80	10	
ACMP-Q7040-701	500	700	15	4	80	10	
ACMP-Q7040-102	800	1020	17	3	80	10	
ACMP-Q7040-132	910	1300	20	3	80	10	

Rated Current is based on an Irms temperature rise of 40°C.

ACMP-Q7040 is AEC-Q200 Automotive certified.

ACMP-Q7040 Series is RoHS Compliant and Pb free.

Operating Temperature: -40°C to +125°C. (Including self-heating)

Storage Temperature (on PCB): -40°C to +125°C. Storage (in original packaging): <40°C, <60% RH.





ACMP-Q7040


Request Samples





Check Inventory (>)





7.0 x 6.0 x 3.8 mm **RoHS/RoHS II Compliant** MSL Level = 1



















5101 Hidden Creek Ln, Spicewood TX 78669 Phone: 512-371-6159 Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com

REVISION A 8/24/2023

ABRACON IS ISO9001-2015 CERTIFIED



ACMP-Q7040

Request Samples (>)




Check Inventory (>)




7.0 x 6.0 x 3.8 mm **RoHS/RoHS II Compliant** MSL Level = 1

Mechanical Specifications



A	В	C	D	E	F	G
7.0 ± 0.5	6.0 ± 0.5	3.8 MAX	3.5 Typ.	1.5 ± 0.5	1.5 ± 0.5	1.7 ± 0.2



Recommended Layout

Dimensions: mm





ACMP-Q7040

Request Samples (>)




Check Inventory (>)




7.0 x 6.0 x 3.8 mm **RoHS/RoHS II Compliant** MSL Level = 1

Schematic




Materials



	Description	Specification
a	Upper Plate	Plastic
b	Core	Ferrite Core
С	Wire	Enameled Copper
d	Electrode	Ag/Ni/Sn + Sn Solder
e	Marking	Laser Marking

Part Identification







ACMP-Q7040

Request Samples (>)




Check Inventory (>)



7.0 x 6.0 x 3.8 mm RoHS/RoHS II Compliant MSL Level = 1

Reflow Profile



Zone	Description	Temperature	Times		
1	Preheat	$\begin{split} T_{SMIN} \sim T_{SMAX} \\ 150^{\circ}C \sim 200^{\circ}C \end{split}$	$60 \sim 120 \text{ sec.}$		
2	Reflow	T _L 217°C	$60 \sim 150 \text{ sec.}$		
3	Peak heat	T_P $250^{\circ}C \pm 5^{\circ}C$	30 sec. MAX		





ACMP-Q7040

Request Samples (>)




Check Inventory (>)




7.0 x 6.0 x 3.8 mm **RoHS/RoHS II Compliant** MSL Level = 1


Packaging

Tape & Reel: 1500pcs/reel





Series	A	В	C	D	
ACMP-Q7040	16.0 ± 0.5	100.0 ± 2.0	13.5 ± 0.5	330	



W	P	E	F	P0	P2	Bo	Ao	Ko	t
16.0	12	1.75	7.5	4.0	2.0	7.5	6.3	3.8	0.35
± 0.30	± 0.10	± 0.05							

Dimensions: mm

ATTENTION: Abracon LLC's products are COTS - Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependent Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon LLC is required. Please contact Abracon LLC for more information.

