NOTES:

I. MATERIALS AND FINISHES: BODY - BRASS, WHITE BRONZE PLATING CONTACT - BeCu, SILVER PLATING INSULATOR - PTFE, NATURAL

2. ELECTRICAL:

A. IMPEDANCE: 50 OHM
B. FREQUENCY RANGE: DC-18 GHz
C. VSWR(RETURN LOSS): 1.15 MAX. DC-12.4 GHz

1.20 MAX. 12.4-18 GHz

D. DIELECTRIC WITHSTANDING VOLTAGE: 1000 VRMS, MIN. E. INTERMODULATION 3rd ORDER: -166 dBc @2X20W

3. MECHANICAL:

A. DURABILITY: 500 CYCLES MIN. B. TEMPERATURE RANGE: -65°C TO 165°C


4. PACKAGING:

A. QUANTITY: SINGLE PACK


B. MARKING: PACKAGING TO BE MARKED
"AMPHENOL RF, AD-NJNJ-2, DATE CODE"

THIRD ANGLE PROJ. 🕀 🖯

REVISIONS DESCRIPTION APPR DATE ECN RELEASE TO MFG. 18-Dec-19 Α 14001 CJV



SCALE 2.000



## **CUSTOMER OUTLINE DRAWING**

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

ANGLES ±1° NOTICE - These drawings, specifications, or other data (I) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. the furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE:

MATERIAL	DRAWN	DATE
SEE NOTES	WIKI	24-Dec-I9
	ENGINEER	DATE
REFERENCE	STAR	7 - Jan - 20
EAR# 9071	APPROVED	DATE
REF:	S.HSIEH	7 - Jan - 20
CONFIGURATION LEVEL: In Work	CAD FILE	
FINISH		

18 GHz T	YPE N JACK
TO JACK	LOW PIM
ADAPTER	
SCALE: 5 O.L O	CHEET 2 OF 2

ADA	PTER						
SCALE:	5.0:1.0	SHEET	2	OF	2		
	DWG SIZE	-				REV	
	R					Δ	

////pirciror iti			
	www.amphenolrf.com		
	DRAWING NO. AD-NJNJ-2		
	ITEM NO. AD-NJNJ-2		
	PART NO. AD-NJNJ-2		

Amphenal RF