

MLFB-Ordering data

6SL3210-5BB17-5UV1



Figure similar

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

Rated data		General tech. specifications	
Input		Power factor λ	0.72
Number of phases	1 AC	Offset factor $\cos \phi$	0.95
Line voltage	200 240 V -15 % +10 %	Efficiency η	0.98
Line frequency	47 63 Hz	Filter class (integrated)	Unfiltered
Output		Ambient conditions	
Number of phases	3 AC	Cooling	convection cooling
Rated voltage	230 V	Installation altitude	1000 m (3281 ft)
Rated power (HO)	0.75 kW / 1.00 hp		
Rated power (LO)	0.75 kW / 0.75 hp	Ambient temperature	
Rated current (HO)	4.20 A	Operation	-10 60 °C (14 140 °F)
Rated current (LO)	4.20 A	Storage	-40 70 °C (-40 158 °F)
		Relative humidity	
		Max. operation	95 %
Pulse frequency	8.00 kHz	Communication	
Output frequency	0 550 Hz	Communication	USS, Modbus RTU
		Standards	
		Compliance with standards	CE, cULus, C-Tick (RCM), KC
		CE marking	EN 61800-5-1 /EN 60204-1 and EN 61800-3

Overload capability

Low Overload (LO)

110 % rated output current for 60 s, cycle time 300 s

High Overload (HO)

150 % rated output current for 60 s, cycle time 300 s



MLFB-Ordering data

6SL3210-5BB17-5UV1



Figure similar

Mechanical data		Connections	
Mounting position Wall r	nounting / side-by-side mounting	Max. motor cable length	
Degree of protection IP20 /	UL open type	Shielded	25 m (82 ft)
Size FSAB	or open type	Unshielded	50 m (164 ft)
	g(1.98 lb)		
	nm (2.68 in)		
Height 142.0	mm (5.59 in)		
Depth 127.8	mm (5.03 in)		
Inputs / outputs]	
Standard digital inputs		_	
Number	4		
Digital outputs			
Number as relay changeover contact	: 1		
Number as transistor	1		
Analog inputs			
Number	2 (Can be used as additional digital input)		
Analog outputs			
Number	1		