

MLFB-Ordering data

6SL3220-3YC20-0UP0



Figure similar

Client order no. : Order no. : Offer no. : Remarks:

Item no.: Consignment no. : Project :

Rated data			General tech. specifications		
nput			Power factor λ		
Number of phases	3 AC			0.70 0.85	
		/ .10 % 20 %	Offset factor cos φ	0.96	
Line voltage	200 240 V +10 % -20 %		Efficiency η	0.96	
Line frequency	47 63 Hz		Sound pressure level (1m)	63 dB	
Rated voltage	200V IEC	240V NEC	Power loss	0.180 kW	
Rated current (LO)	16.30 A	16.30 A	Filter class (integrated)	Unfiltered	
Rated current (HO)	12.70 A	12.70 A	Titler class (integrated)	Offilitered	
utput			EMC category (with accessories)	without	
Number of phases	3 AC			Without	
Rated voltage	200V IEC 240V NEC		Ambient conditions		
nateu voitage	200V ILC	240V NLC		Class 3C2, according to IEC 60721	
Rated power (LO)	4.00 kW	5.00 hp	Standard board coating type	3: 2002	
Rated power (HO)	3.00 kW	4.00 hp			
Rated current (LO)	17.50 A	17.50 A	Cooling	Air cooling using an integrated fa	
Rated current (HO)	13.60 A	13.60 A			
Rated current (IN)	18.10 A		Cooling air requirement	0.018 m³/s (0.653 ft³/s)	
Max. output current	23.70 A		Installation altitude	1000 m (3280.84 ft)	
Pulse frequency	4 kHz		Ambient temperature		
Output frequency for vector control	0 200 Hz		Operation	-20 45 °C (-4 113 °F)	
Output frequency for vector control	0 200 HZ		Transport	-40 70 °C (-40 158 °F)	
Output frequency for V/f control	0 550 Hz		Storage	-25 55 °C (-13 131 °F)	
			Relative humidity	23 33 ((13 131 1)	
			nerative numbers		
			Max. operation	95 % At 40 °C (104 °F), condensa and icing not permissible	

Page 1 of 3

Overload capability

Low Overload (LO)

110% base load current IL for 60 s in a 300 s cycle time

High Overload (HO)

150% x base load current IH for 60 s within a 600 s cycle time



MLFB-Ordering data

6SL3220-3YC20-0UP0



	_	1		Figure simila
Mechanical data		Closed-loop control techniques		
Degree of protection	IP20 / UL open type	V/f linear / square-law / parameter	izable Yes	
Size	FSB			
Net weight	6 kg (12.79 lb)	V/f with flux current control (FCC)		
Width	100 mm (3.94 in)	V/f ECO linear / square-law	Yes	
Height	275 mm (10.83 in)	Sensorless vector control Vector control, with sensor	Yes	
Depth	218 mm (8.58 in)			
Inputs / out	puts	Encoderless torque control	Yes	
Standard digital inputs		Torque control, with encoder	No	
Number	6	C		
Switching level: 0→1	11 V	Communication		
Switching level: 1→0	5 V	Communication	PROFIBUS DP	
Max. inrush current	15 mA	Connections		
Fail-safe digital inputs		Signal cable		
Number	1	Conductor cross-section	0.15 1.50 mm ² (AWG 24 AWG 16)	
Digital outputs		Line side		
Number as relay changeover contact	2	Version	screw-type terminal	
Output (resistive load) DC 30 V, 5.0 A		Conductor cross-section	1.50 6.00 mm ² (AWG 16 AWG 10)	
Number as transistor	0	Motor end		
Analog / digital inputs		Version	Screw-type terminals	
Number	2 (Differential input)	Conductor cross-section	1.50 6.00 mm ² (AWG 16 AWG 10)	
Resolution	10 bit	DC link (for braking resistor)		
Switching threshold as digital inp	out	PE connection	On housing with M4 sc	rew
0→1	4 V	Max. motor cable length	J	
1→0	1.6 V	Shielded	150 m (492.13 ft)	
Analog outputs		Unshielded	300 m (984.25 ft)	
Number	1 (Non-isolated output)			
PTC/ KTY interface				

1 motor temperature sensor input, sensors that can be connected: PTC, KTY and Thermo-Click, accuracy $\pm 5~^{\circ}\text{C}$



MLFB-Ordering data

6SL3220-3YC20-0UP0

90%



Figure similar

	Converter lo	sses to EN 505	598-2*	
Efficier	ncy class		IE2	
	rison with the reference	converter (90% /	-49.58 %	Con
100%)			49.50 %	
1	162.5 W (2.23 %)	. 184.9 W (2.54 %)	216.8 W (2.98 %)	CE i
100% →		•	رة مراكب المراكب المرا	
	110.8 W (1.52 %)	121.1 W (1.66 %)	134.2 W (1.84 %)	
50% →	110.0 W (1.32 %)	(1.50 %)	134.2 W (1.54 /6)	
	90.7 W (1.25 %)	96 W (1.31 %)		

Standards

Compliance with standards UL, cUL, CE, C-Tick (RCM), EAC, KCC, SEMI F47, REACH

E marking EMC Directive 2004/108/EC, Low-Voltage Directive 2006/95/EC

The percentage values show the losses in relation to the rated apparent power of the converter.

50%

The diagram shows the losses for the points (as per standard EN 50598) of the relative torque generating current (I) over the relative motor stator frequency(f). The values are valid for the basic version of the converter without options/components.

Operator panel: Intelligent Operator Panel (IOP-2)

S	Screen	Ambie	ent conditions
Display design	LCD colors	Ambient temperature during	
		Operation	0 50 °C (32 122 °F)
Screen resolution	320 x 240 Pixel		55 °C only with door mounting kit
Mech	anical data	Storage	-40 70 °C (-40 158 °F)
Degree of protection	IP55 / UL type 12	Transport	-40 70 °C (-40 158 °F)
Net weight	0.13 kg (0.30 lb)	Relative humidity at 25°C di	uring
Width	70.0 mm (2.76 in)	Max. operation	95 %
Height	106.85 mm (4.21 in)		
Depth	19.65 mm (0.77 in)	P	Approvals
T.		Certificate of suitability	CE, cULus, EAC, KCC, RCM

^{*}converted values