

1

2



3

4



5

6

7



0,6
N x 7,5
0,6



P.C.B LAYOUT

Material

1. Terminal body (metal housing): Brass(CuZn)
 2. Terminal screw: Steel Zinc plating"-*slot type
 3. Contacts: Brass
 4. Surface of solder tail: Tin plated
 5. Insulator (housing): Thermoplastic (UL94V-0)
- Electrical
1. Voltage rating: 300VAC
 2. Current rating: 20A
 3. Solid wire(AWG): 12-30
 4. Stranded wire(AWG): 12-30
 5. Torque: 3.5 Lb-In
 6. Screw: M3
 7. Wire strip length: 6-7mm
 8. Withstanding Voltage: 1.6KV
 9. Operating temperature: -30°C to +105°C
 10. Soldering temperature: 250°C ± 10°C/5 Sec
 11. Safety Approval: us

N = NUMBER OF CONTACTS

RoHS compliant



File No.: E349947

Scale	1:1								
TOLERANCE									
X.	±0.50	Drawn	Date	27.05.2009	Dean	Winnie			
X.X	±0.30	Approved	19.04.2016	Winnie					
X.XX	±0.10								
DIM	TOL	② Add the UL File No.		19.04.2016	Winnie				
X.°	±1°	① Drawn		27.05.2009	Dean				
X.X°	±X°	Id.		Modification					
Angle	TOL								

Customer-No.

ASSMANN WSW-No.
A-TB750-VJXXH

Drawing-No.

ASS 3523 CO rev02

Replace

Sheet

1

2

3

4

5

6

7

SV1501