



LOC	DIST	REVISIONS					
—	—	P	LTR	DESCRIPTION	DATE	DWN	APVD
			5	CAD-NEUERSTELLUNG, WAR AUF 826 545-550 C-FORMAT FORM-UND LAGETOLERANZ KORRIGIERT	11.05.90	A.HO	—
			6	REV PER ECO-10-000443	16.01.10	KK	AEG
			7	ECR-10-025774	21JAN11	KK	HMR

POLZ.	L±0.3	BESTELL-NR.	
1	3.3	826 576 -1	△3
2	7.3		-2
3	11.3		-3
4	15.2		-4
5	19.2		-5
6	23.1		-6
7	27.1		-7
8	31.1		-8
9	35.1		-9
10	39.0	1-	-0
11	43.0	1-	-1
12	46.9	1-	-2
13	50.9	1-	-3
14	54.8	1-	-4
15	58.8	1-	-5
16	62.8	1-	-6
17	66.7	1-	-7
18	70.7	1-	-8
19	74.7	1-	-9
20	78.6	2-	-0
21	82.6	2-	-1
22	86.5	2-	-2
23	90.5	2-	-3
24	94.4	2-	-4
25	98.4	2-	-5
26	102.4	2-	-6
27	106.3	2-	-7
28	110.3	2-	-8
29	114.2	2-	-9
30	118.2	3-	-0
31	122.2	3-	-1
32	126.1	3-	-2
33	130.1	3-	-3
34	134.0	3-	-4
35	138.0	3-	-5
36	141.6	3- 826 576 -6	

ZEICHNUNG GÜLTIG AB 20/90



- △1 2.5 μm-5 μm ZINN ÜBER 1.27 μm NICKEL
- △2 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- △3 OBSOLETE

KONTAKTSTIFT	Cu Zn	△1
STIFTGEHÄUSE	PBTP GV	GRÜN
BENENNUNG	WERKSTOFF	OBERFLÄCHE FARBE

THIS DRAWING IS UNPUBLISHED. ALL RIGHTS RESERVED. RELEASED FOR PUBLICATION BY - COPYRIGHT -

DIMENSIONS: mm	DWN HIRT 02.11.78	MATERIAL	FINISH
TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.2mm	CHK HÖWEL 09.02.79	TE Connectivity	
0 PLC ± -	APVD -		
1 PLC ± -	PRODUCT SPEC	NAME	
2 PLC ± -		AMPMODU I STIFTL. RASTER 3.96 EINREIHIG	
3 PLC ± -	APPLICATION SPEC	SIZE	CAGE CODE
4 PLC ± -		A4	00779
ANGLES ± -	WEIGHT	DRAWING NO	
		C-826576	
	CUSTOMER DRAWING	SCALE	SHEET
		4:1	1 OF 1
			REV 7