

## **Data sheet for SINAMICS G120X**

Article No.: 6SL3220-2YH20-0UP0

Client order no. : Order no. : Offer no. : Remarks :

Rated data Input 3 АС Number of phases 500 ... 690 V +10 % -20 % Line voltage 47 ... 63 Hz Line frequency Rated voltage 690V IEC 600V NEC Rated current (LO) 6.00 A 6.00 A 5.20 A 5.20 A Rated current (HO) Output Number of phases 3 AC Rated voltage 690V IEC 600V NEC 1) Rated power (LO) 4.00 kW 5.00 hp Rated power (HO) 3.00 kW 4.00 hp Rated current (LO) 6.30 A 6.30 A 5.00 A Rated current (HO) 5.00 A Rated current (IN) 7.00 A Max. output current 9.00 A Pulse frequency 2 kHz Output frequency for vector control 0 ... 200 Hz Output frequency for V/f control 0 ... 550 Hz

### Overload capability

Low Overload (LO)

110% base load current IL for 60 s in a 300 s cycle time

High Overload (HO)

Communication

150% x base load current IH for 60 s within a 600 s cycle time

General tech. specifications		
Power factor λ	0.90 0.95	
Offset factor $\cos\phi$	0.99	
Efficiency η	0.97	
Sound pressure level (1m)	70 dB	
Power loss 3)	0.191 kW	
Filter class (integrated)	Unfiltered	
EMC category (with accessories) without		
Safety function "Safe Torque Off"	without SIRIUS device (e.g. via S7- 1500F)	
Communication		

Error: No CAD-Data available for this configuration.

Figure similar

Item no. : Consignment no. : Project :

Inputs / outputs	
Standard digital inputs	
Number	6
Switching level: $0 \rightarrow 1$	11 V
Switching level: $1 \rightarrow 0$	5 V
Max. inrush current	15 mA
Fail-safe digital inputs	
Number	1
Digital outputs	
Number as relay changeover contact	2
Output (resistive load)	DC 30 V, 5.0 A
Number as transistor	0
Analog / digital inputs	
Number	2 (Differential input)
Resolution	10 bit
Switching threshold as digital input	
0 → 1	4 V
1 → 0	1.6 V
Analog outputs	
Number	1 (Non-isolated output)
DTC/VTV intenfere	

#### PTC/ KTY interface

1 motor temperature sensor input, sensors that can be connected PTC, KTY and Thermo-Click, accuracy  $\pm 5\,^{\circ}\text{C}$ 

Closed-loop control techniques	
V/f linear / square-law / parameterizable	Yes
V/f with flux current control (FCC)	Yes
V/f ECO linear / square-law	Yes
Sensorless vector control	Yes
Vector control, with sensor	No
Encoderless torque control	No
Torque control, with encoder	No

PROFIBUS DP




# **Data sheet for SINAMICS G120X**

Article No.: 6SL3220-2YH20-0UP0

Ambie	ent conditions
Standard board coating type	Class 3C2, according to IEC 60721-3-3: 2002
Cooling	Air cooling using an integrated fan
Cooling air requirement	0.055 m³/s (1.942 ft³/s)
Installation altitude	1,000 m (3,280.84 ft)
Ambient temperature	
Operation	-20 45 °C (-4 113 °F)
Transport	-40 70 °C (-40 158 °F)
Storage	-25 55 °C (-13 131 °F)
Relative humidity	
Max. operation	95 % At 40 °C (104 °F), condensation and icing not permissible
Co	onnections
Signal cable	
Conductor cross-section	0.15 1.50 mm² (AWG 24 AWG 16)
Line side	
Version	screw-type terminal
Conductor cross-section	10.00 35.00 mm <sup>2</sup> (AWG 8 AWG 2)
Motor end	
Version	Screw-type terminals
Conductor cross-section	10.00 35.00 mm <sup>2</sup> (AWG 8 AWG 2)
DC link (for braking resistor)	
PE connection	Screw-type terminals
Max. motor cable length	
Shielded	200 m (656.17 ft)
Unshielded	300 m (984.25 ft)

Mechanical data		
Degree of protection	IP20 / UL open type	
Frame size	FSD	
Net weight	16.6 kg (36.60 lb)	
Dimensions		
Width	200 mm (7.87 in)	
Height	472 mm (18.58 in)	
Depth	248 mm (9.76 in)	
Standards		
Compliance with standards	UL, cUL, CE, C-Tick (RCM), EAC, KCC, SEMI F47, REACH	
CE marking	EMC Directive 2004/108/EC, Low- Voltage Directive 2006/95/EC	





The percentage values show the losses in relation to the rated apparent power of the converter.

The diagram shows the losses for the points (as per standard IEC61800-9-2) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter without options/components.

\*converted values

<sup>1)</sup> The output current and HP ratings are valid for the voltage range 550V-600V

<sup>&</sup>lt;sup>3)</sup>Typical value. More information can be found in the element group "Converter losses to IEC 61800-9-2" in this datasheet.



# **Data sheet for SINAMICS G120X**

Article No.: 6SL3220-2YH20-0UP0

	Operator pane	el: Basic Operator Panel (BOP-2)
	Screen	
Display design	LCD, monochrome	Ambient temperature
	Mechanical data	Operation
	wechanical data	Storage
Degree of protection	IP55 / UL type 12	Transport
Net weight	0.140 kg (0.31 lb)	Hallsport
Dimensions		Relative humidity at 25
Width	70.00 mm (2.76 in)	Max. operation
Height	106.85 mm (4.21 in)	
Depth	19.60 mm (0.77 in)	Certificate of suitability

	<u> </u>	
Ambient conditions		
Ambient temperature		
Operation	0 50 °C (32 122 °F)	
Storage	-40 70 °C (-40 158 °F)	
Transport	-40 70 °C (-40 158 °F)	
Relative humidity at 25°C during		
Max. operation	95 %	
Approvals		
Certificate of suitability	CE, cULus, EAC, KCC, RCM	