


## **Data sheet for SINAMICS G120X**

Article No.: 6SL3230-2YC34-0UF0

Client order no. : Order no. : Offer no. : Remarks :



Low Overload (LO)

110% base load current IL for 60 s in a 300 s cycle time

High Overload (HO)

Communication

150% x base load current IH for 60 s within a 600 s cycle time

General tech. specifications	
Power factor λ	0.90 0.95
Offset factor $\cos\phi$	0.99
Efficiency η	0.96
Sound pressure level (1m)	70 dB
Power loss 3)	1.310 kW
Filter class (integrated)	Unfiltered
EMC category (with accessories)	without
Safety function "Safe Torque Off"	without

Communication

Item no. :
Consignment no. :
Project :



Figure simila

Inputs / outputs	
Standard digital inputs	
Number	6
Switching level: $0 \rightarrow 1$	11 V
Switching level: $1 \rightarrow 0$	5 V
Max. inrush current	15 mA
Fail-safe digital inputs	
Number	1
Digital outputs	
Number as relay changeover contact	2
Output (resistive load)	DC 30 V, 5.0 A
Number as transistor	0
Analog / digital inputs	
Number	2 (Differential input)
Resolution	10 bit
Switching threshold as digital input	
0 → 1	4 V
1 → 0	1.6 V
Analog outputs	
Number	1 (Non-isolated output)

## PTC/ KTY interface

1 motor temperature sensor input, sensors that can be connected PTC, KTY and Thermo-Click, accuracy  $\pm 5\,^{\circ}\text{C}$ 

Closed-loop control techniques		
V/f linear / square-law / parameterizable	Yes	
V/f with flux current control (FCC)	Yes	
V/f ECO linear / square-law	Yes	
Sensorless vector control	Yes	
Vector control, with sensor	No	
Encoderless torque control	No	
Torque control, with encoder	No	

PROFINET, EtherNet/IP




## **Data sheet for SINAMICS G120X**

Article No.: 6SL3230-2YC34-0UF0

Ambient conditions	
Standard board coating type	Class 3C3, according to IEC 60721-3-3: 2002
Cooling	Air cooling using an integrated fan
Cooling air requirement	0.083 m³/s (2.931 ft³/s)
Installation altitude	1,000 m (3,280.84 ft)
Ambient temperature	
Operation	-20 45 °C (-4 113 °F)
Transport	-40 70 °C (-40 158 °F)
Storage	-25 55 °C (-13 131 °F)
Relative humidity	
Max. operation	95 % At 40 °C (104 °F), condensation and icing not permissible
Conn	ections
Signal cable	
Conductor cross-section	0.15 1.50 mm <sup>2</sup> (AWG 24 AWG 16)
Line side	
Version	screw-type terminal
Conductor cross-section	25.00 70.00 mm <sup>2</sup> (AWG 6 AWG 3/0)
Motor end	
Version	Screw-type terminals
Conductor cross-section	25.00 70.00 mm <sup>2</sup> (AWG 6 AWG 3/0)
DC link (for braking resistor)	
PE connection	Screw-type terminals
Max. motor cable length	
Shielded	200 m (656.17 ft)
Unshielded	300 m (984.25 ft)

Mechanical data		
Degree of protection	IP20 / UL open type	
Frame size	FSE	
Net weight	16.6 kg (36.60 lb)	
Dimensions		
Width	275 mm (10.83 in)	
Height	551 mm (21.69 in)	
Depth	248 mm (9.76 in)	
S	tandards	
Compliance with standards	UL, cUL, CE, C-Tick (RCM), EAC, KCC, SEMI F47, REACH	
CE marking	EMC Directive 2004/108/EC, Low- Voltage Directive 2006/95/EC	

Converter losses to IEC61800-9-2*	
Efficiency class	IE2
Comparison with the reference converter (90% / 100%)	63.3 %



The percentage values show the losses in relation to the rated apparent power of the converter.

The diagram shows the losses for the points (as per standard IEC61800-9-2) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter without options/components.

\*converted values

 $<sup>^{1)}</sup>$ The output current and HP ratings are valid for the voltage range 220V-240V

<sup>&</sup>lt;sup>3)</sup> Typical value. More information can be found in the element group "Converter losses to IEC 61800-9-2" in this datasheet.



## **Data sheet for SINAMICS G120X**

Article No.: 6SL3230-2YC34-0UF0

	Operator pane	el: Basic Operator Panel (BOP-2)
	Screen	
Display design	LCD, monochrome	Ambient temperature
	Mechanical data	Operation
Degree of protection	IP55 / UL type 12	Storage
Net weight	0.140 kg (0.31 lb)	Transport
Dimensions		Relative humidity at 25  Max. operation
Width	70.00 mm (2.76 in)	Max. Operation
Height	106.85 mm (4.21 in)	
Depth	19.60 mm (0.77 in)	Certificate of suitability

Ambient conditions  Ambient temperature		
Storage	-40 70 °C (-40 158 °F)	
Transport	-40 70 °C (-40 158 °F)	
Relative humidity at 25°C durir	ng	
Max. operation	95 %	
	Approvals	
Certificate of suitability	CE, cULus, EAC, KCC, RCM	