

T90 Series, 30A PCB Relay

- 30A, 1 Form A (NO); 20A, 1 Form C (CO)
- Available as open frame or sealed construction
- Meets UL 508 and 873 Spacing 3.18 through air, 6.36 over surface
- UL class F insulation system standard

Typical applications HVAC, Appliances, Industrial Controls









Approvals
UL E22575; CSA LR15734
Technical data of approved types on request

Contact Data	
Contact arrangement	1 form A (NO), 1 form B (NC), 1 form C (CO)
Rated voltage	277VAC
Max. switching voltage	277VAC
Rated current	30A
Limiting continuous current	30A
Limiting making current	30A
Limiting breaking current	30A
Contact material	AgCdO
Min. recommended contact load	1A, 5VDC or 12VAC
Initial contact resistance	75 mΩ at 1A at 5VDC or 12VAC
Frequency of operation, with load	d 360hr
Operate/release time max., inclu	ding bounce 15/15ms

_		
Contact	rating	S

Type Load Cycles Typical AgCdO, open style relay NO 30A, 240VAC, general purpose 100x10³ NO 20A, 240VAC, resistive heater 100x10³ CO 20A/10A, 240VAC, general purpose 100x10³ CO 20A/10A, 28VDC, resistive 100x10³ UL 508/873 AgCdO
AgCdO, open style relay 100x10³ NO 30A, 240VAC, general purpose 100x10³ NO 20A, 240VAC, resistive heater 100x10³ CO 20A/10A, 240VAC, general purpose 100x10³ CO 20A/10A, 28VDC, resistive 100x10³ UL 508/873
NO 30A, 240VAC, general purpose 100x10³ NO 20A, 240VAC, resistive heater 100x10³ CO 20A/10A, 240VAC, general purpose 100x10³ CO 20A/10A, 28VDC, resistive 100x10³ UL 508/873
NO 20A, 240VAC, resistive heater 100x10³ CO 20A/10A, 240VAC, general purpose 100x10³ CO 20A/10A, 28VDC, resistive 100x10³ UL 508/873 300x10²
CO 20A/10A, 240VAC, general purpose 100x10 ³ CO 20A/10A, 28VDC, resistive 100x10 ³ UL 508/873
CO 20A/10A, 28VDC, resistive 100x10 ³ UL 508/873
UL 508/873
AgCdO
NO 30A, 240VAC, general purpose 100x10 ³
NC 15A, 240VAC, general purpose 100x10 ³
CO 20A/10A, 240VAC, general purpose 100x10 ³
NO 20A, 240VAC, resistive 100x10 ³
NC 15A, 240VAC, resistive 100x10 ³
CO 20A/10A, 240VAC, resistive 100x10 ³
NO 80LRA/30FLA, 240VAC 30x10 ³
NC 30LRA/10FLA, 240VAC 30x10 ³
CO 53.6LRA/20FLA / 20LRA/6.7FLA, 240VAC 100x10 ³
NO 98LRA/22FLA, 120VAC 100x10 ³
NO 2HP, 240VAC 1x10 ³
NC 1/2HP, 240VAC 1x10 ³
NO 1HP, 120VAC 1x10 ³
NC 1/4HP, 120VAC 1x10 ³
NO 6A, 277VAC, ballast 100x10 ³
NC 3A, 277VAC, ballast 6x10 ³
NO TV5, 240VAC, tungsten 6x10 ³
NC TV3, 240VAC, tungsten 6x10 ³
NO 20A, 28VDC, resistive 100x10 ³
NC 10A, 28VDC, resistive 100x10 ³

All ratings at 25°C (unless otherwise noted) with relay properly vented. Remove vent nib from enclosed relays after soldering and cleaning for optimum life.

Mechanical endurance 10x10⁶ ops.


Coil Data		
Coil voltage range	5 to 110VDC	
Max. coil power	1.0W	
Max. coil temperature	155°C	
Coil insulation system according UL	Class F	

Coil vers	sions, DC co	il			
Coil	Rated	Operate	Release	Coil	Rated coil
code	voltage	voltage	voltage	resistance	power
	VDC	VDC	VDC	Ω±10%	wW
5	5	3.75	0.5	27	900
6	6	4.5	0.6	40	900
9	9	6.75	0.9	97	900
12	12	9	1.2	155	900
18	18	13.5	1.8	380	900
24	24	18	2.4	660	900
48	48	36	4.8	2560	900
110	110	82.5	11	13450	900

All figures are given for coil without preenergization, at ambient temperature +23°C.

Ambient temperature vs. coil voltage - 1W coil Open Style Relay, No Dust Cove

120



Data graphed above are average values and should be verified in application. Tests were conducted within a 2' (.6m) cube (still air); at nominal coil power @ 25°C; with normally open contact loaded; and with 4' (1.22m) long, #10AWG load wires. P.C. board relays were mounted to a 30A, single side P.C. board. Coil rise test conducted with a 30A PC board to maintain 20°C max. rise at 30°C. The relay connections and wiring must be designed with an adequate cross section to ensure proper current flow and heat dissipation. After cleaning process knock-off nib should be removed for optimum life of wash-tight relays.



T90 Series, 30A PCB Relay (Continued)

Insulation Data	
Initial dielectric strength	
between open contacts	1500V _{rms}
between contact and coil	1500V _{rms}
Initial insulation resistance	
between insulated elements	1x10 ⁹ Ω
Clearance/creepage	
between contact and coil	3.17mm

	Oth	er	D	ata
--	-----	----	---	-----

Material compliance: EU RoHS/ELV, China RoHS, REACH, Halogen content refer to the Product Compliance Support Center at www.te.com/customersupport/rohssupportcenter

Ambient temperature

DC coil -55°C to 85°C 1)


Category of environmental protection


IEC 61810 RT0 - open, RTII - flux proof

Other Data (continued)	
Vibration resistance (functional)	1.65mm max excursions, 10-55 Hz
Shock resistance (functional)	10g for 11msec
Shock resistance (destructive)	100g
Terminal type	pcb-tht
Weight	20g open relay
	26g wash-tight relay
Resistance to soldering heat THT	
IEC 60068-2-20	250°C
Packaging/unit	tray/50 pcs., box/500 pcs.

 Operating ambient temperature must consider "Must Operate Voltage Change Over Temperature," Contact Temperature Rise, Coil Temperature Rise (If coil is not allowed to cool) and Maximum Coil Temperature. Specification ambient considers 20A load with coil cooled to ambient.


Dimensions






Terminal assignment

Bottom view on pins



PCB layout

Bottom view on pins




Only necessary terminals are present on single throw models and terminal code 4 models. Consequently, some holes will be unnecessary for those models.

Accessory

Optional plastic dust cover is a snap-on unit, open on the PC board side of the relay. The cover, when ordered with the relay, is shipped separately. It is designed to be snapped into place by the customer after the relay has been assembled to the PC board.


Product Code	Description	Part Number
35C620A	Black dust cover, for use on T90N relay	4-1393209-2

35C620A





T90 Series, 30A PCB Relay (Continued)



Product Code	Enclosure	Contacts	Terminals	Contact Material	Coil	Part Number
T90N1D12-5	open, no cover	1 form A, 1 NO	pcb	AgCdO	5 VDC	7-1393208-4
T90N1D12-9			·	Ü	9 VDC	7-1393208-5
T90N1D12-12					12 VDC	6-1393208-5
T90N1D12-18					18 VDC	6-1393208-8
T90N1D12-24					24 VDC	7-1393208-0
T90N1D12-48					48 VDC	7-1393208-3
T90N1D12-110					110 VDC	6-1393208-4
T90N1D42-12			pcb, no extra COM		12 VDC	7-1393208-7
T90N1D42-24			. ,		24 VDC	7-1393208-9
T90N5D12-5		1 form C, 1 CO	pcb		5 VDC	9-1393208-5
T90N5D12-12		,			12 VDC	8-1393208-6
T90N5D12-18					18 VDC	9-1393208-0
T90N5D12-24					24 VDC	9-1393208-3
T90N5D12-48					48 VDC	9-1393208-4
T90N5D12-110					110 VDC	8-1393208-5
T90N5D42-12			pcb, no extra COM		12VDC	9-1393208-9
T90N5D42-24			1,		24 VDC	1393209-2
T90S1D12-5	wash tight	1 form A, 1 NO	pcb		5 VDC	1-1393209-8
T90S1D12-6		,			6 VDC	1-1393209-9
T90S1D12-9					9 VDC	2-1393209-0
T90S1D12-12					12 VDC	1-1393209-2
T90S1D12-18					18 VDC	1-1393209-3
T90S1D12-24					24 VDC	1-1393209-6
T90S1D42-12			pcb, no extra COM		12 VDC	2-1393209-2
T90S1D42-24					24 VDC	2-1393209-5
T90S1D42-48					48 VDC	2-1393209-6
T90S5D12-5		1 form C, 1 CO	pcb		5 VDC	3-1393209-4
T90S5D12-12					12 VDC	2-1393209-8
T90S5D12-18					18 VDC	3-1393209-0
T90S5D12-24					24 VDC	3-1393209-1
T90S5D12-48					48 VDC	3-1393209-3
T90S5D42-12			pcb, no extra COM		12 VDC	1423094-1
T90S5D42-18					18 VDC	3-1393209-8
T90S5D42-24					24 VDC	4-1393209-0