

Ŧ	D G	П	m	







LAYOUT SHOWN AS

Keying Shown as example

Connector dimension

Е

D

Nominal

Dim

CHARACTERISTICS

Н

ω


-Standard : Based on MIL-DTL-38999 Series III

	Standard - Based on h	The Bire sossis berres in						
\square	 -Shell Material	: Composite				Р	3.25±0.2	
ſ						PP	4.93±0.2	
	-Shell Plating	: Nickel				R1	26.97	
	-Insulator	: Thermoplastic				R2	24.61	
	-Contacts	: Copper Alloy				S	33.3±0.3	
	-Seals & Grommet	: Silicon Elastomer				V'	19.5+1.4/-0	
N						W'	2.1/3.65	
	-Contact Plating : Gold over copper Alloy 0.8μm minimum			Z' VV THREAD	32 Max			
	-Durability	: 500 Mating cycles				VVINKEAD	M25x1-6g	
	-Delivered without Sou	uriau contacts						
	_							
	-Temperature Range	-65°C to +200°C						
	-Salt Spray	: 2000 hours						
	-Mass	: 19.2 g ± 10%						
	BASIC SERIES:	8D 0 - 17 N	A 06	P	N	L		
-	SHELL TYPE : Square	Flange Receptacle					Delivered W/O	Contacts
	CONTACT TYPE : Sta	ndard Crimp Contact					ORIENTA	TION : N
	SHELL SIZE : 17					CONTACT TYPE : PIN(500 Matings)		
	PLATING : M =	Nickel		L			CONTACT LAYOU	T:17-06

F

G

SOURIAU shall not be liable for due to a use of the Products the Specifications issued by either (professional recommend



	Ξ		A				
					4		
AS EXAM	MPLE				3		
which er of the adation untry R	does not con e Parties or b , technical no	y a third part			2		
		CUSTOME	R DRAWING	MOD N°			
ite Receptacle 8D series							
ar	NPRDS / PROJECT 859						
J.COM This document is the property of SOURIAU it must not be reproduced or communicated without permission							
	RG N° PNL-C			SHEET 1/2			
	B		A		J		

