

AFBC-Q4532

Request Samples



Check Inventory (>)



4.50 x 3.20 x 1.50 mm RoHS/RoHS II Compliant MSL Level = 1

Features

- AEC-Q200 Qualified
- Operating Temperature: $-55 \sim +150$ °C
- Wide range impedance
- Monolithic inorganic material construction
- Excellent heat resistance
- Current rating up to 6A

Applications

- Electronic control Units (ECUs)
- Battery Management Systems (BMS)
- Powertrain system
- DC/AC Converters
- Industrial connectivity (IIoT)

Electrical Specifications

Part Number	Impedance	DC Resistance	Rated Current
Units	$\Omega \pm 25\%$	Ω Max.	mA Max.
Symbol	Z	R_{DC}	I_R
AFBC-Q4532-800	80	0.01	6000
AFBC-Q4532-121	120	0.02	5000
AFBC-Q4532-131	130	0.04	3000
AFBC-Q4532-151	150	0.02	5000


Test Conditions and Equipment


Impedance Test Frequency: 100MHz

I_R: Temperature Rise: 40° C Max. At Rated Current ≥ 1 A.

Operating Temperature: -55°C to +150°C (Including self-temperature rise)

Storage Temperature: <+40°C and RH 60% (Max). **AFBC-Q4532 is RoHS Compliant and Pb free**







5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com

REVISION: IR 08-10-22

ABRACON IS
ISO9001-2015
CERTIFIED



AFBC-Q4532

Request Samples (>)





Check Inventory (>)




4.50 x 3.20 x 1.50 mm **RoHS/RoHS II Compliant** MSL Level = 1

Electrical Specifications (Cont'd)





Part Number Identification







AFBC-Q4532

Request Samples (>)





Check Inventory (>)



4.50 x 3.20 x 1.50 mm **RoHS/RoHS II Compliant** MSL Level = 1

Mechanical Specifications






L	W	T	a	Н	I	J
4.50±0.20	3.20±0.20	1.50 ± 0.20	0.50 ± 0.30	3.40 Ref.	1.05 Ref.	3.30 Ref.

Dimension: mm

Materials



	Structure Description
1	Ferrite for Beads
2	Internal Terminal Electrode: Ag (100%)
3	Electro-plating: Ni (100%)
4	External Electro-plating: Sn (100%)





AFBC-Q4532

Request Samples (>)




Check Inventory (>)



4.50 x 3.20 x 1.50 mm RoHS/RoHS II Compliant MSL Level = 1

Reflow Profile



Zone	Description	Temperature	Times	
1	Preheat	$T_{SMIN} \sim T_{SMAX} \\ 150 ^{\circ}C \sim 200 ^{\circ}C$	60 ~ 180 sec.	
2	Reflow	T _L 245°C	20 ~ 40 sec.	
3	Peak heat	Т _Р 260°С	10 sec. MAX	





AFBC-Q4532

Request Samples (>)




Check Inventory (>)




4.50 x 3.20 x 1.50 mm **RoHS/RoHS II Compliant** MSL Level = 1


Packaging

T= Tape and reel (1,000 pcs/reel)





Type	A	В	С	D
7"x12mm	13.5 ± 0.5	60.0 ± 2.0	13.5 ± 0.5	178.0 ± 2.0



Series	Во	Ao	Ko	P
AFBC-Q4532	4.70 ± 0.1	3.45 ± 0.1	1.60 ± 0.1	8.00 ± 0.10

Dimension: mm

ATTENTION: Abracon LLC's products are COTS - Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependent Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon LLC is required. Please contact Abracon LLC for more information.

