				0	₿ >		
And CERTIFIES A B B C SERVES: BOD S LIDER Substance: Substance: Substance: Substance: Substance: Substance: Substance: Substance: Substance: Substance: Substance: Substance: Substance: Substance: Substance: Substance: Substance: Substance: Substance: Substance: Substance: Substan							
Source Particular is assed on MILDTU-38999 Series III Dim		Keying Shown as example		LAYOUT SHOWN AS EXAM	PLE		
-Durability :: 500 Mating cycles -Delivered with Souriau contacts and Accessories -Temperature Range :: -65°C to +200°C -Salt Spray :: 2000 hours -Mass :: 17.4 g ± 10% BASIC SERIES: 8D 5 13 M 35 A B CONTACT TYPE : Plug with RFI Shielding CONTACT TYPE :: Standard Crimp Contact SHELL SIZE :: 13 PLATING :: M = Nickel CONTACT TYPE :: Plug with RFI Shielding CONTACT TYPE :: Plug With RFI Shielding	-Standard : Based on MIL-DTL-38999 Series III -Shell Material : Composite -Shell Plating : Nickel -Insulator : Thermoplastic -Contacts : Copper Alloy -Seals & Grommet : Silicon Elastomer	DimNominalØS29.4 MaxZ'31.5 Max		due to a use of the Products which does not comply with the Specifications issued by either of the Parties or by a third party (professional recommendation, technical notice.)			
-Mass : 17.4 g ± 10% -Mass : 17.4 g ± 10% BASIC SERIES: 8D 5 13 M 35 A B SHELL TYPE : Plug with RFI Shielding CONTACT TYPE : Standard Crimp Contact SHELL SIZE : 13 PLATING : M = Nickel -Mass : 17.4 g ± 10% -Mass :	-Durability: 500 Mating cycles-Delivered with Souriau contacts and Accessories-Temperature Range: -65°C to +200°C		A 18-10-2016	PN: 8D513M35AB			
BASIC SERIES: 8D 5 - 13 M 35 A B SHELL TYPE : Plug with RFI Shielding CONTACT TYPE : Standard Crimp Contact 0RIENTATION : B SHELL SIZE : 13 CONTACT TYPE : PIN(500 Matings) PLATING : M = Nickel CONTACT TYPE : PIN(500 Matings)						MOD N°	
BASIC SERIES: 8D 5 - 13 M 35 A B SHELL SUP SUPPORT SCALE NA Scale State							
CONTACT TYPE : Standard Crimp Contact ORIENTATION : B SOURIAU This document is the property of SOURIAU.COM SHELL SIZE : 13 CONTACT TYPE : PIN(500 Matings) CONTACT LAYOUT : 13-35 FORMAT SOURIAU DRG N° SHEET		5 A B		-{			
	CONTACT TYPE : Standard Crimp Contact			SOURIAU WWW.SOURIAU.COM SOURIAU it must not be reproduced or			
	PLATING : M = Nickel	CONTACT LAYOUT	. 15-55				

F	Ŧ	G	п –	m		0	
		Contact Layout					
4	-х -	+Y +Y + 10 + 0 + 0 + 0 + 0 + 0 + 0 + 0 +					
	2 +.126 (3.20)	Contacts (Insert arrangement 13-35) ion Contact position Location Y-axis position X-axis Y-axis (mm) ID (mm) (mm) (mm) +.197 (5.00) 12 182 (4.62) +.088 (2.24) +.088 (2.24) 14 045 (1.14) +.197 (5.00) +.000 (0.00) 15 +.045 (1.14) +.197 (5.02) 088 (2.24) 16 +.117 (2.97) +.026 (0.68) 158 (4.01) 17 +.093 (2.36) 075 (1.91) .197 (5.00) 18 +.000 (0.00) 120 (3.05) .197 (5.00) 19 093 (2.36) 075 (1.91)					
ယ	9 -126 (3.20) 10 -182 (4.62) 11 -203 (5.16) (Shell Arrangement Nur size no. co	158 (4.01) 20 117 (2.97) +.026 (0.66) 088 (2.24) 21 045 (1.14) +.107 (2.72) +.000 (0.00) 22 +.000 (.00) 030 (0.76)					
						SOURIAU shall not be liable due to a use of the Produ the Specifications issued by eit (professional recomm	cts w ther c
N							Count FR
					A 18-10-20 ISS DATE Designed By:	PN: 8D5	131
					SCALE	Co General li Toleranc	
→					SOURIA		
					FORMAT A3	SOUR 8D51	
	Н	G	F	E	D	C	

