עם ד 			0			
Z'	ØS					
			LAYOUT SHO	OWN AS EXAMPLE		
	Keying Shown as example					
CHARACTERISTICS	Connector dimension					
-Standard : Based on MIL-DTL-38999 Series III	Dim Nominal ØS 32.5 Max					
-Shell Material : Composite	Z' 31.5 Max		SOURIAU shall not be liable for any non-conformity or damage			
-Shell Plating : Nickel -Insulator : Thermoplastic	VV THREAD M22x1-6g		due to a use of the Products which does not comply with the Specifications issued by either of the Parties or by a third party			
-Contacts : Copper Alloy			(professional reco	mmendation, technical notice.)		
-Seals & Grommet : Silicon Elastomer				Country Jurisdiction	& Control List	
-Contact Plating : Gold over copper Alloy 0.8µm minimum					Listed	
-Durability : 500 Mating cycles						
-Delivered without Souriau contacts			PN: 8D515M15SAL			
-Temperature Range : -65°C to +200°C			.0-2016 First Release			
-Salt Spray : 2000 hours						
Mass : 23 g ± 10%		ISS Designed By:	DATE Latest modification - by Date:	CUS	TOMER DRAWING	DD N°
		ТІТІ	TITLE Composite Plug 8D series		ries	
BASIC SERIES: 8D 5 - 15 M	I 15 S A L	SCALE	Gene	ral linear N	IPRDS / PROJECT	
SHELL TYPE : Plug with RFI Shielding		W/O Contacts NA	$ ( ( \Psi ) ) $	rances: ±	859	
					This document is the property of	
CONTACT TYPE : Standard Crimp Contact		IENTATION : A SOUR	IAU WWW.SOUF		SOURIAU it must not be reproduced or	
SHELL SIZE : 15	CONTACT TYPE : SOCKET				communicated without permission	
		AVOLIT · 15-15 FORMAT			і с <b>ц</b>	HEET
PLATING : M = Nickel	CONTACT L	AYOUT : 15-15 FORMAT A3		IRIAU DRG N° 15M15SAL-C		1/2

-	T	۵	וד	m	D	0	
		Contact Layout					
4	•	$ \begin{array}{c} \begin{array}{c} & & & \\ & & & & \\ & & & \\ & & & \\ & & & \\ & & & \\ & & & \\ & & & \\ & & & \\ & & & & \\ & & & \\ & & & \\ & & & \\ & & & & \\ & & & \\ & & & \\ & & & \\ & & & \\ & & & \\ & & & \\ & & & \\ & &$					
	· · · · · · · · · · · · · · · · · · ·	V-axis (mm)  Contract position ID (mm)  X-axis (mm)  V-axis (mm)    + 225 (5.72)  J  -244 (6.20)  +.014 (0.36)    +.140 (3.56)  K  -202 (5.13)  +.140 (3.56)   014 (0.36)  L 100 (2.54)  +.225 (5.72)   113 (2.87)  M  +.000 (0.00)  +.140 (3.56)   209 (5.31)  N  +.110 (2.79)  +.040 (1.02)   208 (5.31)  R 110 (2.79)  +.040 (1.02)   209 (5.31)  R 110 (2.79)  +.040 (1.02)   113 (2.87)					
ω	size no. con	nber of Size Service Contact Supersedes tacts contacts rating location 1 16 1 16 1 14 10 10 10 10 10 10 10 10 10 10 10 10 10					
						SOURIAU shall not be liab due to a use of the Pro	ducts w
N						the Specifications issued by (professional recor	
					A 19-10-20 ISS DATE	D16 First Release	515N
					Designed By:	Date:	Compo
					NA SOURIA		ances: :
					FORMAT A3	SOU 8D5	
L	Н	G	F	E	D	C	

