



LAYOUT SHOWN AS EXAMPLE

Keying Shown as example

CHARACTERISTICS

- Standard : Based on MIL-DTL-38999 Series III
- Shell Material : Aluminium
- Shell Plating : Olive drab Cadmium
- Insulator : Thermoplastic
- Contacts : Copper Alloy
- Seals & Grommet : Silicon Elastomer
- Contact Plating : Gold over copper Alloy 0.8µm minimum
- Durability : 500 Mating cycles
- Delivered with Souriau contacts and Accessories
- Temperature Range : -65°C to +175°C
- Salt Spray : 500 hours

| Connector dimension | |
|---------------------|----------|
| Dim | Nominal |
| ØS | 44.9 Max |
| Z | 31 Max |
| VV THREAD | M34x1-6g |

SOURIAU shall not be liable for any non-conformity or damage due to a use of the Products which does not comply with the Specifications issued by either of the Parties or by a third party (professional recommendation, technical notice.)

| Country | Jurisdiction & Control List |
|---------|-----------------------------|
| FR | Not Listed |

PN: 8D523W06BD

| | | | |
|--------------|------------|--------------------------|-------------------------|
| A | 07-10-2016 | First Release | |
| ISS | DATE | Latest modification - by | MOD N° |
| Designed By: | | Date: | CUSTOMER DRAWING |

| | | | | | | | | | |
|----------------|-------------------------|---|---|----|---|----|---|---|------------------------------------|
| BASIC SERIES: | 8D | 5 | - | 23 | W | 06 | B | D | ORIENTATION : D |
| SHELL TYPE : | Plug with RFI Shielding | | | | | | | | CONTACT TYPE : SOCKET(500 Matings) |
| CONTACT TYPE : | Standard Crimp Contact | | | | | | | | CONTACT LAYOUT : 23-06 |
| SHELL SIZE : | 23 | | | | | | | | |
| PLATING : | W = Olive drab Cadmium | | | | | | | | |

| | | | |
|----------------|--------------------------|--------------------------------|---|
| TITLE | Aluminium Plug 8D series | | |
| SCALE | NA | General linear Tolerances: ±-- | NPRDS / PROJECT 859 |
| SOURIAU | WWW.SOURIAU.COM | | This document is the property of SOURIAU it must not be reproduced or communicated without permission |
| FORMAT | A3 | | SOURIAU DRG N° 8D523W06BD-C |
| | | | SHEET 1/2 |

Contact Layout

06



6#8 Concentric
Twinax
Service M

| 23-06 | | |
|-------|-------|-------|
| Ctc | X | Y |
| A | 0 | 9.24 |
| B | 8.81 | 2.87 |
| C | 5.43 | -7.49 |
| D | -5.43 | -7.49 |
| E | -8.81 | 2.87 |
| F | 0 | 0 |

SOURIAU shall not be liable for any non-conformity or damage due to a use of the Products which does not comply with the Specifications issued by either of the Parties or by a third party (professional recommendation, technical notice.)

| Country | Jurisdiction & Control List |
|---------|-----------------------------|
| FR | Not Listed |

PN: 8D523W06BD

| | | | |
|----------------|------------------------------------|----------------------------|---|
| A | 07-10-2016 | First Release | |
| ISS | DATE | Latest modification - by | MOD N° |
| Designed By: | | Date: | CUSTOMER DRAWING |
| TITLE | Aluminium Plug 8D series | | |
| SCALE | | General linear Tolerances: | NPRDS / PROJECT |
| NA | | ±-- | 859 |
| SOURIAU | WWW.SOURIAU.COM | | This document is the property of SOURIAU it must not be reproduced or communicated without permission |
| FORMAT | SOURIAU DRG N° 8D523W06BD-C | | SHEET 2/2 |