



LAYOUT SHOWN AS EXAMPLE

Keying Shown as example

**CHARACTERISTICS**

- Standard : Based on MIL-DTL-38999 Series III
- Shell Material : Aluminium
- Shell Plating : Black Zinc Nickel
- Insulator : Thermoplastic
- Contacts : Copper Alloy
- Seals & Grommet : Silicon Elastomer
- Contact Plating : Gold over copper Alloy 0.8µm minimum
- Durability : 500 Mating cycles
- Delivered without Souriau contacts
- Temperature Range : -65°C to +175°C
- Salt Spray : 500 hours

| Connector dimension |                 |
|---------------------|-----------------|
| Dim                 | Nominal         |
| A                   | 49.2±0.3        |
| B                   | 33.32+0.1/-0.15 |
| R                   | 32.5Max         |
| S                   | 46±0.4          |
| W                   | 3+0.9/-0.1      |
| VV THREAD           | M28x1-6g        |

SOURIAU shall not be liable for any non-conformity or damage due to a use of the Products which does not comply with the Specifications issued by either of the Parties or by a third party (professional recommendation, technical notice.)


| Country | Jurisdiction & Control List |
|---------|-----------------------------|
| FR      | Not Listed                  |

**PN: 8D719Z28SNL**

|                     |                                       |                                |   |
|---------------------|---------------------------------------|--------------------------------|---|
| A                   | 30-09-2016                            | First Release                  |   |
| ISS                 | DATE                                  | Latest modification - by       | MOD N°  |
| Designed By:        |                                       | Date:                          | <b>CUSTOMER DRAWING</b>   |
| <b>TITLE</b>        | <b>Aluminium Receptacle 8D series</b> |                                |   |
| SCALE               |                                       | General linear Tolerances: ±-- | NPRDS / PROJECT<br><b>859</b>   |
| NA                  |                                       |                                | This document is the property of SOURIAU it must not be reproduced or communicated without permission |
| <b>SOURIAU</b>      | <b>WWW.SOURIAU.COM</b>                |                                |   |
| FORMAT<br><b>A3</b> | <b>SOURIAU DRG N° 8D719Z28SNL-C</b>   |                                | SHEET<br>1/2  |

|                |                        |   |   |    |   |    |   |   |   |                                    |
|----------------|------------------------|---|---|----|---|----|---|---|---|------------------------------------|
| BASIC SERIES:  | 8D                     | 7 | - | 19 | Z | 28 | S | N | L | Delivered W/O Contacts             |
| SHELL TYPE :   | Jam nut Receptacle     |   |   |    |   |    |   |   |   | ORIENTATION : N                    |
| CONTACT TYPE : | Standard Crimp Contact |   |   |    |   |    |   |   |   | CONTACT TYPE : SOCKET(500 Matings) |
| SHELL SIZE :   | 19                     |   |   |    |   |    |   |   |   | CONTACT LAYOUT : 19-28             |
| PLATING :      | Z = Black Zinc Nickel  |   |   |    |   |    |   |   |   |                                    |

Contact Layout



| Contacts<br>(Insert arrangement 19-28) |                  |             |                     |                  |             |
|--|------------------|-------------|---------------------|------------------|-------------|
| Contact position ID                    | Contact location |             | Contact position ID | Contact location |             |
|  | X-axis (mm)      | Y-axis (mm) |                     | X-axis (mm)      | Y-axis (mm) |
| A                                      | +066 (1.68)      | +353 (8.97) | R                   | -286 (7.26)      | +217 (5.51) |
| B                                      | +189 (4.80)      | +305 (7.75) | S                   | -189 (4.80)      | +305 (7.75) |
| C                                      | +286 (7.26)      | +217 (5.51) | T                   | -066 (1.68)      | +353 (8.97) |
| D                                      | +345 (8.76)      | +098 (2.49) | U                   | +000 (0.00)      | +230 (5.84) |
| E                                      | +357 (9.07)      | -033 (0.84) | V                   | +124 (3.15)      | +193 (4.90) |
| F                                      | +321 (8.15)      | -160 (4.06) | W                   | +209 (5.31)      | +095 (2.41) |
| G                                      | +242 (6.15)      | -265 (6.73) | X                   | +228 (5.79)      | -033 (0.84) |
| H                                      | +130 (3.30)      | -335 (8.51) | Y                   | +174 (4.42)      | -151 (3.84) |
| J                                      | +000 (0.00)      | -359 (9.12) | Z                   | +000 (0.00)      | -191 (4.85) |
| K                                      | -130 (3.30)      | -335 (8.51) | a                   | -174 (4.42)      | -151 (3.84) |
| L                                      | -242 (6.15)      | -265 (6.73) | b                   | -228 (5.79)      | -033 (0.84) |
| M                                      | -321 (8.15)      | -160 (4.06) | c                   | -209 (5.31)      | +095 (2.41) |
| N                                      | -357 (9.07)      | -033 (0.84) | d                   | -124 (3.15)      | +193 (4.90) |
| P                                      | -345 (8.76)      | +098 (2.49) | e                   | +000 (0.00)      | +062 (1.57) |

| Shell size | Arrangement no. | Number of contacts | Size contacts | Service rating | Contact location & Z | Supersedes |
|------------|-----------------|--------------------|---------------|----------------|----------------------|------------|
| 19         | -28             | 2                  | 16            | I              | All others           | MS20054-28 |
|            |                 | 26                 | 20            |                |                      |            |

Panel cutout

JAM NUT RECEPTACLE (TYPE 7)



| Dim | Nominal       |
|-----|---------------|
| B   | 33.91+0/-0.25 |
| ØC  | 35.18+0.25/-0 |

SOURIAU shall not be liable for any non-conformity or damage due to a use of the Products which does not comply with the Specifications issued by either of the Parties or by a third party (professional recommendation, technical notice.)

| Country | Jurisdiction & Control List |
|---------|-----------------------------|
| FR      | Not Listed                  |

PN: 8D719Z28SNL

|                |                                     |                                |  |
|----------------|-------------------------------------|--------------------------------|--|
| A              | 30-09-2016                          | First Release                  |  |
| ISS            | DATE                                | Latest modification - by       | MOD N°   |
| Designed By:   |                                     | Date:                          | <b>CUSTOMER DRAWING</b>  |
| <b>TITLE</b>   | Aluminium Receptacle 8D series      |                                |  |
| SCALE          |                                     | General linear Tolerances: ±-- | NPRDS / PROJECT<br><b>859</b>  |
| <b>SOURIAU</b> | WWW.SOURIAU.COM                     |                                | This document is the property of SOURIAU<br>it must not be reproduced or communicated without permission |
| FORMAT         | <b>SOURIAU DRG N° 8D719Z28SNL-C</b> |                                | SHEET<br>2/2   |