

Sep.1.2023 Copyright 2023 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD						
RATING	OPERATING TEMPERATURE RANGE	-55 °C TO 85 °C <sup>(1)</sup>		STORAGE TEMPERATURE RANGE	-10 °C TO 60 °C <sup>(2)</sup>	
	VOLTAGE	200 V AC		OPERATING HUMIDITY RANGE	40 % TO 80 %.	
	CURRENT	1 A		STORAGE HUMIDITY RANGE	40 % TO 70 % <sup>(2)</sup>	
SPECIFICATIONS						
ITEM	TEST METHOD			REQUIREMENTS	QT	AT
CONSTRUCTION						
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.			ACCORDING TO DRAWING.	×	×
MARKING	CONFIRMED VISUALLY.				×	×
ELECTRIC CHARACTERISTICS						
CONTACT RESISTANCE	100 mA (DC OR 1000 Hz).			15 mΩ MAX.	×	-
INSULATION RESISTANCE	500 V DC			1000 MΩ MIN.	×	-
VOLTAGE PROOF	650 V AC FOR 1 min.			NO FLASHOVER OR BREAKDOWN.	×	-
MECHANICAL CHARACTERISTICS						
CONTACT INSERTION AND EXTRACTION FORCES	□0.5±0.002mm BY STEEL GAUGE.			INSERTION FORCE: 2.45 N MAX. EXTRACTION FORCE: 0.25 N MIN.	×	-
MECHANICAL OPERATION	100 TIMES INSERTIONS AND EXTRACTIONS.			①CONTACT RESISTANCE: 20 mΩ MAX. ②NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×	-
VIBRATION	FREQUENCY 10 TO 55 Hz, AMPLITUDE : 1.5 mm, AT 2 h FOR 3 DIRECTIONS.			①NO ELECTRICAL DISCONTINUITY OF 1 μs. ②NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×	-
SHOCK	490 m/s <sup>2</sup> , DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.				×	-
ENVIRONMENTAL CHARACTERISTICS						
DAMP HEAT (STEADY STATE)	EXPOSED AT 40±2 °C, 90 ~ 95 %, 96 h.			①CONTACT RESISTANCE: 20 mΩ MAX. ②INSULATION RESISTANCE:1000 MΩ MIN.	×	-
RAPID CHANGE OF TEMPERATURE	TEMPERATURE-65→+15~+35→+125→+15~+35°C TIME 30 → 10~15 → 30 → 10~15 min. UNDER 5 CYCLES.			③NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×	-
CORROSION SALT MIST	EXPOSED IN 5 % SALT WATER SPRAY FOR 48 h.			①CONTACT RESISTANCE: 20 mΩ MAX. ②NO HEAVY CORROSION.	×	-
SULPHUR DIOXIDE	EXPOSED IN 10 PPM FOR 96 h. (TEST STANDARD: JEIDA - 39)				×	-
RESISTANCE TO SOLDERING HEAT	1) SOLDER BATH:SOLDER TEMPERATURE, 260±5 °C FOR IMMERSION,DURATION,10±1s. 2) SOLDERING IRONS : 350 °C FOR 3 s MAX.			NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS.	×	-
SOLDERABILITY	SOLDERED AT SOLDER TEMPERATURE, 245±3°C, FOR IMMERSION DURATION, 2 s.			A NEW UNIFORM COATING OF SOLDER SHALL COVER A MINIMUM OF 95 % OF THE SURFACE BEING IMMersed.	×	-
	COUNT	DESCRIPTION OF REVISIONS		DESIGNED	CHECKED	DATE
⚠						
REMARK <sup>(1)</sup> TEMPERATURE RISE INCLUDED WHEN ENERGIZED. <sup>(2)</sup> THIS STORAGE INDICATES A LONG-TERM STORAGE STATE FOR THE UNUSED PRODUCT BEFORE THE BOARD MOUNTED.				APPROVED	HS. OKAWA	06.05.20
				CHECKED	HS. OZAWA	06.05.20
				DESIGNED	KY. NAKAMURA	06.05.20
Unless otherwise specified, refer to MIL-STD-1344.				DRAWN	KY. NAKAMURA	06.05.20
Note QT:Qualification Test AT:Assurance Test X:Applicable Test				DRAWING NO.		ELG4-081233-21
<b>HRS</b>	SPECIFICATION SHEET			PART NO.	A3C-16DA-2DSA (71)	
	HIROSE ELECTRIC CO., LTD.			CODE NO.	CL621-0507-2-71	⚠