

#### Main

Range of Product	Advantys Telefast ABE7
Product or Component Type	Plug-in electromechanical relay
Control circuit type	DC
Minimum ordered quantity	Set of 4

# Complementary

Width pitch dimension	0.47 in (12 mm)	
Product Compatibility	ABE7R16T370	
[Uc] control circuit voltage	24 V	
[Ith] conventional free air thermal current	8 A	
Threshold tripping voltage	16.8 V 104 °F (40 °C)	
Drop-out voltage	3.6 V 68 °F (20 °C)	
Drop-out current	3.5 mA 68 °F (20 °C)	
Maximum power dissipation per pole	0.6 W	
Associated fuse rating	1 A, fast blow	
Maximum switching voltage	130 V DC IEC 60947-5-1 264 V AC 50/60 Hz IEC 60947-5-1	
Electrical durability	500000 Cycles 1000 mA 24 V DC-13 10 ms 500000 Cycles 1300 mA 230 V AC-15 500000 Cycles 2500 mA 230 V AC-12 500000 cycles 2500 mA 24 V DC-12	
Minimum switching current	100 mA >= 5 V	
Electrical reliability	1e-008	
Operating rate in Hz	5 Hz no load 0.5 Hz at le	
Mechanical durability	20000000 cycles	
[Uimp] rated impulse withstand voltage	2.5 kV IEC 60947-1	
Net Weight	0.04 lb(US) (0.017 kg)	

# Environment

Max immunity to microbreaks	5 ms
Dielectric strength	2000 V IEC 60947-1

# Ordering and shipping details

Category	22375 - INTERFACE MODULE(ABA,R,S)	
Discount Schedule	CP2	
GTIN	3389110720754	
Nbr. of units in pkg.	1	
Package weight(Lbs)	0.71 oz (20 g)	
Returnability	No	
Country of origin	LV	

# Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.18 in (3 cm)
Package 1 width	1.57 in (4 cm)
Package 1 Length	0.47 in (1.2 cm)
Unit Type of Package 2	CAR
Number of Units in Package 2	4
Package 2 Weight	3.07 oz (87 g)
Package 2 Height	1.34 in (3.4 cm)
Package 2 width	1.77 in (4.5 cm)
Package 2 Length	2.36 in (6 cm)
Unit Type of Package 3	S01
Number of Units in Package 3	40
Package 3 Weight	2.41 lb(US) (1.095 kg)
Package 3 Height	5.91 in (15 cm)
Package 3 width	5.91 in (15 cm)
Package 3 Length	15.75 in (40 cm)

# Offer Sustainability

WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov	
<sup>™</sup> REACh Declaration	
Pro-active compliance (Product out of EU RoHS legal scope)	
Yes	
Yes	
₫Yes	
China RoHS Declaration	
Yes	

# Contractual warranty

Warranty	18 months	


# Electrical Durability (in Millions of Operating Cycles) Conforming to IEC 60947-5-1

# DC Loads

#### DC12 curves 3,0 2,5 48V 2,0 24V 1,5 1,0 0,5 0,0 0 0,5 1,5 2,5 3 3.5 4 4,5 1<sub>(A)</sub>

DC12control of resistive loads and of solid state loads isolated by optocoupler,  $I/R \le 1$  ms.


#### DC13 curves



DC13 Switching electromagnets, L/R ≤ 2 x (Ue x Ie) in ms, Ue: rated operational voltage, Ie: rated operational current (with a protective diode on the load, DC12 curves must be used with a coefficient of 0.9 applied to the number in millions of operating cycles)


#### AC Loads

#### AC12 curves




AC12control of resistive loads and of solid state loads isolated by optocoupler,  $\cos \phi \ge 0.9$ .

#### AC14 curves



AC14control of small electromagnetic loads  $\leq$  72 VA, make:  $\cos \varphi = 0.3$ , break:  $\cos \varphi = 0.3$ .

#### AC15 curves



AC15control of electromagnetic loads > 72 VA, make:  $\cos \phi$  = 0.7, break:  $\cos \phi$  = 0.4.