
MALLORY Mallory Sonalert Products, Inc. | Part #: SCE016LD2VC2S | Sales Outline Drawing | Revision: A

Specifications:

opecinications.			
Loud	Medium	Soft	
Fast Pulse	Fast Pulse	Fast Pulse	
10	10	10	
85 to 95 dB(A) Typ.	75 to 85 dB(A) Typ.	65 to 75 dB(A) Typ.	
2000 ± 500 Hz	2000 ± 500 Hz	2000 ± 500 Hz	
TERMINALS ONLY	TERMINALS; BLUE WIRE TO (-)	TERMINALS; YELLOW WIRE TO (-)	
6 to 16 VDC			
40mA MAX			
6/6 Nylon, Color: Black			
-40° to +85° C			
-40° to +85° C			
Recommended hole size is 1.25"(31.75mm). Thread front will fit standard 30mm(1.181") hole.			
Used to attach part to panel. The max recommended torque is 10 in-lbs.			
2.1 oz (60g)			
Approved with use of ACC03.			
cUL Recognized			
Please contact factory.			
	Fast Pulse 10 85 to 95 dB(A) Typ. 2000 ± 500 Hz TERMINALS ONLY Recommended hole s	Fast Pulse 10 10 85 to 95 dB(A) Typ. 2000 ± 500 Hz TERMINALS ONLY TERMINALS ONLY 6 to 16 VI 40mA M/ 6/6 Nylon, Cold -40° to +85 Recommended hole size is 1.25"(31.75mm). Thre Used to attach part to panel. The max r 2.1 oz (60 Approved with use CUL Recogn	Fast Pulse Fast Pulse Fast Pulse 10 10 10 85 to 95 dB(A) Typ. 75 to 85 dB(A) Typ. 65 to 75 dB(A) Typ. 2000 ± 500 Hz 2000 ± 500 Hz 2000 ± 500 Hz TERMINALS; BLUE WIRE TO (-) TERMINALS; YELLOW WIRE TO (-) 40mA MAX 6/6 Nylon, Color: Black -40° to +85° C Recommended hole size is 1.25"(31.75mm). Thread front will fit standard Used to attach part to panel. The max recommended torque is 2.1 oz (60g) Approved with use of ACC03. CUL Recognized

Dimensions: Inches (mm)



ON. DO NOT OVERTIGHTEN.

QUICK CONNECT