




# Wirewound/Metal Oxide Resistors, Commercial Power, Radial Terminals



## FEATURES

- Direct mounting on printed circuit board
- Circuit board lock-in mounting tabs
- High performance for low cost
- Special inorganic potting compound and ceramic case provide high thermal conductivity in a fireproof package
- Material categorization: for definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)



**RoHS**  
COMPLIANT  
HALOGEN  
**FREE**  
**GREEN**  
(5-2008)



| STANDARD ELECTRICAL SPECIFICATIONS |   |                       |                         |                      |                       |
|------------------------------------|---|-----------------------|-------------------------|----------------------|-----------------------|
| GLOBAL MODEL (1)                   | POWER RATING<br>$P_{40\text{ }^\circ\text{C}}$<br>W | RESISTANCE RANGE      | RESISTANCE RANGE        | TOLERANCE<br>$\pm$ % | WEIGHT (typical)<br>g |
|                                    |   | $\Omega$<br>WIREWOUND | $\Omega$<br>METAL OXIDE |                      |                       |
| CPR03...xx                         | 3   | 0.1 to 100            | -                       | 5, 10                | 5.5                   |
| CPR05...xx                         | 5   | 0.1 to 100            | 110 to 33K              | 5, 10                | 6.5                   |
| CPR10...xx                         | 10  | 0.5 to 100            | 110 to 10K              | 5, 10                | 10                    |
| CPR15...xx                         | 15  | 1.0 to 100            | 110 to 10K              | 5, 10                | 20.3                  |
| CPR20...xx                         | 20  | 1.0 to 100            | 110 to 10K              | 5, 10                | 25.5                  |

### Notes


- E24 decade values are available, although others may be available upon request
- The CPR07 product series was recently terminated and is not recommended for new designs. Hence it was removed from the datasheet
- (1) The xx is for the two digit "special" number as specified in Global Part Number Information section. Standard part number without the two digit "special" is 10.5 mm length (15 mm for CPR20), 1 pin terminals

| TECHNICAL SPECIFICATIONS    |        |  |
|-----------------------------|--------|--|
| PARAMETER                   | UNIT   | CPR HIGH VOLUME RESISTOR CHARACTERISTICS               |
| Temperature Coefficient     | ppm/°C | $\pm$ 400  |
| Short Time Overload         | -      | 5 x rated power for 5 s                                |
| Maximum Working Voltage     | V      | $(P \times R)^{1/2}$                                   |
| Terminal Strength           | lb     | 10 minimum   |
| Operating Temperature Range | °C     | -65 to +275 for wirewound, -65 to +225 for metal oxide |

| GLOBAL PART NUMBER INFORMATION                  |   |   |   |   |   |                                     |   |   |                            |   |   |   |   |   |   |  |
|---|---|---|---|---|---|-------------------------------------|---|---|----------------------------|---|---|---|---|---|---|--|
| Global Part Numbering Example: CPR05100R0JE6630 |   |   |   |   |   |                                     |   |   |                            |   |   |   |   |   |   |  |
| C   | P | R | 0   | 5 | 1 | 0                                   | 0 | R | 0                          | J | E | 6   | 6 | 3 | 0 |  |
| GLOBAL MODEL                                    |   |   | VALUE   |   |   | TOLERANCE                           |   |   | PACKAGING                  |   |   | SPECIAL   |   |   |   |  |
| CPR03<br>CPR05<br>CPR10<br>CPR15<br>CPR20       |   |   | R = decimal<br>K = thousand<br>R1500 = 0.15 $\Omega$<br>1K500 = 1500 $\Omega$ |   |   | J = $\pm$ 5.0 %<br>K = $\pm$ 10.0 % |   |   | E66 = lead (Pb)-free, bulk |   |   | Blank = short, 1 pin<br>CPRxx...30 = long, 1 pin<br>CPRxx...31 = short, 2 pin<br>CPRxx...32 = long, 2 pin |   |   |   |  |

**DIMENSIONS** in inches [millimeters]

Terminal style 1 (Single Pin)



Terminal style 2 (Double Pin)

| GLOBAL MODEL | TERMINAL STYLE | DIMENSIONS in inches [millimeters] |                       |                        |                        |                        |                       |                       |                       |                       |
|--------------|----------------|------------------------------------|-----------------------|------------------------|------------------------|------------------------|-----------------------|-----------------------|-----------------------|-----------------------|
|              |                | L<br>± 0.059<br>[1.5]              | W<br>± 0.039<br>[1.0] | H1<br>± 0.039<br>[1.0] | H2<br>± 0.039<br>[1.0] | D<br>± 0.005<br>[0.13] | P<br>± 0.059<br>[1.5] | G<br>± 0.008<br>[0.2] | H<br>± 0.008<br>[0.2] | J<br>± 0.039<br>[1.0] |
| CPR03        | 1              | 0.944<br>[24]                      | 0.354<br>[9.0]        | 0.354<br>[9.0]         | 0.413<br>[10.5]        | -                      | 0.492<br>[12.5]       | 0.197<br>[5.0]        | 0.059<br>[1.5]        | 0.193<br>[4.9]        |
| CPR03...30   | 1              | 0.944<br>[24]                      | 0.354<br>[9.0]        | 0.354<br>[9.0]         | 0.984<br>[25.0]        | -                      | 0.492<br>[12.5]       | 0.287<br>[7.3]        | 0.059<br>[1.5]        | 0.193<br>[4.9]        |
| CPR03...31   | 2              | 0.944<br>[24]                      | 0.354<br>[9.0]        | 0.354<br>[9.0]         | 0.472<br>[12.0]        | 0.197<br>[5.0]         | 0.492<br>[12.5]       | 0.287<br>[7.3]        | 0.059<br>[1.5]        | 0.193<br>[4.9]        |
| CPR03...32   | 2              | 0.944<br>[24]                      | 0.354<br>[9.0]        | 0.354<br>[9.0]         | 0.984<br>[25.0]        | 0.197<br>[5.0]         | 0.492<br>[12.5]       | 0.287<br>[7.3]        | 0.059<br>[1.5]        | 0.193<br>[4.9]        |
| CPR05        | 1              | 1.10<br>[28]                       | 0.394<br>[10.0]       | 0.394<br>[10.0]        | 0.413<br>[10.5]        | -                      | 0.590<br>[15.0]       | 0.197<br>[5.0]        | 0.059<br>[1.5]        | 0.193<br>[4.9]        |
| CPR05...30   | 1              | 1.10<br>[28]                       | 0.394<br>[10.0]       | 0.394<br>[10.0]        | 0.984<br>[25.0]        | -                      | 0.590<br>[15.0]       | 0.287<br>[7.3]        | 0.059<br>[1.5]        | 0.193<br>[4.9]        |
| CPR05...31   | 2              | 1.10<br>[28]                       | 0.394<br>[10.0]       | 0.394<br>[10.0]        | 0.472<br>[12.0]        | 0.197<br>[5.0]         | 0.590<br>[15.0]       | 0.287<br>[7.3]        | 0.059<br>[1.5]        | 0.193<br>[4.9]        |
| CPR05...32   | 2              | 1.10<br>[28]                       | 0.394<br>[10.0]       | 0.394<br>[10.0]        | 0.984<br>[25.0]        | 0.197<br>[5.0]         | 0.590<br>[15.0]       | 0.287<br>[7.3]        | 0.059<br>[1.5]        | 0.193<br>[4.9]        |
| CPR10        | 1              | 1.89<br>[48]                       | 0.394<br>[10.0]       | 0.394<br>[10.0]        | 0.413<br>[10.5]        | -                      | 1.26<br>[32.0]        | 0.197<br>[5.0]        | 0.059<br>[1.5]        | 0.193<br>[4.9]        |
| CPR10...30   | 1              | 1.89<br>[48]                       | 0.394<br>[10.0]       | 0.394<br>[10.0]        | 0.984<br>[25.0]        | -                      | 1.26<br>[32.0]        | 0.287<br>[7.3]        | 0.059<br>[1.5]        | 0.193<br>[4.9]        |
| CPR10...31   | 2              | 1.89<br>[48]                       | 0.394<br>[10.0]       | 0.394<br>[10.0]        | 0.472<br>[12.0]        | 0.197<br>[5.0]         | 1.26<br>[32.0]        | 0.287<br>[7.3]        | 0.059<br>[1.5]        | 0.193<br>[4.9]        |
| CPR10...32   | 2              | 1.89<br>[48]                       | 0.394<br>[10.0]       | 0.394<br>[10.0]        | 0.984<br>[25.0]        | 0.197<br>[5.0]         | 1.26<br>[32.0]        | 0.287<br>[7.3]        | 0.059<br>[1.5]        | 0.193<br>[4.9]        |
| CPR15        | 1              | 1.89<br>[48]                       | 0.492<br>[12.5]       | 0.472<br>[12.0]        | 0.413<br>[10.5]        | -                      | 1.26<br>[32.0]        | 0.197<br>[5.0]        | 0.059<br>[1.5]        | 0.193<br>[4.9]        |
| CPR15...30   | 1              | 1.89<br>[48]                       | 0.492<br>[12.5]       | 0.472<br>[12.0]        | 0.984<br>[25.0]        | -                      | 1.26<br>[32.0]        | 0.287<br>[7.3]        | 0.059<br>[1.5]        | 0.199<br>[5.1]        |
| CPR15...32   | 2              | 1.89<br>[48]                       | 0.492<br>[12.5]       | 0.472<br>[12.0]        | 1.18<br>[30.0]         | 0.197<br>[5.0]         | 1.26<br>[32.0]        | 0.394<br>[10.0]       | 0.069<br>[1.75]       | 0.199<br>[5.1]        |
| CPR20        | 1              | 2.461<br>[62.5]                    | 0.492<br>[12.5]       | 0.492<br>[12.5]        | 0.591<br>[15.0]        | -                      | 1.65<br>[42.0]        | 0.394<br>[10.0]       | 0.106<br>[2.7]        | 0.193<br>[4.9]        |
| CPR20...30   | 1              | 2.461<br>[62.5]                    | 0.492<br>[12.5]       | 0.492<br>[12.5]        | 0.984<br>[25.0]        | -                      | 1.65<br>[42.0]        | 0.394<br>[10.0]       | 0.106<br>[2.7]        | 0.193<br>[4.9]        |
| CPR20...32   | 2              | 2.461<br>[62.5]                    | 0.492<br>[12.5]       | 0.492<br>[12.5]        | 1.18<br>[30.0]         | 0.197<br>[5.0]         | 1.65<br>[42.0]        | 0.394<br>[10.0]       | 0.069<br>[1.75]       | 0.199<br>[5.1]        |



## MATERIAL SPECIFICATIONS

### Element:

wirewound = copper-nickel alloy or nickel-chrome alloy, depending on resistance value;  
metal oxide = high temperature fired metal oxide film


**Core:** ceramic

**Body:** steatite ceramic case with cement potting compound

**Terminals:** tin plated steel

**Part Marking:** DALE, model, wattage, value, tolerance, date code

## DERATING



| PERFORMANCE                     |  |                        |
|---------------------------------|--|------------------------|
| TEST                            | CONDITIONS OF TEST   | TEST LIMITS            |
| Thermal Shock                   | -55 °C to +275 °C (+225 °C for metal oxide), 5 cycles, 30 min dwell time | ± (5.0 % + 0.05 Ω) ΔR  |
| Short Time Overload             | 5 x rated power for 5 s  | ± (4.0 % + 0.05 Ω) ΔR  |
| Dielectric Withstanding Voltage | 1000 V <sub>RMS</sub> for 1 min  | ± (2.0 % + 0.05 Ω) ΔR  |
| Low Temperature Operation       | -65 °C, full rated working voltage for 45 min                            | ± (3.0 % + 0.05 Ω) ΔR  |
| Humidity                        | 75 °C, 90 % to 100 % RH, 240 h   | ± (5.0 % + 0.05 Ω) ΔR  |
| Load Life                       | 1000 h at rated power, +40 °C, 1.5 h "ON", 0.5 h "OFF"                   | ± (10.0 % + 0.05 Ω) ΔR |
| Terminal Strength               | 5 pounds for 30 s; body twisted about axis, 3 x 360° rotations           | ± (2.0 % + 0.05 Ω) ΔR  |
| Resistance to Solder Heat       | Terminal immersed 3.5 s in molten solder at 1/8" to 3/16" from body      | ± (4.0 % + 0.05 Ω) ΔR  |



## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.