



Recommended PCB Layout  
Total tolerance:±0.05mm

Specifications:  
规格:  
Voltage rating:250V AC/DC  
额定电压: 250V AC/DC  
Current rating:5A AC/DC  
额定电流: 5A AC/DC  
Withstanding voltage:1500V AC/minute  
耐受电压: 1500V AC/分钟  
Temperature range:-40°C-+105°C  
温度范围: -40°C-+105°C  
Insulation resistance:1000MΩ min  
绝缘电阻: 1000MΩ Min  
Contact resistance:10mΩ Max  
接触电阻: 10mΩ Max

X3025 W R - XX - 9T SN  
① ② ③ ④ ⑤ ⑥

- 1.Series No
- 2.Category:W-Wafer
- 3.Welding Board Angle:R-Stright 90°
- 4.Row No.Pin No:XX-02~12P
- 5.Material:9T-PA9T UL94V-0
- 6.Plating:SN-Tin Plated over Nickel

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
2	3.00	9.65	8	21.00	27.65
3	6.00	12.65	9	24.00	30.65
4	9.00	15.65	10	27.00	33.65
5	12.00	18.65	11	30.00	36.65
6	15.00	21.65	12	33.00	39.65
7	18.00	24.65		0.00	0.00

X3025WR-XX-9TSN	PA9T	Brass	X3025HM
PART NO	Material	Material(Pin)	Suitable XKB Housing

广东星坤科技股份有限公司

日期

文件工程章

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
Δ*					ANGULAR ±5°
ΔX					L ≤ 4 ±0.2
ΔX					4 < L ≤ 16 ±0.3
					16 < L ≤ 63 ±0.4
					L > 63 ±0.5



DSND	SCALE: N/A	MODEL TYPE: 3.0mm Crimp Style Connector
DWN	VIEW:	PART NO.: X3025WR-XX-9TSN
CHKD	UNIT: mm/in	DWG NO.: X-X3025WR-XX-9TSN
APPD	SIZE: A4	WEIGHT SHEET REVISION 1/1 A0

XKB INDUSTRIAL PRECISION CO., LIMITED