TOSHIBA CMOS Linear Integrated Circuit Silicon Monolithic

# **TCR3DG** series

300 mA CMOS Low Dropout Regulator with inrush current protection circuit


### 1. Description

The TCR3DG series are CMOS general purpose single output voltage regulators with an on/off control input, featuring low dropout voltage, low output noise voltage and low inrush current.

These voltage regulators are available in fixed output voltages between 1.0 V and 4.5 V and capable of driving up to 300 mA.

They feature overcurrent protection, thermal shutdown, Inrush current reduction and Auto-discharge.

The TCR3DG series are offered in the ultra small package WCSP4E (0.645 mm x 0.645 mm; t 0.40 mm). It has a low dropout voltage of 160 mV (3.2 V output, I<sub>OUT</sub> = 300 mA) with low output noise voltage of 38  $\mu$ V<sub>rms</sub> (2.5 V output) and a load transient response of only  $\Delta$ V<sub>OUT</sub> = ±80 mV (I<sub>OUT</sub> = 1 mA⇔300 mA, C<sub>OUT</sub> = 1.0  $\mu$ F).



Weight : 0.34 mg (Typ.)

As small ceramic input and output capacitors can be used with the TCR3DG series, these devices are ideal for portable applications that require high-density board assembly such as cellular phones.

### 2. Applications

Power IC developed for portable applications, IoT equipment and wearable devices

### 3. Features

Low Dropout voltage

V<sub>DO</sub> = 160 mV (Typ.) at 3.2 V output, I<sub>OUT</sub> = 300 mA

• Low output noise voltage

 $V_{NO}$  = 38  $\mu$ V<sub>rms</sub> (Typ.) at 2.5 V output, I<sub>OUT</sub> = 10 mA, 10 Hz ≤ f ≤ 100 kHz

Fast load transient response (∠V<sub>OUT</sub> = ±80 mV (Typ.) at I<sub>OUT</sub> = 1 ⇔ 300 mA, C<sub>OUT</sub> = 1.0 μF)

- High ripple rejection ratio (70 dB (Typ.) at 2.5 V output, I<sub>OUT</sub> = 10 mA, f = 1 kHz)
- Overcurrent protection
- Thermal shutdown
- Inrush current reduction
- Auto-discharge
- Pull down connection between CONTROL and GND
- Ceramic capacitors can be used ( $C_{IN}$  = 1.0  $\mu$ F,  $C_{OUT}$  = 1.0  $\mu$ F)
- Ultra small package WCSP4E (0.645 mm x 0.645 mm ; t 0.40 mm)

Start of commercial production 2016-03

### 4. Absolute Maximum Ratings (Ta = 25°C)


Characteristics	Symbol	Rating	Unit
Input voltage	VIN	6.0	V
Control voltage	Vct	-0.3 to 6.0	V
Output voltage	Vout	-0.3 to V <sub>IN</sub> + 0.3	V
Power dissipation	PD	800 (Note1)	mW
Junction temperature	Тј	150	°C
Storage temperature range	T <sub>stg</sub>	−55 to 150	°C

Note: Using continuously under heavy loads (e.g. the application of high temperature/current/voltage and the significant change in temperature, etc.) may cause this product to decrease in the reliability significantly even if the operating conditions (i.e. operating temperature/current/voltage, etc.) are within the absolute maximum ratings and the operating ranges.

Please design the appropriate reliability upon reviewing the Toshiba Semiconductor Reliability Handbook ("Handling Precautions"/"Derating Concept and Methods") and individual reliability data (i.e. reliability test report and estimated failure rate, etc).

#### Note1: Rating at mounting on a board Board material: Glass epoxy (FR4) Board dimension: 40 mm x 40 mm (both sides of board), t = 1.6 mm Metal pattern ratio: a surface approximately 50 %, the reverse side approximately 50 % Through hole: diameter 0.5 mm x 24

### 5. Pin Assignment (top view)



	1	2
А	VIN	VOUT
В	CONTROL	GND

### 6. Operating Ranges

Characteristics	Symbol	Rating			Unit
Input voltage	VIN	V <sub>OUT</sub> + 0.1 to 5.5 V (Note 2)			V
Control voltage	V <sub>CT</sub>	0 to V <sub>IN</sub>			
Output voltage	Vout	1.0 to 4.5			V
Output current	Ιουτ	DC	300	(Note 3)	mA
Operation Temperature	T <sub>opr</sub>	-40 to 85			°C
Output Capacitance	COUT	≥ 1.0 µF			_
Input Capacitance	C <sub>IN</sub>		≥ 1.0 µF		_

Note 2: IOUT = 1 mA.

Please refer to Dropout Voltage (Page 4) and use it within Absolute Maximum Ratings Junction temperature and Operation Temperature Ranges.

Note 3: Do not operate at or near the maximum ratings of operating ranges for extended periods of time. Exposure to such conditions may adversely impact product reliability and results in failures not covered by warranty.


# 7. List of Products Number, Output voltage and Marking

Product No.	Output voltage (V)(Typ.)	Marking	Product No.	Output voltage (V)(Typ.)	Marking
TCR3DG10	1.0	E	TCR3DG285*	2.85	R
TCR3DG11*	1.1	F	TCR3DG30*	3.0	Т
TCR3DG12	1.2	Н	TCR3DG31*	3.1	U
TCR3DG13*	1.3	J	TCR3DG32	3.2	А
TCR3DG135*	1.35	К	TCR3DG33	3.3	В
TCR3DG18*	1.8	L	TCR3DG35*	3.5	V
TCR3DG25*	2.5	Р	TCR3DG36*	3.6	С
TCR3DG28*	2.8	W	TCR3DG45*	4.5	D

Please ask your local retailer about the devices with (\*) or other output voltages.

### Top Marking (top view)

Example: TCR3DG32 (3.2 V output)



### 8. Electrical Characteristics

### (Unless otherwise specified, $V_{IN} = V_{OUT} + 1 V$ , $I_{OUT} = 50 \text{ mA}$ , $C_{IN} = 1.0 \mu\text{F}$ , $C_{OUT} = 1.0 \mu\text{F}$ , $T_a = 25^{\circ}\text{C}$ )

Characteristics	Symbol	Test Condition		Min	Тур.	Max	Unit	
Output voltage accuracy	Vour	V <sub>OUT</sub> < 1.8 V		-18	—	+18	mV	
Output voltage accuracy	Vout	I <sub>OUT</sub> = 50 mA (Note 4)	1.8V ≤ V <sub>OUT</sub>	-1.0	_	+1.0	%	
Input voltage	VIN	Iout = 300 mA		1.75	_	5.5	V	
Line regulation	Reg·line			_	1	15	mV	
Load regulation	Reg·load	1 mA ≤ I <sub>OUT</sub> ≤ 300 mA			8	35	mV	
		Iout = 0 mA	Vout = 1.0 V		65	—		
Quiescent current			Vout = 1.8 V	_	65	—		
	IB		V <sub>OUT</sub> = 2.5 V	_	68	—	μA	
			V <sub>OUT</sub> = 4.5 V	_	78	125		
Stand-by current	IB (OFF)	$V_{CT} = 0 V$		_	0.1	1	μA	
Dropout voltage	V <sub>DO</sub>	I <sub>OUT</sub> = 300 mA	(Note 5)	_	195	275	mV	
Temperature coefficient	Тсуо	$-40^{\circ}C \leq T_{opr} \leq 85^{\circ}C$		_	75	_	ppm/°C	
Output noise voltage	VNO			_	38	_	μV <sub>rms</sub>	
Ripple rejection ratio	R.R.			_	70	_	dB	
Load transient response	∕∠Vout	I <sub>OUT</sub> = 1⇔300mA, C <sub>OUT</sub> = 1.0 μF		_	±80	—	mV	
Control voltage (ON)	VCT (ON)	_		1.0	_	5.5	V	
Control voltage (OFF)	VCT (OFF)			0	_	0.4	V	

Note 4: Stable state with fixed I<sub>OUT</sub> condition.

Note 5: The 2.5 V output product.


### Dropout voltage table

### (IOUT = 300 mA, CIN = 1.0 $\mu\text{F},$ COUT = 1.0 $\mu\text{F},$ Ta = 25°C)

Output voltages	Symbol	Min	Тур.	Max	Unit
1.0 V, 1.05 V		_	575	735	
1.1 V		_	535	635	
1.2 V		_	475	585	
1.3 V		_	435	535	
1.35V		_	395	515	
1.4 V		_	375	505	
1.5 V ≤ Vout < 1.8 V		_	335	435	
$1.8 V \le V_{OUT} < 2.1 V$	VDO	_	255	365	mV
2.1 V ≤ V <sub>OUT</sub> < 2.5 V		_	225	315	
$2.5 V \le V_{OUT} < 2.8 V$		_	195	275	
2.8 V ≤ V <sub>OUT</sub> < 3.2 V		_	185	235	
3.2 V		_	165	215	
3.2 V ≤ V <sub>OUT</sub> < 3.6 V		_	165	215	
$3.6 \text{ V} \leq \text{V}_{OUT} \leq 4.5 \text{ V}$		_	135	185	

# 9. Application Note





The figure above shows the Example of configuration for using a Low dropout regulator. Insert a capacitor at V<sub>OUT</sub> and V<sub>IN</sub> pins for stable input/output operation. (Ceramic capacitors can be used).

#### 9.2. Power Dissipation


Board-mounted power dissipation ratings for TCR3DG series are available in the Absolute Maximum Ratings table. Power dissipation is measured on the board condition shown below.

#### [The Board Condition]

Board material: Glass epoxy (FR4)

Board dimension: 40 mm x 40 mm (both sides of board), t = 1.6 mm

Metal pattern ratio: a surface approximately 50 %, the reverse side approximately 50 % Through hole: diameter 0.5 mm x 24



Ambient temperature Ta (°C)

### 9.3. Attention in Use

#### Output Capacitors

Ceramic capacitors can be used for these devices. However, because of the type of the capacitors, there might be unexpected thermal features. Please consider application condition for selecting capacitors. And Toshiba recommend the ESR of ceramic capacitor is under 10  $\Omega$ . For stable operation, please use over 1.0  $\mu$ F.

#### Mounting

The long distance between IC and output capacitor might affect phase compensation by impedance in wire and inductor. For stable power supply, output capacitor need to mount near IC as much as possible. Also VIN and GND pattern need to be large and make the wire impedance small as possible.

#### Power Dissipation

Please have enough design patterns for expected maximum power dissipation. And under consideration of ambient temperature, input voltage, and output current etc, we recommend proper dissipation ratings for maximum power dissipation; in general maximum dissipation rating is 70 to 80 percent.


#### • Overcurrent Protection and Thermal shutdown

Overcurrent protection and Thermal shutdown are designed in these products, but these are not designed to constantly ensure the suppression of the device within operation limits. Depending on the condition during actual usage, it could affect the electrical characteristic specification and reliability. Also note that if output pins and GND pins are not completely shorted out, these products might break down.


When using these products, please read through and understand the concept of dissipation for absolute maximum ratings from the above mention or our 'Semiconductor Reliability Handbook'. Then use these products under absolute maximum ratings in any condition. Furthermore, Toshiba recommends inserting failsafe system into the design.

# **10. Representative Typical Characteristics**


# 10.1. Output Voltage vs. Input Voltage




10.2. Output Voltage vs. Output Current







V<sub>OUT</sub> = 1.8 V



300

V<sub>OUT</sub> = 3.0 V

V<sub>IN</sub> = 4.0 V,

 $C_{IN}$  = 1  $\mu$ F,  $C_{OUT}$  = 1  $\mu$ F

200

Ιουτ

250

(mA)

3.1

3

2.9

0

50


100

Output current


150

S


Output voltage Vour










#### 10.4. Quiescent Current vs. Input voltage V<sub>OUT</sub> = 1.0 V V<sub>OUT</sub> = 1.8 V 400 200 $\overline{C_{IN}}$ = 1 µF, $C_{OUT}$ = 1 µF $C_{IN}$ = 1 $\mu$ F, $C_{OUT}$ = 1 $\mu$ F (Ph) (Ph) I<sub>OUT</sub> = 0 mA 350 I<sub>OUT</sub> = 0 mA <u>\_</u> <u>\_</u> 300 150 **Quiescent current** 250 **Quiescent current** 200 100 150 100 50 50 0 0 2 0 1 3 4 5 2 5 0 3 1 4 Input voltage VIN (V) Input voltage V<sub>IN</sub> (V) V<sub>OUT</sub> = 2.5 V V<sub>OUT</sub> = 3.0 V 400 400 $C_{IN} = 1 \ \mu F, C_{OUT} = 1 \ \mu F$ (Pu) $C_{IN} = 1 \ \mu F, C_{OUT} = 1 \ \mu F$ (MA) 350 $I_{OUT} = 0 \text{ mA}$ 350 I<sub>OUT</sub> = 0 mA Quiescent current I<sub>B</sub> Quiescent current l<sub>B</sub> 300 300 250 250 200 200 150 150 100 100 50 50 0 0 5 0 1 2 3 4 0 2 3 4 5 1 Input voltage Input voltage VIN (V) VIN (V)









# 10.6. Ripple rejection ratio vs. Frequency










V<sub>OUT</sub> = 1.8 V









### 10.8. Load Transient Response






### 2022-11-18 Rev.2.0

### 10.9. ton Response



10.10. toff Response




The above characteristics curves are presented for reference only and not guaranteed by production test, unless otherwise noted.

# Package Information

### WCSP4E


Unit : mm



Weight: 0.34 mg (typ.)

### Land pattern dimensions for reference only

Unit : mm



# **RESTRICTIONS ON PRODUCT USE**

Toshiba Corporation and its subsidiaries and affiliates are collectively referred to as "TOSHIBA". Hardware, software and systems described in this document are collectively referred to as "Product".

- TOSHIBA reserves the right to make changes to the information in this document and related Product without notice.
- This document and any information herein may not be reproduced without prior written permission from TOSHIBA. Even with TOSHIBA's written permission, reproduction is permissible only if reproduction is without alteration/omission.
- Though TOSHIBA works continually to improve Product's quality and reliability, Product can malfunction or fail. Customers are responsible for complying with safety standards and for providing adequate designs and safeguards for their hardware, software and systems which minimize risk and avoid situations in which a malfunction or failure of Product could cause loss of human life, bodily injury or damage to property, including data loss or corruption. Before customers use the Product, create designs including the Product, or incorporate the Product into their own applications, customers must also refer to and comply with (a) the latest versions of all relevant TOSHIBA information, including without limitation, this document, the specifications, the data sheets and application notes for Product and the precautions and conditions set forth in the "TOSHIBA Semiconductor Reliability Handbook" and (b) the instructions for the application with which the Product will be used with or for. Customers are solely responsible for all aspects of their own product design or applications, including but not limited to (a) determining the appropriateness of the use of this Product in such design or applications; (b) evaluating and determining the applicability of any information contained in this document, or in charts, diagrams, programs, algorithms, sample application circuits, or any other referenced documents; and (c) validating all operating parameters for such designs and applications. TOSHIBA ASSUMES NO LIABILITY FOR CUSTOMERS' PRODUCT DESIGN OR APPLICATIONS.
- PRODUCT IS NEITHER INTENDED NOR WARRANTED FOR USE IN EQUIPMENTS OR SYSTEMS THAT REQUIRE EXTRAORDINARILY HIGH LEVELS OF QUALITY AND/OR RELIABILITY, AND/OR A MALFUNCTION OR FAILURE OF WHICH MAY CAUSE LOSS OF HUMAN LIFE, BODILY INJURY, SERIOUS PROPERTY DAMAGE AND/OR SERIOUS PUBLIC IMPACT ("UNINTENDED USE"). Except for specific applications as expressly stated in this document, Unintended Use includes, without limitation, equipment used in nuclear facilities, equipment used in the aerospace industry, lifesaving and/or life supporting medical equipment, equipment used for automobiles, trains, ships and other transportation, traffic signaling equipment, equipment used to control combustions or explosions, safety devices, elevators and escalators, and devices related to power plant. IF YOU USE PRODUCT FOR UNINTENDED USE, TOSHIBA ASSUMES NO LIABILITY FOR PRODUCT. For details, please contact your TOSHIBA sales representative or contact us via our website.
- Do not disassemble, analyze, reverse-engineer, alter, modify, translate or copy Product, whether in whole or in part.
- Product shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable laws or regulations.
- The information contained herein is presented only as guidance for Product use. No responsibility is assumed by TOSHIBA for any infringement of patents or any other intellectual property rights of third parties that may result from the use of Product. No license to any intellectual property right is granted by this document, whether express or implied, by estoppel or otherwise.
- ABSENT A WRITTEN SIGNED AGREEMENT, EXCEPT AS PROVIDED IN THE RELEVANT TERMS AND CONDITIONS OF SALE FOR PRODUCT, AND TO THE MAXIMUM EXTENT ALLOWABLE BY LAW, TOSHIBA (1) ASSUMES NO LIABILITY WHATSOEVER, INCLUDING WITHOUT LIMITATION, INDIRECT, CONSEQUENTIAL, SPECIAL, OR INCIDENTAL DAMAGES OR LOSS, INCLUDING WITHOUT LIMITATION, LOSS OF PROFITS, LOSS OF OPPORTUNITIES, BUSINESS INTERRUPTION AND LOSS OF DATA, AND (2) DISCLAIMS ANY AND ALL EXPRESS OR IMPLIED WARRANTIES AND CONDITIONS RELATED TO SALE, USE OF PRODUCT, OR INFORMATION, INCLUDING WARRANTIES OR CONDITIONS OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, ACCURACY OF INFORMATION, OR NONINFRINGEMENT.
- Do not use or otherwise make available Product or related software or technology for any military purposes, including without limitation, for the design, development, use, stockpiling or manufacturing of nuclear, chemical, or biological weapons or missile technology products (mass destruction weapons). Product and related software and technology may be controlled under the applicable export laws and regulations including, without limitation, the Japanese Foreign Exchange and Foreign Trade Law and the U.S. Export Administration Regulations. Export and re-export of Product or related software or technology are strictly prohibited except in compliance with all applicable export laws and regulations.
- Please contact your TOSHIBA sales representative for details as to environmental matters such as the RoHS compatibility of Product. Please
  use Product in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including
  without limitation, the EU RoHS Directive. TOSHIBA ASSUMES NO LIABILITY FOR DAMAGES OR LOSSES OCCURRING AS A RESULT
  OF NONCOMPLIANCE WITH APPLICABLE LAWS AND REGULATIONS.

# **TOSHIBA ELECTRONIC DEVICES & STORAGE CORPORATION**

https://toshiba.semicon-storage.com/