



Wet Tantalum Capacitors Surface Mount, Molded Case



PERFORMANCE CHARACTERISTICS

Operating Temperature: -55 °C to +85 °C (to + 125 °C with voltage derating)
Capacitance Tolerance: at 120 Hz, +25 °C. ± 20 % standard. ± 10 %, ± 5 % available as special.
DC Leakage Current (DCL Max.): at +25 °C and above: Leakage current shall not exceed the values listed in the Standard Ratings Tables.
Life Test: capacitors are capable of withstanding a 2000 h life test at a temperature of +85 °C or +125 °C at the applicable rated DC working voltage.

Following life test:

1. DCL, measured at +85 °C rated voltage, shall not be in excess of the original requirement.
2. The equivalent series resistance shall not exceed 150 % of the initial requirement.
3. Change in capacitance shall not exceed 10 % from the initial measurement.

FEATURES

- Molded surface mountable design
- Terminations: standard tin/lead (SnPb), 100 % tin (RoHS compliant) available
- Industry standard ratings
- Model M35 wet tantalum electrolytic chip capacitors incorporate the advantages of all the varieties of electrolytic capacitors and eliminate most of the disadvantages. These units have a 3 V reverse voltage capability at +85 °C and a higher ripple current capability than any other electrolytic type with similar combinations of capacitance and case size.
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



RoHS* Available

Note

* This datasheet provides information about parts that are RoHS-compliant and / or parts that are non RoHS-compliant. For example, parts with lead (Pb) terminations are not RoHS-compliant. Please see the information / tables in this datasheet for details

| ORDERING INFORMATION | | | | | | | | | |
|----------------------|----------------------------------|--------------------------------------------------------------------------------------------------------------------------------|--------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------|-------------------|----------|---------------------|--|
| M35 | C | 826 | M | 125 | B | Z | S | L | |
| MODEL | CASE CODE | CAPACITANCE | CAPACITANCE TOLERANCE | DC VOLTAGE RATING AT +85 °C | TERMINATION AND PACKAGING | RELIABILITY LEVEL | TEMP. | ESR | |
| | See Ratings and Case Codes table | This is expressed in picofarads. The first two digits are the significant figures. The third is the number of zeros to follow. | K = ± 10 % M = ± 20 % | This is expressed in volts. To complete the three-digit block, zeros precede the voltage rating. A decimal point is indicated by an "R" (6R3 = 6.3 V) | A = 100 % tin (RoHS compliant), bulk B = std., tin / lead, bulk | Z = non-ER | S = std. | S = std. L = low | |


Note

- Packaging: The use of formed plastic tubes for packing bulk components is standard

| DIMENSIONS in inches [millimeters] | | | | | | |
|------------------------------------|--------------|-------------------------|---------------------------|-------------|---------------------------|-----------------------|
| | | | | | | |
| CASE CODE | L (MAX.) | W | H | P (MIN.) | T _w | T _H (MIN.) |
| C | 0.835 [21.2] | 0.315 ± 0.012 [8 ± 0.3] | 0.295 ± 0.012 [7.5 ± 0.3] | 0.118 [3.0] | 0.236 ± 0.012 [6.0 ± 0.3] | 0.075 [1.9] |



RECOMMENDED REFLOW PROFILES



| T_p Lead (Pb)-free | T_p Sn/Pb | t_p | T_L Lead (Pb)-free | T_L Sn/Pb | T_s MIN. Lead (Pb)-free | T_s MIN. Sn/Pb | T_s MAX. Lead (Pb)-free | T_s MAX. Sn/Pb | t_s Lead (Pb)-free | t_s Sn/Pb | t_L |
|-------------------------|----------------|-------|-------------------------|----------------|------------------------------|---------------------|------------------------------|---------------------|-------------------------|----------------|-------|
| 260 °C | 240 °C | 10 | 217 °C | 183 °C | 150 °C | 100 °C | 200 °C | 150 °C | 60 to 150 | 60 to 90 | 60 |

MOUNTING

Due to the size and weight of these capacitors, we recommend that a supplemental mounting restraint to be used in printed circuit board attachment in addition to the reflowed solder.

One recommendation is to use an adhesive such as defined in the J-STD-001DS.

This is the Space Application Electronic Hardware Addendum to J-STD-001 (Requirements for Solder Electrical and Electronic Assemblies).

STANDARD RATINGS

| CAPACITANCE (μ F) | CASE CODE | PART NUMBER | MAX. ESR AT +25 °C | MAX. ESR AT -55 °C | MAX. DCL (μ A) AT | | MAX. CAPACITANCE CHANGE (%) AT | | | MAX. RIPPLE 40 kHz RMS (mA) |
|-----------------------------------------------------------------|--------------|-----------------------|-----------------------|-----------------------|------------------------|-------------------|-----------------------------------|--------|---------|-----------------------------------------|
| | | | | | +25 °C | +85 °C +125 °C | -55 °C | +85 °C | +125 °C | |
| 6 V_{DC} AT +85 °C; 4 V_{DC} AT +125 °C | | | | | | | | | | |
| 30 | C | M35C306(1)006(2)ZS(3) | 4.0 | 100 | 1.0 | 2.0 | -40 | +10.5 | +12 | 820 |
| 68 | C | M35C686(1)006(2)ZS(3) | 3.2 | 60 | 1.0 | 2.0 | -40 | +14 | +16 | 960 |
| 220 | C | M35C227(1)006(2)ZS(3) | 3.0 | 36 | 2.0 | 9.0 | -64 | +13 | +16 | 1000 |
| 8 V_{DC} AT +85 °C; 5 V_{DC} AT +125 °C | | | | | | | | | | |
| 25 | C | M35C256(1)008(2)ZS(3) | 4.0 | 100 | 1.0 | 2.0 | -40 | +10.5 | +12 | 820 |
| 56 | C | M35C566(1)008(2)ZS(3) | 3.3 | 59 | 1.0 | 2.0 | -40 | +14 | +16 | 900 |
| 180 | C | M35C187(1)008(2)ZS(3) | 3.0 | 45 | 2.0 | 9.0 | -60 | +13 | +16 | 1000 |
| 10 V_{DC} AT +85 °C; 7 V_{DC} AT +125 °C | | | | | | | | | | |
| 20 | C | M35C206(1)010(2)ZS(3) | 4.0 | 120 | 1.0 | 2.0 | -32 | +10.5 | +12 | 820 |
| 47 | C | M35C476(1)010(2)ZS(3) | 3.7 | 90 | 1.0 | 2.0 | -36 | +14 | +16 | 855 |
| 120 | C | M35C127(1)010(2)ZS(3) | 3.2 | 54 | 2.0 | 6.0 | -40 | +14 | +16 | 900 |
| 150 | C | M35C157(1)010(2)ZS(3) | 3.0 | 54 | 2.0 | 9.0 | -55 | +13 | +16 | 900 |

Note

- Part number definitions:
 - Capacitance tolerance: K, M
 - Termination / packaging: (see Ordering Information)
 - Reliability level: Z = non-ER
 - Temperature: S = std
 - ESR: S = std, L = low (1/2 standard ESR value)



| STANDARD RATINGS | | | | | | | | | | | |
|-------------------------------------------------------------------|--------------|-----------------------|-----------------------|-----------------------|------------------------|-------------------|-----------------------------------|--------|---------|-----------------------------------------|--|
| CAPACITANCE (μ F) | CASE CODE | PART NUMBER | MAX. ESR AT +25 °C | MAX. ESR AT -55 °C | MAX. DCL (μ A) AT | | MAX. CAPACITANCE CHANGE (%) AT | | | MAX. RIPPLE 40 kHz RMS (mA) | |
| | | | | | +25 °C | +85 °C +125 °C | -55 °C | +85 °C | +125 °C | | |
| 15 V_{DC} AT +85 °C; 10 V_{DC} AT +125 °C | | | | | | | | | | | |
| 15 | C | M35C156(1)015(2)ZS(3) | 4.4 | 155 | 1.0 | 2.0 | -24 | +10.5 | +12 | 780 | |
| 33 | C | M35C336(1)015(2)ZS(3) | 4.0 | 90 | 1.0 | 2.0 | -28 | +14 | +16 | 820 | |
| 82 | C | M35C826(1)015(2)ZS(3) | 3.9 | 72 | 2.0 | 6.0 | -35 | +12 | +16 | 900 | |
| 100 | C | M35C107(1)015(2)ZS(3) | 3.9 | 72 | 2.0 | 9.0 | -44 | +13 | +16 | 900 | |
| 25 V_{DC} AT +85 °C; 15 V_{DC} AT +125 °C | | | | | | | | | | | |
| 10 | C | M35C106(1)025(2)ZS(3) | 5.3 | 220 | 1.0 | 2.0 | -16 | +8 | +9 | 715 | |
| 22 | C | M35C226(1)025(2)ZS(3) | 4.2 | 140 | 1.0 | 2.0 | -20 | +10.5 | +12 | 800 | |
| 56 | C | M35C566(1)025(2)ZS(5) | 4.3 | 90 | 2.0 | 6.0 | -25 | +12 | +15 | 850 | |
| 68 | C | M35C686(1)025(2)ZS(5) | 4.3 | 90 | 2.0 | 9.0 | -40 | +12 | +15 | 850 | |
| 30 V_{DC} AT +85 °C; 20 V_{DC} AT +125 °C | | | | | | | | | | | |
| 8 | C | M35C805(1)030(2)ZS(3) | 6.6 | 275 | 1.0 | 2.0 | -16 | +8 | +12 | 640 | |
| 15 | C | M35C156(1)030(2)ZS(3) | 6.2 | 175 | 1.0 | 2.0 | -20 | +10.5 | +12 | 780 | |
| 47 | C | M35C476(1)030(2)ZS(3) | 5.2 | 100 | 2.0 | 6.0 | -23 | +12 | +15 | 800 | |
| 56 | C | M35C566(1)030(2)ZS(3) | 5.2 | 100 | 2.0 | 9.0 | -38 | +12 | +15 | 800 | |
| 35 V_{DC} AT +85 °C; 22 V_{DC} AT +125 °C | | | | | | | | | | | |
| 15 | C | M35C156(1)035(2)ZS(3) | 6.2 | 175 | 0.75 | 1.5 | -20 | +10.5 | +12 | 660 | |
| 39 | C | M35C396(1)035(2)ZS(3) | 4.1 | 61 | 2.0 | 6.0 | -22 | +12 | +14 | 820 | |
| 50 V_{DC} AT +85 °C; 30 V_{DC} AT +125 °C | | | | | | | | | | | |
| 5 | C | M35C505(1)050(2)ZS(3) | 8.0 | 400 | 1.0 | 2.0 | -16 | +5 | +6 | 580 | |
| 10 | C | M35C106(1)050(2)ZS(3) | 6.4 | 250 | 1.0 | 2.0 | -24 | +8 | +9 | 715 | |
| 33 | C | M35C336(1)050(2)ZS(3) | 5.0 | 135 | 2.0 | 9.0 | -29 | +10 | +12 | 700 | |
| 60 V_{DC} AT +85 °C; 40 V_{DC} AT +125 °C | | | | | | | | | | | |
| 4 | C | M35C405(1)060(2)ZS(3) | 9.3 | 550 | 1.0 | 2.0 | -16 | +5 | +6 | 525 | |
| 8.2 | C | M35C825(1)060(2)ZS(3) | 6.6 | 275 | 1.0 | 2.0 | -24 | +8 | +9 | 625 | |
| 27 | C | M35C276(1)060(2)ZS(3) | 5.0 | 144 | 3.0 | 12 | -24 | +10 | +12 | 700 | |
| 75 V_{DC} AT +85 °C; 50 V_{DC} AT +125 °C | | | | | | | | | | | |
| 3.5 | C | M35C355(1)075(2)ZS(3) | 9.5 | 650 | 1.0 | 2.0 | -16 | +5 | +6 | 525 | |
| 6.8 | C | M35C685(1)075(2)ZS(3) | 6.8 | 300 | 1.0 | 2.0 | -20 | +8 | +9 | 610 | |
| 22 | C | M35C226(1)075(2)ZS(3) | 5.1 | 157 | 3.0 | 12 | -19 | +10 | +12 | 600 | |
| 100 V_{DC} AT +85 °C; 65 V_{DC} AT +125 °C | | | | | | | | | | | |
| 2.5 | C | M35C255(1)100(2)ZS(3) | 10.6 | 950 | 1.0 | 2.0 | -16 | +7 | +8 | 505 | |
| 4.7 | C | M35C475(1)100(2)ZS(3) | 8.5 | 500 | 1.0 | 2.0 | -16 | +7 | +8 | 565 | |
| 10 | C | M35C106(1)100(2)ZS(3) | 5.9 | 200 | 3.0 | 12 | -17 | +10 | +12 | 800 | |
| 125 V_{DC} AT +85 °C; 85 V_{DC} AT +125 °C | | | | | | | | | | | |
| 1.7 | C | M35C175(1)125(2)ZS(3) | 15.6 | 1250 | 1.0 | 2.0 | -16 | +7 | +8 | 415 | |
| 3.6 | C | M35C365(1)125(2)ZS(3) | 10.0 | 600 | 1.0 | 2.0 | -16 | +7 | +8 | 520 | |
| 6.8 | C | M35C685(1)125(2)ZS(3) | 11.7 | 300 | 3.0 | 12 | -14 | +10 | +12 | 700 | |

Note

- Part number definitions:
 - Capacitance tolerance: K, M
 - Termination / packaging: (see Ordering Information)
 - Reliability level: Z = non-ER
 - Temperature: S = std
 - ESR: S = std, L = low (1/2 standard ESR value)



PERFORMANCE CHARACTERISTICS OF M35 CAPACITORS

| ELECTRICAL CHARACTERISTICS | |
|-------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| ITEM | PERFORMANCE CHARACTERISTICS |
| Operating temperature range | - 55 °C to + 125 °C |
| Capacitor tolerance | ± 20 %, ± 10 % at 120 Hz |
| Capacitance change (maximum) | Limits per Standard Ratings table. Measured per requirements of MIL-PRF-39006. |
| ESR | |
| AC ripple current | |
| DCL (maximum leakage current) | |
| Impedance (maximum) | |
| Reverse voltage | Reverse voltage shall be in accordance with MIL-PRF-39006/22. Units are capable of withstanding 3 V in reverse at + 85 °C for 125 h. |
| Surge voltage | Surge voltage shall be in accordance with MIL-PRF-39006. The DC rated surge voltage is the maximum voltage to which the capacitors should be subjected under any conditions. This includes transients and peak ripple at the highest line voltage. The surge voltage is 115 % of rated DC working voltage. |
| Life test | The capacitors shall be capable of withstanding a 2000 h life test at 85 °C at rated voltage. |

| ENVIRONMENTAL CHARACTERISTICS | | |
|----------------------------------------|---------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| ITEM | CONDITION | COMMENTS |
| Hermeticity | MIL-PRF-39006 | The internal component has been tested to be compliant to the hermeticity requirements of MIL-PRF-39006/22. The internal component has been tested to be compliant to the moisture resistance requirements of MIL-PRF-39006/22. The internal component has been tested to be compliant to the altitude or reduced barometric pressure requirements of MIL-PRF-39006/22 (150 000 feet). |
| Moisture resistance | MIL-PRF-39006 | |
| Altitude/barometric pressure (reduced) | MIL-PRF-39006 | |

| MECHANICAL CHARACTERISTICS | | |
|----------------------------|----------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| ITEM | CONDITION | COMMENTS |
| Thermal shock | MIL-STD-202, Method 107, A | Per MIL-PRF-39006, 30 cycles |
| Shock | MIL-STD-202, Method 213 | Per MIL-PRF-39006, 500 g |
| Vibration (high frequency) | MIL-STD-202, Method 204 | Per MIL-PRF-39006, 80 g |
| Vibration (random) | MIL-STD-202, Method 214 | Per MIL-PRF-39006, 53.79 g |
| Resistance to solder heat | MIL-STD-202, Method 210 | The capacitor must withstand solder dipping of the terminals at 260 °C for 10 s. The capacitor must not be visibly damaged and the electrical characteristics must not be affected. |
| Solderability | ANSI J-STD-002 | The terminations must be solderable per the requirements of MIL-PRF-55365 para. 4.10 |
| Part markings | MIL-STD-1285 | The part marking shall include Vishay name, trademark, capacitance, voltage, date code and lot symbol. |
| Weight (typical) in g | 3.5 | |

| PAD DIMENSIONS in millimeters | | | | |
|-------------------------------|----------|----------|----------|----------|
| | | | | |
| CASE CODE | A (MIN.) | B (NOM.) | C (NOM.) | D (NOM.) |
| C | 22.7 | 14.7 | 4.0 | 6.4 |

| STANDARD PACKAGING QUANTITY | | |
|-----------------------------|-----------|-----------|
| SERIES | CASE CODE | BULK/TUBE |
| M35 | C | 10 pcs |



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.