

300V High Performance NPN Transistor



FEATURES

- Epitaxial Planar Type
- NPN Silicon Transistor
- Compliant to RoHS Directive 2011/65/EU and in accordance to WEEE 2002/96/EC
- Halogen-free according to IEC 61249-2-21

APPLICATION

- Consumer electronics
- High voltage switching
- High voltage driver

KEY PERFORMANCE PARAMETERS			
PARAMETER		VALUE	UNIT
BV _{CBO}		300	V
BV _{CEO}		300	V
I _C		500	mA
V _{CE(SAT)}	I _C =100mA, I _B =10mA	0.2	V



Notes: MSL 1 (Moisture Sensitivity Level) per J-STD-020

ABSOLUTE MAXIMUM RATINGS (T _A = 25°C unless otherwise noted)			
PARAMETER	SYMBOL	LIMIT	UNIT
Collector-Base Voltage	V _{CBO}	300	V
Collector-Emitter Voltage	V _{CEO}	300	V
Emitter-Base Voltage	V _{EBO}	5	V
Collector Current (DC)	I _C	500	mA
Collector Peak Current (Pulse) ^{Note}	I _{CM}	1	A
Base Current	I _B	200	mA
Power Total Dissipation @ T _A =25°C	P _D	0.5	W
Maximum Operating Junction Temperature	T _J	+150	°C
Storage Temperature Range	T _{STG}	-55 to +150	°C

Note: Single pulse, P_w ≤ 380μs, Duty ≤ 2%

THERMAL PERFORMANCE			
PARAMETER	SYMBOL	TYP	UNIT
Junction to Ambient Thermal Resistance	R _{θJA}	420	°C/W
Junction to Case Thermal Resistance	R _{θJC}	155	°C/W

ELECTRICAL SPECIFICATIONS ($T_A = 25^\circ\text{C}$ unless otherwise noted)						
PARAMETER	CONDITIONS	SYMBOL	MIN	TYP	MAX	UNIT
Static (Note 1)						
Collector-Base Breakdown Voltage	$I_C = 100\mu\text{A}$	BV_{CBO}	300	--	--	V
Collector-Emitter Breakdown Voltage	$I_C = 10\text{mA}$	BV_{CEO}	300	--	--	V
Emitter-Base Breakdown Voltage	$I_E = 100\mu\text{A}$	BV_{EBO}	5	--	--	V
Collector Cutoff Current	$V_{CB} = 250\text{V}$	I_{CBO}	--	--	100	nA
Collector Cutoff Current	$V_{CES} = 250\text{V}$	I_{CES}	--	--	100	nA
Emitter Cutoff Current	$V_{EB} = 4\text{V}$	I_{EBO}	--	--	100	nA
Collector-Emitter Saturation Voltage	$I_C = 100\text{mA}, I_B = 10\text{mA}$	$V_{CE(SAT)}^1$	--	--	0.2	V
	$I_C = 250\text{mA}, I_B = 25\text{mA}$	$V_{CE(SAT)}^2$	--	--	0.3	V
Base-Emitter Saturation Voltage	$I_C = 250\text{mA}, I_B = 25\text{mA}$	$V_{BE(SAT)}$	--	--	1	V
Base-Emitter Turn-on Voltage	$I_C = 250\text{mA}, V_{CE} = 10\text{V}$	$V_{BE(ON)}$	--	--	1	V
DC Current Transfer Ratio	$V_{CE} = 10\text{V}, I_C = 1\text{mA}$,	h_{FE}^1	100	--	--	
	$V_{CE} = 10\text{V}, I_C = 100\text{mA}$,	h_{FE}^2	80	--	300	
	$V_{CE} = 10\text{V}, I_C = 250\text{mA}$,	h_{FE}^3	20	--	--	
Dynamic (Note 2)						
Transition Frequency	$V_{CE} = -10\text{V}, I_C = -30\text{mA}$, $f = 100\text{MHz}$	f_T	75	--	--	MHz
Collector Output Capacitance	$V_{CB} = -10\text{V}, I_E = 0\text{A}$, $f = 100\text{MHz}$	C_{ob}	--	--	5	pF
Delay Time	$V_{CC} = 100\text{V}, I_C = 100\text{mA}$, $I_{B1} = -I_{B2} = 10\text{mA}$	t_d	--	53	--	ns
Rise Time		t_r	--	126	--	ns
Storage Time		t_s	--	2580	--	ns
Fall Time		t_f	--	228	--	ns

Note:

1. Pulse test: $\leq 380\mu\text{s}$, duty cycle $\leq 2\%$
2. For DESIGN AID ONLY, not subject to production testing

ORDERING INFORMATION

ORDERING CODE	PACKAGE	PACKING
TSC497CX RFG	SOT-23	3,000pcs / 7" Reel

ELECTRICAL CHARACTERISTICS CURVES ($T_A=25^\circ\text{C}$, unless otherwise noted)

Figure 1. $V_{CE(sat)}$ vs. Collector Current




Figure 2. DC Current Gain




Figure 3. $V_{BE(sat)}$ vs. Collector Current




Figure 4. $V_{BE(on)}$ vs. Collector Current






Figure 5. Safe Operating Area




PACKAGE OUTLINE DIMENSIONS (Unit: Millimeters)


SOT-23



SUGGESTED PAD LAYOUT (Unit: Millimeters)



MARKING DIAGRAM



- C9** = Device Code
- Y** = Year Code
- M** = Month Code for Halogen Free Product
 - O** =Jan **P** =Feb **Q** =Mar **R** =Apr
 - S** =May **T** =Jun **U** =Jul **V** =Aug
 - W** =Sep **X** =Oct **Y** =Nov **Z** =Dec
- L** = Lot Code (1~9, A~Z)

Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.