

## Small Signal Schottky Diode



### FEATURES

- For general purpose applications
- This diode features low turn-on voltage and high breakdown voltage. This device is protected by a PN junction guard ring against excessive voltage, such as electrostatic discharges
- This diode is also available in a MiniMELF case with type designation LL41
- Material categorization: for definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)



**RoHS**  
COMPLIANT  
HALOGEN  
**FREE**

### LINKS TO ADDITIONAL RESOURCES



### MECHANICAL DATA

**Case:** DO-35 (DO-204AH)

**Weight:** approx. 125 mg

**Cathode Band Color:** black

**Packaging Codes/Options:**

TR/10K per 13" reel (52 mm tape), 50K/box

TAP/10K per ammpack (52 mm tape), 50K/box

### PARTS TABLE

| PART  | ORDERING CODE         | CIRCUIT CONFIGURATION | TYPE MARKING | REMARKS               |
|-------|-----------------------|-----------------------|--------------|-----------------------|
| BAT41 | BAT41-TR or BAT41-TAP | Single                | BAT41        | Tape and reel/ammpack |

### ABSOLUTE MAXIMUM RATINGS ( $T_{amb} = 25\text{ }^{\circ}\text{C}$ , unless otherwise specified)

| PARAMETER                                      | TEST CONDITION                         | SYMBOL    | VALUE | UNIT |
|--|--|-----------|-------|------|
| Repetitive peak reverse voltage                |  | $V_{RRM}$ | 100   | V    |
| Forward continuous current <sup>(1)</sup>      |  | $I_F$     | 100   | mA   |
| Repetitive peak forward current <sup>(1)</sup> | $t_p < 1\text{ s}, \delta < 0.5$       | $I_{FRM}$ | 350   | mA   |
| Surge forward current <sup>(1)</sup>           | $t_p = 10\text{ ms}$                   | $I_{FSM}$ | 750   | mA   |
| Power dissipation <sup>(1)</sup>               | $T_{amb} = 65\text{ }^{\circ}\text{C}$ | $P_{tot}$ | 200   | mW   |

#### Note

<sup>(1)</sup> Valid provided that electrodes are kept at ambient temperature

### THERMAL CHARACTERISTICS ( $T_{amb} = 25\text{ }^{\circ}\text{C}$ , unless otherwise specified)

| PARAMETER                                  | TEST CONDITION   | SYMBOL     | VALUE       | UNIT               |
|--|--|------------|-------------|--------------------|
| Thermal resistance junction to ambient air | Valid provided that electrodes are kept at ambient temperature | $R_{thJA}$ | 300         | K/W                |
| Junction temperature                       |  | $T_j$      | 125         | $^{\circ}\text{C}$ |
| Ambient operating temperature range        |  | $T_{amb}$  | -65 to +125 | $^{\circ}\text{C}$ |
| Storage temperature range                  |  | $T_{stg}$  | -65 to +150 | $^{\circ}\text{C}$ |

### ELECTRICAL CHARACTERISTICS ( $T_{amb} = 25\text{ }^{\circ}\text{C}$ , unless otherwise specified)

| PARAMETER                                | TEST CONDITION   | SYMBOL     | MIN. | TYP. | MAX. | UNIT          |
|--|--|------------|------|------|------|---------------|
| Reverse breakdown voltage <sup>(1)</sup> | $I_R = 100\text{ }\mu\text{A}$                         | $V_{(BR)}$ | 100  | 110  |      | V             |
| Leakage current <sup>(1)</sup>           | $V_R = 50\text{ V}, T_j = 25\text{ }^{\circ}\text{C}$  | $I_R$      |      |      | 100  | nA            |
|  | $V_R = 50\text{ V}, T_j = 100\text{ }^{\circ}\text{C}$ | $I_R$      |      |      | 20   | $\mu\text{A}$ |
| Forward voltage <sup>(1)</sup>           | $I_F = 1\text{ mA}$                                    | $V_F$      |      | 400  | 450  | mV            |
|  | $I_F = 200\text{ mA}$                                  | $V_F$      |      |      | 1000 | mV            |
| Diode capacitance                        | $V_R = 1\text{ V}, f = 1\text{ MHz}$                   | $C_D$      |      | 2    |      | pF            |

#### Note

<sup>(1)</sup> Pulse test,  $t_p = 300\text{ }\mu\text{s}$

**TYPICAL CHARACTERISTICS** ( $T_{amb} = 25\text{ }^{\circ}\text{C}$ , unless otherwise specified)




Fig. 1 - Admissible Power Dissipation vs. Ambient Temperature




Fig. 3 - Typical Forward Characteristics




Fig. 2 - Typical Reverse Characteristics





Fig. 4 - Typical Capacitance vs. Reverse Voltage

**PACKAGE DIMENSIONS** in millimeters (inches): **DO-35 (DO-204AH)**



Rev. 6 - Date: 19. December 2011  
 Document no.: SB-V-3906.04-031(4)  
 94 9366



## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.