# **High Pass Filter**

### 950 to 3200 MHz $50\Omega$

# **Maximum Ratings**


Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power Input*	7W max. at 25°C
Max. DC Voltage at pins 1&3	25 VDC


<sup>\*</sup> Passband rating, derate linearly to 3W at 100°C ambient. Permanent damage may occur if any of these limits are exceeded

## **Pin Connections**

RF IN	1_
RF OUT	3
GROUND	2,4

# **Outline Drawing**






## Outline Dimensions (inch)

Α	В	С	D	Е	F	G	
.126	.063	.037	.020	.032	.009	.169	
3.20	1.60	0.94	0.51	0.81	0.23	4.29	
Н	J	K	L	M	N	Р	wt
H .087	J .024	.122	.024	M .087	N .012	P .071	wt grams

## Demo Board MCL P/N: TB-270 Suggested PCB Layout (PL-137)



. COPLANAR WAYEGUIDE PARAMETERS ARE SHOWN FOR ROGERS RO4350B WITH THICKNESS .020" ± .0015". COPPER: 1/2 0Z. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH & GAP MAY NEED TO BE MODIFIED.

BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC
(SOLDER MASK OVER BARE COPPER)


DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

### **Features**

- low cost
- small size
- 7 sections
- temperature stable
- hermetically sealed
- LTCC construction
- excellent power handling, 7W

# **Applications**

- sub-harmonic rejection
- transmitters/receivers
- lab use



HFCN-880D+

CASE STYLE: FV1206

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications




# Electrical Specifications<sup>1,2</sup> at 25°C


(MI	BAND Hz) in.	fco, MHz Nom.			` '	POWER INPUT (W)	NO. OF SECTIONS	
-	••••	(loss 3 dB)	(loss < 1.3 dB)	(loss < 2 dB)		Frequency (MHz)	(,	
(loss > 40 dB)	(loss > 20 dB)	Тур.	Max.	Typ.	Stopband	1.5:1		
500	640	880	1060-2500	950-3200	20:1	970-2400	7	7

- 1. DC Resistance to ground is 100 Mohms min.
- 2. Measured on Mini-Circuits Characterization Test Board TB-270.

# typical frequency response





### electrical schematic



# Typical Performance Data at 25°C

Frequency	Insertion Loss	VSWR		
(MHz)	(dB)	(:1)		
1.00	82.28	868.59		
100.00	78.78	868.59		
500.00	45.84	56.04		
640.00	23.68	24.14		
750.00	10.22	8.68		
810.00	4.65	3.84		
880.00	1.97	1.83		
950.00	1.17	1.36		
970.00	1.06	1.32		
1060.00	0.83	1.26		
2400.00	0.52	1.46		
2500.00	0.60	1.58		
3200.00	1.42	2.62		
5000.00	5.12	7.87		





- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

  B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and programment.

  C. The parts covered by this specification document are subject to Mini-Circuit's storded limited and the part of this specification document. Electrical specifications and performance data contained in this specification document are harded to be excluded and of the form a part of this specification. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

  The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp