


## AL0510 Series Leaded RF Chokes



### ◆特征:

- 环氧树脂涂层,耐湿度,使用寿命长.
- 电感范围宽,设计紧凑体积小,重量轻.
- 高 Q 和自我共振频率
- 编带包装可用于自动插件
- 符合 RoHS,无卤和 REACH

### Features:

- Coating epoxy resin that ensure the humidity resistance to be long life
- Design to be compact, small and light-weight
- Wide range of inductance
- Contribute to be high Q and self-resonant frequencies
- Tape packaging for auto-insertion
- RoHS, Halogen Free and REACH Compliance

### ◆用途:

- 电视、个人电脑
- 收音机、电话
- 充电器,快充
- 其他各种电子产品

### Applications:

- Televisions, personal computers
- Radios, telephones
- Charger, fast charge
- Other various electronic products

### ◆环境:

- 工作温度: -25℃ 至+85℃  
(包括线圈自身温升)

### Environmental Data:

- Operating Temperature: -25℃ to +85℃  
(Including coils self-temperature rise)

### ◆试验设备:

- 电感值:HP4284A, HP4285A 或同等仪器
- 电流:HP4284+42841A
- 自谐振频率: HM 9461
- 品质因子: HP4285A
- 直流电阻: Chroma 16502 或同等仪器

### Test Equipment:

- L:HP4284A or HP4285A LCR meter or equivalent
- Isat & Irms: HP4284+42841A
- SRF: HM 9461
- Q: HP4285A
- DCR:Chroma 16502 or equivalent

### ◆产品型号:

### Product Identification:

AL  
①
0510  
②
100  
③
K  
④
I  
⑤

①

|         |                                 |
|---------|---------------------------------|
| 类型 Type |                                 |
| AL      | 轴向固定电感<br>Axial Fixed Inductors |

②

|   |         |
|---|---------|
| 外形尺寸(L×W×H) (mm)<br>External Dimensions (L×H)<br>(mm) |         |
| 0510  | 5.0×111 |

③

|            |
|------------|
| Inductance |
| 10 μH      |

④

|  |
|--|
| 公差 Inductance Tolerance                            |
| J:±5%,K: ±10%, L: ±15%<br>M: ±20%,P: ±25%, N: ±30% |


⑤

|            |                 |
|------------|-----------------|
| 包装 Packing |                 |
| B          | 散装 Bulk Package |
| TF         | 编带 Tape         |

◆颜色编码:

Color Coding:

The nominal inductance is marked. Color code listed in table below. 标称电感值用色码编码表示如下表所示。







| Color<br>颜色 | Nominal Inductance(uH)标称电感值(微亨) |            |            |           |
|-------------|---------------------------------|------------|------------|-----------|
|             | 1st Figure                      | 2nd Figure | Multiplier | Tolerance |
| Black 黑     | 0                               |            | x1         | ±20%      |
| Brown 棕     | 1                               |            | x10        |           |
| Red 红       | 2                               |            | x100       |           |
| Orange 橙    | 3                               |            | x1000      |           |
| Yellow 黄    | 4                               |            |            |           |
| Green 绿     | 5                               |            |            |           |
| Blue 蓝      | 6                               |            |            |           |
| Violet 紫    | 7                               |            |            |           |
| Gray 灰      | 8                               |            |            |           |
| White 白     | 9                               |            |            |           |
| Gold 金      |                                 |            | x0.1       | ±5%       |
| Silver 银    |                                 |            | x0.01      | ±10%      |

◆外观尺寸:

Shape and Dimensions(dimensions are in mm):

F1

F2



| Part No | ITEM   |          |          |           |
|---------|--------|----------|----------|-----------|
|         | Figure | A        | B        | C         |
| AL0510  | F2     | Ø5.0 Max | 11.0 Max | Ø0.60±0.1 |

◆规格特性:

SpALifications:

● AL0510 Series EIALtrical Characteristics (EIALtrical spALifications at 25°C)


| Part No     | Inductance      |      | Q   | G             | SRF          | DCR        | Rated Current |
|-------------|-----------------|------|-----|---------------|--------------|------------|---------------|
|             | @ 1KHz<br>L(mH) | Tole | Min | Test<br>Freq. | (MHz)<br>Min | (Ω)<br>Max | (mA)<br>Max   |
| AL0510-3R3M | 3.3             | ±10% | 20  | 7.96MHZ       | 50           | 0.18       | 1100          |
| AL0510-4R7M | 4.7             | ±10% | 20  | 7.96MHZ       | 45           | 0.20       | 1000          |
| AL0510-6R8M | 6.8             | ±10% | 20  | 7.96MHZ       | 45           | 0.25       | 790           |
| AL0510-100K | 10              | ±10% | 15  | 7.96MHZ       | 30           | 0.45       | 750           |
| AL0510-150K | 15              | ±10% | 15  | 7.96MHZ       | 30           | 0.50       | 650           |
| AL0510-220K | 22              | ±10% | 30  | 2.52 MHz      | 8.0          | 0.65       | 500           |
| AL0510-330K | 33              | ±10% | 30  | 2.52 MHz      | 6.0          | 0.75       | 400           |
| AL0510-470K | 47              | ±10% | 30  | 2.52 MHz      | 6.3          | 0.8        | 370           |
| AL0510-680K | 68              | ±10% | 30  | 2.52 MHz      | 5.0          | 0.8        | 350           |
| AL0510-820K | 82              | ±10% | 20  | 2.52 MHz      | 3.8          | 0.82       | 330           |
| AL0510-101K | 100             | ±10% | 20  | 2.52 MHz      | 3.5          | 0.90       | 300           |
| AL0510-121K | 120             | ±10% | 20  | 0.796 MHz     | 3.3          | 1.20       | 250           |
| AL0510-151K | 150             | ±10% | 20  | 0.796 MHz     | 3.2          | 1.80       | 225           |
| AL0510-181K | 180             | ±10% | 20  | 0.796 MHz     | 2.8          | 2.00       | 200           |
| AL0510-221K | 220             | ±10% | 30  | 0.796 MHz     | 2.6          | 2.10       | 180           |
| AL0510-271K | 270             | ±10% | 30  | 0.796 MHz     | 2.4          | 2.50       | 170           |
| AL0510-331K | 330             | ±10% | 30  | 0.796 MHz     | 2.2          | 3.00       | 160           |
| AL0510-391K | 390             | ±10% | 30  | 0.796 MHz     | 2.0          | 3.50       | 150           |
| AL0510-471K | 470             | ±10% | 30  | 0.796 MHz     | 1.9          | 4.00       | 140           |
| AL0510-561K | 560             | ±10% | 30  | 0.796 MHz     | 1.8          | 5.40       | 130           |
| AL0510-681K | 680             | ±10% | 40  | 0.796 MHz     | 1.5          | 6.00       | 120           |
| AL0510-821K | 820             | ±10% | 50  | 0.796 MHz     | 1.2          | 7.50       | 110           |
| AL0510-102K | 1000            | ±10% | 50  | 0.252 MHz     | 1.0          | 8.00       | 100           |
| AL0510-122K | 1200            | ±10% | 60  | 0.252 MHz     | 0.95         | 14.50      | 95            |
| AL0510-152K | 1500            | ±10% | 60  | 0.252 MHz     | 0.9          | 10.50      | 90            |
| AL0510-182K | 1800            | ±10% | 60  | 0.252 MHz     | 0.9          | 19.00      | 85            |
| AL0510-222K | 2200            | ±10% | 60  | 0.252 MHz     | 0.8          | 27.50      | 80            |
| AL0510-272K | 2700            | ±10% | 60  | 0.252 MHz     | 0.75         | 40.00      | 75            |
| AL0510-332K | 3300            | ±10% | 50  | 0.252 MHz     | 0.7          | 50.00      | 62            |
| AL0510-392K | 3900            | ±10% | 50  | 0.252 MHz     | 0.65         | 53.00      | 59            |
| AL0510-472K | 4700            | ±10% | 50  | 0.252 MHz     | 0.6          | 60.00      | 55            |
| AL0510-562K | 5600            | ±10% | 50  | 0.252 MHz     | 0.5          | 64.00      | 40            |
| AL0510-682K | 6800            | ±10% | 50  | 0.252 MHz     | 0.45         | 73.00      | 35            |
| AL0510-822K | 8200            | ±10% | 30  | 0.252 MHz     | 0.4          | 80.00      | 30            |
| AL0510-103K | 10000           | ±10% | 25  | 79.6 KHZ      | 0.35         | 132.00     | 25            |
| AL0510-123K | 12000           | ±10% | 25  | 79.6 KHZ      | 0.3          | 145.00     | 20            |
| AL0510-153K | 15000           | ±10% | 25  | 79.6 KHZ      | 0.25         | 166.00     | 18            |
| AL0510-183K | 18000           | ±10% | 25  | 79.6 KHZ      | 0.2          | 185.00     | 15            |
| AL0510-223K | 22000           | ±10% | 20  | 79.6 KHZ      | 0.15         | 330.00     | 12            |
| AL0510-273K | 27000           | ±10% | 20  | 79.6 KHZ      | 0.1          | 370.00     | 10            |
| AL0510-333K | 33000           | ±10% | 40  | 79.6 KHZ      | 0.25         | 240.00     | 10            |

- Saturation Current: The current when the inductance becomes 10% lower than its initial value ( $T_a=25^{\circ}\text{C}$ ).
- Temperature Rise Current: the actual value of DC current when the temperature rise is  $\Delta T 40^{\circ}\text{C}$  ( $T_a=25^{\circ}\text{C}$ )
- Rated DC Current: The less value which is  $I_{\text{sat}}$  or  $I_{\text{rms}}$
- Special remind: Circuit design, component, PCB trace size and thickness, airflow and other cooling provisions all affect the part temperature. Part temperature should be verified in the end application


### ◆ 产品包装:

### Packaging:


- Tape Specifications (mm) 编带尺寸



- Tape Specifications for T5A (mm) 直脚编带盒装，产品常规包装方式



INSIDE BOX



Outside Carton




不足整箱用内盒或填充物装满





- Tape and reel specification (mm)



| Series | Type | Packaging Quantity(pcs) |            |              | Carton Size(mm) |     |     |
|--------|------|-------------------------|------------|--------------|-----------------|-----|-----|
|        |      | Parts/Box               | Parts/Reel | Parts/Carton | L               | W   | H   |
|        | T5A  | 1000                    |            | 24,000       | 440             | 275 | 392 |

◆可靠性测试:

Reliability Testing:


| Items  | Requirements   | Test Methods and Remarks   |
|--|--|--|
| Terminal Strength<br>Reference documents: GB/T 2423.60-2008<br>端子强度(SMT) | <p>1. Pulling test:<br/>Define: A: sALtional area of terminal<br/><math>A \geq 8\text{mm}^2</math> force <math>\geq 5\text{N}</math> time: 30sAL<br/><math>8\text{mm}^2 &lt; A \leq 20\text{mm}^2</math> force <math>\geq 10\text{N}</math> time: 10sAL<br/><math>20\text{mm}^2 &lt; A</math> force <math>\geq 20\text{N}</math> time: 10sAL</p> <p>2. Solder paste thickness: 0.12mm</p> <p>3. Meet the above requirements without any loose terminal</p>                             | <p>Solder the inductor to the testing jig using leadfree solder. Then apply a force in the direction shown</p> <p>Keep time: <math>10 \pm 1\text{s}</math> Speed: 1.0mm/s.</p>   |
| Terminal Strength<br>Reference documents: GB/T 2423.60-2008<br>端子强度(DIP) | <p>1. Terminal diameter(d) mm <math>0.35 &lt; d \leq 0.50</math> Applied force: 5N Duration: 10sAL</p> <p>2. Terminal diameter(d) mm <math>0.50 &lt; d \leq 0.80</math> Applied force: 10N Duration: 10sAL</p> <p>3. Terminal diameter(d) mm <math>0.80 &lt; d \leq 1.25</math> Applied force: 20N Duration: 10sAL</p> <p>4. Terminal diameter(d) mm <math>D &gt; 1.25</math> Applied force: 40N Duration: 10sAL</p> <p>5. Meet the above requirements without any loose terminal.</p> | <p>Pull Force: the force shall be applied gradually to the terminal and then maintained for 10 sALonds.</p>   |
| Resistance to Flexure<br>JIS C 5321:1997<br>抗弯曲性试验                       | <p>1. No visible mechanical damage.</p>  | <p>1. Solder the inductor to the test jig (glass epoxy board)</p> <p>2. shown in Using a leadfree solder. Then apply a force in the direction shown</p> <p>3. Flexure: 2mm.</p> <p>4. Pressurizing Speed: 0.5mm/sAL.</p> <p>5. Keep time: 30 sAL.</p>  |
| Dropping<br>Reference documents: GB/T 2423.7-2018<br>落下试验                | <p>1. No case deformation or change in appearance.</p> <p>2. No short and no open.</p>   | <p>1. Drop the packaged products from 1m high in 1 angle, 3 ridges and 6 surfaces, twice in each direction.</p>  |
| Solderability<br>Reference documents: GB/T 2423.28-2005<br>可焊性试验         | <p>1. No visible mechanical damage.</p> <p>2. Wetting shall exceed 75% coverage for</p> <p>3. Terminals must have 95% minimum solder coverage</p>  | <p>1. Solder temperture: <math>240 \pm 2^\circ\text{C}</math></p> <p>2. Duration: 3 sAL.</p> <p>3. Solder: Sn/3.0Ag/0.5Cu.</p> <p>4. Flux: 25% Resin and 75% ethanol in weight</p>   |

| Items  | Requirements  | Test Methods and Remarks   |
|--|---|--|
| <p>Vibration</p> <p>Reference documents:<br/>GB/T 2423.10-2019<br/>振動試験</p>                              | <p>1.No visible mechanical damage.</p> <p>2. Inductance change: Within <math>\pm 10\%</math>.</p> <p>3.Q factor change: Within <math>\pm 20\%</math>.</p>  <p>Cu pad      Solder mask</p> <p>Glass Epoxy Board</p> | <p>1.Solder the inductor to the testing jig (glass epoxy board shown in ) using leadfree solder.</p> <p>2.The inductor shall be subjected to a simple harmonic motion having total amplitude of 1.5mm, the frequency being varied uniformly between the approximate limits of 10 and 55 Hz.</p> <p>3.The frequency range from 10 to 55 Hz and return to 10 Hz shall be traversed in approximately 1 minute. This motion shall be applied for a period of 2 hours in each 3 mutually perpendicular directions (total of 6 hours).</p>  |
| <p>Thermal Shock</p> <p>Reference documents:<br/>GB/T 2423.22-2012<br/>Method Na<br/>冷热冲击试验</p>          | <p>1.No visible mechanical damage.</p> <p>2. Inductance change: Within <math>\pm 10\%</math>. (Mn-Zn: Within <math>\leq 30\%</math> )</p> <p>3 Q factor change: Within <math>\pm 20\%</math>.</p>   | <p>1.Start at ( 85~125℃ ) for T time, rush to -55~-40℃ for T time as one cycle, go through 100 cycles.</p> <p>2.Transforming interval: Max. 20 s</p> <p>3.Tested cycle: 100 cycles.</p> <p>4.The chip shall be stabilized at normal condition for 1~2 hours</p>    |
| <p>Low temperature Storage</p> <p>Reference documents:<br/>GB/T 2423.1-2003<br/>Method 4b<br/>低温储存试验</p> | <p>1.No visible mechanical damage.</p> <p>2. Inductance change: Within <math>\pm 10\%</math>. (Mn-Zn: Within <math>\leq 30\%</math> )</p> <p>3.Q factor change: Within <math>\pm 20\%</math>.</p>   | <p>1. Temperature: M(-55~-40<math>\pm 2^\circ\text{C}</math>)</p> <p>2.Duration: 96<math>\pm 2</math> hours</p> <p>3.The chip shall be stabilized at normal condition for 1~2 hours before measuring.</p>    |

| Items   | Requirements   | Test Methods and Remarks  |
|---|--|---|
| <p>High temperature Storage</p> <p>Reference documents: GB/T 2423.2-2008</p> <p>Method 5b</p> <p>高温储存试验</p> | <p>1.No visible mechanical damage.</p> <p>2. Inductance change: Within <math>\pm 10\%</math>. (Mn-Zn: Within <math>\leq 30\%</math> )</p> <p>3.Q factor change: Within <math>\pm 20\%</math></p>   | <p>1. Temperature: <math>N(125 \sim 85 \pm 2^\circ\text{C})</math>.</p> <p>2. Duration: <math>96 \pm 2</math> hours</p> <p>3. The chip shall be stabilized at normal condition for 1~2 hours before measuring.</p>                          |
| <p>Damp Heat (Steady States)</p> <p>Reference documents: GB/T 2423.3-2016</p> <p>恒定湿热试验</p>                 | <p>1.No visible mechanical damage.</p> <p>2. Inductance change: Within <math>\pm 10\%</math>. (Mn-Zn: Within <math>\leq 30\%</math> )</p> <p>3.Q factor change: Within <math>\pm 20\%</math>.</p>  | <p>1. Temperature: <math>60 \pm 2^\circ\text{C}</math></p> <p>2. Humidity: 90% to 95% RH.</p> <p>3. Duration: <math>96 \pm 2</math> hours.</p> <p>4. The chip shall be stabilized at normal condition for 1~2 hours before measuring.</p>  |
| <p>Heat endurance of Reflow soldering</p> <p>Reference documents: GJB 360B-2009</p> <p>回流焊耐热性试验</p>         | <p>1.No significant defects in appearance.</p> <p>2. <math>\Delta L/L \leq 10\%</math> (Mn-Zn: <math>\Delta L/L \leq 30\%</math> )</p> <p>3. <math>\Delta Q/Q \leq 30\%</math> (SMD series only)</p> <p>4. <math>\Delta DCR/DCR \leq 10\%</math></p> | <p>1. Refer to the above reflow curve and go through the reflow for twice.</p> <p>2. The peak temperature : <math>260 \pm 0.5^\circ\text{C}</math></p>  |
| <p>Resistance to solvent test</p> <p>Reference documents: IAL 68-2-45:1993</p> <p>耐溶剂性试验</p>                | <p>No case deformation or change in appearance or obliteration of marking</p>  | <p>To dip parts into IPA solvent for <math>5 \pm 0.5</math> Min, then drying them at room temp for 5 Min, at last ,to brushing making 10 times.</p>   |
| <p>Overload test</p> <p>Reference documents: JIS C5311-6.13</p> <p>过负荷试验</p>                                | <p>1. During the test no smoke, no peculiar smell, no fire</p> <p>2. The characteristic is normal after test</p>   | <p>Apply twice as rated current for 5 minutes.</p>  |
| <p>voltage resistance test</p> <p>Reference documents: MIL-STD-202G Method 301</p> <p>绝缘耐压测试</p>            | <p>1. During the test no breakdown</p> <p>2. The characteristic is normal after test</p>   | <p>1. For parts with two coils</p> <p>2. DC1000V, Current: 1mA, Time: 1Min.</p> <p>3. Refer to catalogue of spALific products</p>   |

◆推荐无铅波峰焊接曲线:  
(DIP-TYP) :

Lead-free the rALommeded Wave soldering




Notes:

The rALommeded wave soldering, is a reference to a single wave soldering rALommeded by the manufacturer, bALause the various manufacturers of soldering equipment, product process conditions, set methods and so on, when setting the soldering conditions, Please adjust and confirm according to users' environment/equipments.

● Appendix 2: Soldering Iron (Rework)

- 1) Use soldering iron to solder inductors by hand, times does Not exceed 350 degrees 3 times.
- 2) When soldering iron welding, please try to avoid contacting the Inductor itself. (definitely do not contact the wire)
- 3) To solder inductors by soldering iron is not rALommeded).





## 使用注意事项

### REMINDERS FOR USING THESE PRODUCTS



- 保存时间为12个月以内，保存条件（温度5~40°C以下、湿度35%~66%RH以下），需充分注意。若超过保存时间，端子电极的可焊性将可能老化。  
The storage period is within 12 months. Be sure to follow the storage conditions (temperature: 5~40°C, humidity: 35 to 65% RH or less). If the storage period elapses, the soldering of the terminal electrodes may deteriorate.
- 请勿在气体腐蚀环境（盐、酸、碱等）下使用和保存。  
Do not use or store in locations where there are conditions such as gas corrosion (salt, acid, alkali, etc.).
- 手上的油脂会导致可焊性降低，应避免用手直接接触端子。  
Don't touch electrodes directly with bare hands as oil residues may inhibit soldering. Always ensure optimum conditions for soldering.
- 请小心轻拿轻放，避免由于产品的跌落或取出不当而导致的损坏。  
Please always handle products carefully to prevent any damage caused by dropping down or inappropriate removing.
- 端子过度弯曲会导致断线，请不要过度弯曲端子。  
Don't bend the terminals with excessive stress in case of any wire fracture.
- 不要清洗产品，如需要清洗时请联系我司。  
Don't rinse coils by yourself and please contact SXN if necessary.
- 请勿将本产品靠近磁铁或带有磁力的物体  
Don't expose the products to magnets or magnetic fields
- 在实施焊接前，请务必进行预热。预热温度与焊接温度及芯片温度的温度差要在150°C以内。  
Before soldering, be sure to preheat components. The preheating temperature should be set so that the temperature difference between the solder temperature and chip temperature does not exceed 150°C.
- 安装后的焊接修正应在规格书规定的条件范围内。若加热过度可能导致短路、性能降低、寿命减少。  
Soldering corrections after mounting should be within the range of the conditions determined in the specifications. If overheated, a short circuit, performance deterioration, or lifespan shortening may occur.
- 装置会因通电而自我发热（温度上升），因此在热设计方面需留有充分余地。  
Self heating (temperature increase) occurs when the power is turned ON, so the tolerance should be sufficient for the set thermal design.
- 非磁屏蔽型在基板设计时需注意配置线圈，受到电磁干扰可能会导致误动作。  
Carefully lay out the coil for the circuit board design of the non-magnetic shield type. A malfunction may occur due to magnetic interference.