


# 3/8" Square (10 mm) Multi-Turn Cermet Trimmer



## FEATURES

- Industrial grade
- 0.5 W at 70 °C
- Tests according to CECC 41000 or IEC 60393-1
- Contact resistance variation < 2 %
- Material categorization: for definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)



RoHS  
COMPLIANT

## DESIGN SUPPORT TOOLS

[click logo to get started](#)



The Model 64 is a small size trimmer - 3/8" x 3/8" x 3/16" - answering PC board mounting requirements. Five versions are available which differ by the position of the control screw in relation to the PC board plane and by the spacing of the terminals. Excellent operational stability is provided by the use of a cermet element.

| DIMENSIONS in millimeters ( $\pm 0.5$ mm) |  |  |  |
|---|--|--|--|
| <p><b>64X</b></p>                         |  |  | <p><b>Terminal Spacing on a 2.54 PCB</b></p> |
| <p><b>64Z</b></p>                         |  |  | <p><b>Terminal Spacing on a 2.54 PCB</b></p> |
| <p><b>64W</b></p>                         |  |  | <p><b>Terminal Spacing on a 2.54 PCB</b></p> |
| <p><b>64Y</b></p>                         |  |  | <p><b>Terminal Spacing on a 2.54 PCB</b></p> |
| <p><b>64P</b></p>                         |  |  | <p><b>Terminal Spacing on a 2.54 PCB</b></p> |

Note

(1) To be measured at base level

| <b>ELECTRICAL SPECIFICATIONS</b>             |                                       |      |
|--|---------------------------------------|------|
| Resistive element                            | Cermet                                |      |
| Electrical travel                            | 21 turns $\pm$ 2                      |      |
| Resistance range                             | 10 $\Omega$ to 2.2 M $\Omega$         |      |
| Standard series E3                           | 1 - 2 - 2.5 - 5                       |      |
| Tolerance                                    | Standard                              | 10 % |
|  | On request                            | 5 %  |
| Power rating                                 | linear<br>0.5 W at +70 °C<br>         |      |
| Circuit diagram                              |                                       |      |
| Temperature coefficient                      | See Standard Resistance Element table |      |
| Limiting element voltage (linear law)        | 250 V                                 |      |
| Contact resistance variation                 | 2 % R <sub>n</sub> or 2 $\Omega$      |      |
| End resistance (typical)                     | 1 $\Omega$                            |      |
| Dielectric strength (RMS)                    | 1000 V                                |      |
| Insulation resistance (500 V <sub>DC</sub> ) | 10 <sup>6</sup> M $\Omega$            |      |

| <b>MECHANICAL SPECIFICATIONS</b> |                            |
|----------------------------------|----------------------------|
| Mechanical travel                | 23 turns $\pm$ 5           |
| Operating torque (max. Ncm)      | 1.5                        |
| End stop torque                  | Clutch action              |
| Net weight                       | Approx. 0.82 g             |
| Wiper (actual travel)            | Positioned at approx. 50 % |
| Terminals                        | Pure Sn (code e3)          |

| <b>ENVIRONMENTAL SPECIFICATIONS</b> |                     |
|-------------------------------------|---------------------|
| Temperature range                   | -55 °C to +125 °C   |
| Climatic category                   | 55/125/56           |
| Sealing                             | Fully sealed - IP67 |



| STANDARD RESISTANCE ELEMENT DATA |                     |                      |                            |                                  |
|----------------------------------|---------------------|----------------------|----------------------------|----------------------------------|
| STANDARD RESISTANCE VALUES       | LINEAR LAW          |                      |                            | TYPICAL TCR<br>-55 °C<br>+125 °C |
|                                  | MAX. POWER AT 70 °C | MAX. WORKING VOLTAGE | MAX. CURRENT THROUGH WIPER |                                  |
| Ω                                | W                   | V                    | mA                         | ppm/°C                           |
| 10                               | 0.5                 | 2.2                  | 224                        | ± 100                            |
| 20                               | 0.5                 | 3.2                  | 158                        |                                  |
| 50                               | 0.5                 | 5                    | 100                        |                                  |
| 100                              | 0.5                 | 7.1                  | 71                         |                                  |
| 200                              | 0.5                 | 10                   | 50                         |                                  |
| 250                              | 0.5                 | 11.2                 | 45                         |                                  |
| 500                              | 0.5                 | 15.8                 | 32                         |                                  |
| 1K                               | 0.5                 | 22.4                 | 22                         |                                  |
| 2K                               | 0.5                 | 31.6                 | 16                         |                                  |
| 2.5K                             | 0.5                 | 35.4                 | 14                         |                                  |
| 5K                               | 0.5                 | 50                   | 10                         |                                  |
| 10K                              | 0.5                 | 70.7                 | 7.1                        |                                  |
| 20K                              | 0.5                 | 100                  | 5                          |                                  |
| 25K                              | 0.5                 | 112                  | 4.5                        |                                  |
| 50K                              | 0.5                 | 158                  | 3.2                        |                                  |
| 100K                             | 0.5                 | 224                  | 2.2                        |                                  |
| 200K                             | 0.31                | 250                  | 1.3                        |                                  |
| 250K                             | 0.25                | 250                  | 1                          |                                  |
| 500K                             | 0.125               | 250                  | 0.5                        |                                  |
| 1M                               | 0.063               | 250                  | 0.25                       |                                  |
| 2M                               | 0.031               | 250                  | 0.13                       |                                  |

| PERFORMANCES             |   |  |   |
|--------------------------|---|--|---|
| TESTS                    | CONDITIONS  | TYPICAL VALUES AND DRIFTS  |   |
|                          |   | $\Delta R_T/R_T$ (%)   | $\Delta R_{1-2}/R_{1-2}$ (%)                    |
| Load life                | 1000 h at rated power<br>90'/30' - ambient temp. 70 °C  | ± 1 %<br>Contact res. variation: < 1 % Rn  | ± 2 %   |
| Climatic sequence        | Phase A dry heat 125 °C - 30 % Pr<br>Phase B damp heat<br>Phase C cold -55 °C<br>Phase D damp heat 5 cycles | ± 0.5 %  | ± 1 %   |
| Long term damp heat      | 56 days<br>40 °C, 93 % RH   | ± 0.5 %<br>Dielectric strength: 1000 V <sub>RMS</sub><br>Insulation resistance: > 10 <sup>4</sup> MΩ | ± 1 %   |
| Rapid temperature change | 5 cycles<br>-55 °C to +125 °C   | ± 0.5 %  | $\Delta V_{1-2}/\Delta V_{1-3} \leq \pm 1 \%$   |
| Shock                    | 50 g at 11 ms<br>3 successive shocks<br>in 3 directions   | ± 0.1 %  | ± 0.2 %   |
| Vibration                | 10 Hz to 55 Hz<br>0.75 mm or 10 g<br>during 6 h   | ± 0.1 %  | $\Delta V_{1-2}/\Delta V_{1-3} \leq \pm 0.2 \%$ |
| Rotational life          | 200 cycles  | ± 4 %<br>Contact res. variation: < 1 % Rn  | -   |

**Note**

- Nothing stated herein shall be construed as a guarantee of quality or durability

| MARKING   |
|---|
| <ul style="list-style-type: none"> <li>• Vishay trademark</li> <li>• Model</li> <li>• Style</li> <li>• Ohmic value (in Ω, kΩ, MΩ)</li> <li>• Tolerance (in %)</li> <li>• Manufacturing date</li> <li>• Marking of terminal 3</li> </ul> |



| PACKAGING   |
|---|
| <ul style="list-style-type: none"> <li>In box of 200 pieces code B40 (BO200)</li> </ul> On request: <ul style="list-style-type: none"> <li>In box of 100 pieces code B30 (BO100)</li> <li>In tube of 50 pieces code T20 (TU50)</li> </ul> |

| ORDERING INFORMATION (part number) |                       |   |  |   |   |                                   |   |  |   |   |  |  |  |
|------------------------------------|-----------------------|---|--|---|---|-----------------------------------|---|--|---|---|--|--|--|
| M                                  | 6                     | 4 | P                                      | 2 | 2 | 4                                 | K | B  | 4 | 0   |  |  |  |
| Model                              | STYLE                 |   | OHMIC VALUE                            |   |   | TOLERANCE                         |   | PACKAGING  |   | SPECIAL NUMBER  |  |  |  |
| M64                                | P<br>W<br>X<br>Y<br>Z |   | From<br>10 Ω to 2.2 MΩ<br>224 = 220 kΩ |   |   | K = 10 %<br>On request<br>J = 5 % |   | B40 = box<br>200 pieces<br>On request:<br>B30 = box<br>100 pieces<br>T20 = tube<br>50 pieces |   | (If applicable)<br>Given by Vishay<br>for custom design |  |  |  |

| DESCRIPTION (for information only) |       |       |           |         |           |             |
|------------------------------------|-------|-------|-----------|---------|-----------|-------------|
| 64                                 | P     | 220K  | 10 %      |         | BO200     | e3          |
| MODEL                              | STYLE | VALUE | TOLERANCE | SPECIAL | PACKAGING | LEAD FINISH |

| RELATED DOCUMENTS   |  |
|---|--|
| <b>APPLICATION NOTES</b>  |  |
| Potentiometers and Trimmers                                       | <a href="http://www.vishay.com/doc?51001">www.vishay.com/doc?51001</a> |
| Guidelines for Vishay Sfernice Resistive and Inductive Components | <a href="http://www.vishay.com/doc?52029">www.vishay.com/doc?52029</a> |



## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.