4080W 3-Phase Input Industrial Power Supplies

https://product.tdk.com/en/power/tps www.emea.lambda.tdk.com/tps













The TPS series industrial AC-DC power supplies offer output power up to 4,080W in a 2U high package with 3 phase supply input. Features include voltage and current programming, remote on/off, remote sense, a standby supply, PMBus™ communication, built in ORing FET and wide operating temperature range of -40°C to +70°C. The TPS4000 is also designed to meet MIL-STD-461F/G RE102 EMI and MIL-STD-810F vibration and shock.

Features	Benefits
• 400/440/480Vac (Nominal) 3 Phase Delta or Wye	Global Use
Fully Regulated, Wide Range Voltage Adjustment	Versatile Application
Voltage and Current Programming	Flexible Control and Adjustment
• -40°C (start up) to +70°C operation	Suitable for Rugged Environments
• 92% Typical Efficiency	Less Energy Used
PMBus™ Communication	Remote Output Programming and Monitoring
Built in ORing FET for parallel operation	Suitable for N + 1 Redundancy

Model Selecto	or						
Model	Nominal Output Voltage (V)	Adjustment Range (V)	Max Current (A)	Max Power (W)	Max Current at Nominal Voltage (A)	Max Power at Nominal Voltage (V)	
TPS4000-24	24	19.2 - 28.5	166	4000	170	4080	
TPS4000-48	48	38.4 - 58	83.3	4000	85	4080	

^{*}Wider range adjustment as stated on the UL safety files are possible, although some parameters might not meet some of the listed specifications.

Related Pro	ducts	
Туре	Part Number	Description
EMC filter	RTMN-5020	High attenuation 20A 500Vac 3-phase input two stage filter

Specification		
Model		TPS4000
Input		
Input Voltage range	V	350 - 528, Delta or Wye 3 phase (Note: Safety certified for 400-480Vac only)
Input Frequency	Hz	47 - 63 (Note: Safety certified for 50 to 60Hz only)
Input Current (At nominal Vin)	Α	8 per phase (steady state)
Inrush Current at 400-480Vac (Cold Start)	Α	<25 per phase (excluding initial filter capacitor charging <2ms)
Dropped Phase Power	W	1600. Not recommended for long term operation
Leakage Current	mA	<3
Power Factor (400-480Vac)	-	0.92 typical at rated load, nominal Vin
Harmonic Compliance	-	Not applicable
Hold Up Time (typ)	ms	>10 at 80% of rated current, nominal input/output voltage
Efficiency (Typical)	-	92%
Conducted & Radiated EMI	-	EN55032-A Conducted and radiated (In end system)
Immunity	-	EN61000, see immunity table. MIL-STD-461F/G CS101, CS114 (Army Ground), CS115, CS116
Line Dip	-	SEMI F47-0706 at 480Vac nominal (Criteria B)
Safety Certifications and Markings	-	IEC/UL/CSA/EN62368-1, 60950-1, CE and UKCA Marks



Immunity				
Test	Standard	Test Level	Criteria	Notes
ESD	EN61000-4-2	±8 kV air discharge, ±4 kV contact discharge	В	See test report
Radiated Susceptibility	EN61000-4-3	3 V/m from 80-1000 MHz (80% AM at 1kHz)	А	See test report
Electrical Fast Transient Burst	EN61000-4-4	Power line pulses of \pm 1 kV; I/O line pulses of \pm 0.5 kV	В	See test report
Surge	EN61000-4-5	3±2kV common mode, ±1kV differential mode	В	See test report
Conducted Susceptibility	EN61000-4-6	3 Vrms, 150 kHz - 80 MHz 1 kHz 80% AM	А	See test report
Magnetic fields	EN61000-4-8	Inductive loop at 50 Hz, to 30.0 amps (rms) per meter & 300.0 amps (rms) per meter	А	See test report
Voltage Dips and Input Interruptions	EN61000-4-11	Voltage Dips of 30% and >95%; Interruptions of >95%.	B/C	See test report

Specification		
Model		TPS4000
Output		
Line Regulation	%	<0.25
Load Regulation	%	<0.5
Total Regulation	%	<1.75
Warm Up Drift	%	<0.2
Temperature Stability	-	0.05% of rated Vout for 8hrs after 30min warmup
Temperature Coefficient	ppm/°C	200
Ripple & Noise (pk-pk) Maximum	mV	24V model: 240mV, 48V model: 480mV
Minimum Load	Α	None
Overcurrent Protection	%	Adjustable (70-105% of maximum rated current). Constant current style.
Overvoltage Protection	%	115% of output voltage set point (tracking). Cycle AC or use the remote on/off to reset
Overtemperature Protection	-	Internal thermostat. Automatic reset
Fan Fail	-	Blocked or fan failure detection. Cycle AC input or use PMBus to reset
Remote Sense	-	Compensates for a total of 1V cable drop
Remote On/Off	-	Enable or inhibit (selectable)
Voltage Programming	-	0 - 5V external voltage adjusts the output from Vout max to Vout min
Overcurrent Programming	-	0 - 5V external voltage adjusts the current limit from lout max to lout min
DC Good	-	Open Collector, ON when output is above 90% of output set point (tracking)
AC Fail	-	Open Collector, ON when AC input is above 340Vac, the load is >30% and unit is enabled
Dropped Phase Warning	-	Open collector, OFF during normal operation, active low during dropped phase state. Load >30%
Standby Voltage	-	11.2 - 12.5V, 0.3A
Indicators	-	Green LEDs indicates DC is OK and AC is ON. Blinking red/green during dropped phase (Load >30%)
Parallel Operation	-	Single wire current share, up to 8 units. (Internal ORing MOSFETs are fitted). Derate to 90% output power
Series Operation	-	Possible, see installation manual




Specification		
Model		TPS4000
Environmental		
Operating Temperature (-40°C start-up)	°C	-10 to +70, derate linearly from 100% to 80% load from 50 to 60, and from 80% to 55% at 70 (At -40°C a 10 min warm up at 80% load is required to meet specification)
Storage Temperature	°C	-40 to +85
Humidity (non condensing)	%RH	10 - 95%RH
Pollution Degree	-	PD 2
Cooling	-	Internal variable speed fan
Altitude	m	4,000
Withstand Voltage (For 1 minute)	Vac	Input to Ground 2,000Vac, Input to Output 3,000Vac, Output to Ground 500Vdc
Isolation Resistance	ΜΩ	>100 at 25°C, 70%RH & 500VDC
Vibration (Operating)	-	Designed to meet MIL-STD-810F, Method 514.5, Proc I, Category 1, 10
Shock	-	Designed to meet MIL-STD-810F, Method 516.5, Procedure I, IV & VI
Other		
Weight (Typ)	g	4,000
Size (WxHxD)	mm	107 x 84.4 x 335 (excluding output busbars)
Size (WxHxD)	Inches	4.21 x 3.33 x 13.2 (excluding output busbars)
Mating Connectors	-	Signal: Housing, JST PHDR-20VS, Crimp terminals, SPHD-001T-P0.5 PMBus shunt jumper: Samtec 2SN-BK-G
MTBF - Telcordia SR-332 issue 3	hrs	250,000 hours Method 1, Ground Benign, 25C, nominal input
Warranty	yrs	3 years
PMBus Functions		
Output Voltage Monitoring		
Output Current Monitoring		
Internal Temperature Monitoring		
Remote On/Off Programming		
Remote Voltage Programming		
Remote Overcurrent Programming		
Fault Clearing		
Reading Manufacturing Related Data		

Notes


See website for detailed specifications, test methods and installation manual

Derating Curve



TDK·Lambda

Outline Drawing



TDK·Lambda



TDK-Lambda France SAS

Tel: +33 1 60 12 71 65 tlf.fr.powersolutions@tdk.com www.emea.lambda.tdk.com/fr



Italy Sales Office

Tel: +39 02 61 29 38 63 tlf.it.powersolutions@tdk.com www.emea.lambda.tdk.com/it



Netherlands

tlf.nl.powersolutions@tdk.com www.emea.lambda.tdk.com/nl



TDK-Lambda Germany GmbH

Tel: +49 7841 666 0 tlg.powersolutions@tdk.com www.emea.lambda.tdk.com/de



Austria Sales Office

Tel: +43 2256 655 84 tlg.at.powersolutions@tdk.com www.emea.lambda.tdk.com/at



Switzerland Sales Office

Tel: +41 44 850 53 53 tlg.ch.powersolutions@tdk.com www.emea.lambda.tdk.com/ch



Nordic Sales Office

Tel: +45 8853 8086 tlg.dk.powersolutions@tdk.com www.emea.lambda.tdk.com/dk



TDK-Lambda UK Ltd.

Tel: +44 (0) 12 71 85 66 66 tlu.powersolutions@tdk.com www.emea.lambda.tdk.com/uk



TDK-Lambda Ltd.

Tel: +9 723 902 4333 tli.powersolutions@tdk.com www.emea.lambda.tdk.com/il-en



TDK-Lambda Americas

Tel: +1 800-LAMBDA-4 or 1-800-526-2324 tla.powersolutions@tdk.com www.us.lambda.tdk.com



TDK Electronics do Brasil Ltda

Tel: +55 11 3289-9599 sales.br@tdk-electronics.tdk.com www.tdk-electronics.tdk.com/en



TDK-Lambda Corporation

Tel: +81-3-6778-1113 www.jp.lambda.tdk.com



TDK-Lambda (China) Electronics Co. Ltd.

Tel: +86 21 6485-0777 tlc.powersolutions@tdk.com www.lambda.tdk.com.cn



TDK-Lambda Singapore Pte Ltd.

Tel: +65 6251 7211 tls.marketing@tdk.com www.sg.lambda.tdk.com



TDK India Private Limited, Power Supply Division

Tel: +91 80 4039-0660 mathew.philip@tdk.com www.sg.lambda.tdk.com

