

- High power density 3" x 5" open frame medical power supply
- 450 Watt with forced air cooling, up to 320 Watt convection cooled without derating up to 50°C
- Medical certification to IEC/EN/ES 60601-1 3rd edition for 2 x MOPP
- EMC compliance to IEC/EN 60601-1-2 4th edition
- Risk management process according to ISO 14971 incl. risk management file
- Acceptance criteria for electronic assemblies acc. to IPC-A-610 class 3
- Isolation (4000 VAC) and leakage current (<100 µA) rated for BF applications
- Standard features: 5 V standby output 12 V fan output, Remote On/Off, Power Good Signal, variable fan speed
- Operating up to 5000 m altitude
- 5-year product warranty



The TPP 450A Series of 450 Watt AC/DC power supplies feature a reinforced double I/O isolation system according to latest medical safety standards (60601-1 3rd edition, 2 x MOPP). The earth leakage current is below 100 µA what makes the units suitable for BF (body floating) applications. The excellent efficiency of up to 94% allows a high power density for the standard 3" x 5" packaging format.

Natural convection cooled power up to 320 W at +50°C and 150W at +85°C. Thus you can power your medical device in a quiet and hygienic way as you don't need to run a fan to cool down the power supply. High reliability is provided by use of industrial quality grade components and an excellent thermal management. It makes the products an ideal solution for medical devices and for demanding safety and space critical applications.

Models

Order Code	Output Power max.	Output Voltage nom. (adjustable)	Output Current max. (Forced air cooling)	Output Current max. (Natural convection)	Efficiency typ.
TPP 450-112A-M	450 W	12 VDC (11.0 - 13.0 VDC)	37'500 mA	20'800 mA	91 %
TPP 450-115A-M		15 VDC (13.8 - 16.2 VDC)	30'000 mA	16'600 mA	92 %
TPP 450-124A-M		24 VDC (22.1 - 25.9 VDC)	18'750 mA	13'300 mA	93 %
TPP 450-128A-M		28 VDC (25.8 - 30.2 VDC)	16'100 mA	11'400 mA	93 %
TPP 450-136A-M		36 VDC (33.1 - 38.9 VDC)	12'500 mA	8'900 mA	93 %
TPP 450-148A-M		48 VDC (44.2 - 51.8 VDC)	9'400 mA	6'650 mA	94 %
TPP 450-153A-M		53 VDC (48.8 - 57.2 VDC)	8'550 mA	6'050 mA	94 %

Options

TPP 450-AUX1	- Optional Cable for auxiliary connection (2 x 4 pin): www.tracopower.com/products/tpp450-aux1.pdf
TPP 450-AUX2	- Optional Cable for auxiliary connection (2 x 5 pin): www.tracopower.com/products/tpp450-aux2.pdf

Input Specifications

Input Voltage	- AC Range	Operational Range: 85 - 264 VAC (Full Range) Rated Range: 100 - 240 VAC (Full Range)
	- DC Range	Operational Range: 120 - 370 VDC (Designed for, no certification) Polarity: +DC: L / -DC: N
Input Frequency		Operational Range: 47 - 440 Hz Certified: 50/60 Hz
Input Current	- Full Load & Vin = 230 VAC	2'400 mA max.
	- Full Load & Vin = 115 VAC	5'800 mA max.
Power Consumption	- No load & Vin = 230 VAC	650 mW max.
	- No load & Vin = 115 VAC	900 mW max.
Input Inrush Current	- At 230 VAC	100 A max.
	- At 115 VAC	55 A max.
Power Factor	- At 230 VAC	0.95 min. (Active Power Factor Correction)
	- At 115 VAC	0.95 min. (Active Power Factor Correction)
Input Protection		T 6.3 A / 250 VAC (Internal Fuse in L & N)
Recommended Input Fuse		(The need of an external fuse has to be assessed in the final application.)

Output Specifications

Output Voltage Adjustment		±8% (By trim potentiometer) Output power must not exceed rated power!
Voltage Set Accuracy		±1% max.
Regulation	- Input Variation (Vmin - Vmax)	0.2% max.
	- Load Variation (0 - 100%)	0.5% max.
Ripple and Noise (20 MHz Bandwidth)	12 VDC model:	250 mVp-p typ. (w/ 1 µF X7R)
	15 VDC model:	300 mVp-p typ. (w/ 1 µF X7R)
	24 VDC model:	240 mVp-p typ. (w/ 1 µF X7R)
	28 VDC model:	280 mVp-p typ. (w/ 1 µF X7R)
	36 VDC model:	360 mVp-p typ. (w/ 1 µF X7R)
	48 VDC model:	480 mVp-p typ. (w/ 1 µF X7R)
Capacitive Load	53 VDC model:	530 mVp-p typ. (w/ 0.1 µF X7R)
	12 VDC model:	31'250 µF max.
	15 VDC model:	20'000 µF max.
	24 VDC model:	7'820 µF max.
	28 VDC model:	5'750 µF max.
	36 VDC model:	3'500 µF max.
48 VDC model:	1'960 µF max.	
	53 VDC model:	1'600 µF max.
Minimum Load		Not required
Temperature Coefficient		±0.02 %/K max.
Hold-up Time	- At 230 VAC	12 ms min.
	- At 115 VAC	12 ms min.
Start-up Time	- At 230 VAC	2'000 ms max.
	- At 115 VAC	2'000 ms max.
Short Circuit Protection		Continuous, Automatic recovery (Level 1, nom.) Latch (Level 2, instantaneous high current)
Output Current Limitation		115 - 155% of Iout max.
Overvoltage Protection		110 - 135% of Vout nom. (Latch off, Standby Power Source always present)
Transient Response	- Response Deviation	3% max. (50% to 75% Load Step)
	- Response Time	600 µs typ. (50% to 75% Load Step)

All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.

Safety Specifications

Standards	- IT / Multimedia Equipment	EN 62368-1 IEC 62368-1 UL 62368-1
	- Medical Equipment	EN 60601-1 IEC 60601-1 ANSI/AAMI ES 60601-1 2 x MOPP (Means Of Patient Protection)
	- Certification Documents	www.tracopower.com/overview/tpp450a
Protection Class		Class I (Prepared): Connection to PE
Pollution Degree		PD 2
Over Voltage Category		OVC II

EMC Specifications

EMI Emissions	- Conducted Emissions	EN 60601-1-2 edition 4 (Medical Devices) EN 55011 class B (internal filter) EN 55032 class B (internal filter) FCC Part 15 class B (internal filter) FCC Part 18 class B (internal filter)
	- Radiated Emissions	EN 55011 class A (internal filter) EN 55032 class A (internal filter) FCC Part 15 class A (internal filter) FCC Part 18 class A (internal filter)
	- Harmonic Current Emissions	EN 61000-3-2, class A
	- Voltage Fluctuations & Flicker	EN 61000-3-2, class D EN 61000-3-3 (For optimal EMI performance the power supply should be mounted to a grounded aluminium plate (480 x 248 x 12 mm) with electrical contact to the four PCB mounting holes. To comply with safety standards, this plate must be grounded.)
EMS Immunity	- Electrostatic Discharge	EN 55024 (IT Equipment) EN 55035 (Multimedia) EN 60601-1-2 edition 4 (Medical Devices) Air: EN 61000-4-2, ± 15 kV, perf. criteria A Contact: EN 61000-4-2, ± 8 kV, perf. criteria A
	- RF Electromagnetic Field	EN 61000-4-3, 3 V/m, perf. criteria A
	- EFT (Burst) / Surge	EN 61000-4-4, ± 2 kV, perf. criteria A L to L: EN 61000-4-5, ± 1 kV, perf. criteria A L to PE: EN 61000-4-5, ± 2 kV, perf. criteria A
	- Conducted RF Disturbances	EN 61000-4-6, 20 Vrms, perf. criteria A
	- PF Magnetic Field	Continuous: EN 61000-4-8, 30 A/m, perf. criteria A
	- Voltage Dips & Interruptions	230 VAC / 50 Hz: EN 61000-4-11 30%, 25 periods, perf. criteria A >95%, 0.5 periods, perf. criteria A >95%, 1 period, perf. criteria A >95%, 250 periods, perf. criteria B
		115 VAC / 60 Hz: EN 61000-4-11 30%, 25 periods, perf. criteria A >95%, 0.5 periods, perf. criteria A >95%, 1 period, perf. criteria A >95%, 250 periods, perf. criteria B

General Specifications

Relative Humidity		95% max. (non condensing)
Temperature Ranges	- Operating Temperature	-40°C to +85°C
	- Storage Temperature	-40°C to +85°C

All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.

Power Derating	- High Temperature - Low Input Voltage	Depending on model 1.33 %/V below 100 VAC See application note: www.tracopower.com/overview/tpp450a
Over Temperature Protection Switch Off	- Protection Mode - Measurement Point	110°C to 125°C (Latch off) See application note: www.tracopower.com/overview/tpp450a (Standby Power Source always present)
Cooling System	- Option 1 - Option 2	Forced air cooling (with external fan, 21 CFM) Natural convection (20 LFM)
Fan Power Source	- Characteristic - Output Voltage - Output Current	Variable fan speed (temperature regulated) 12 VDC 500 mA max.
Standby Power Source	- Output Voltage - Output Current	5 VDC 2000 mA max.
Remote Control	- Voltage Controlled Remote - Remote Pin Input Current	On: 3.0 to 12 VDC or open circuit Off: 0 to 1.2 VDC or short circuit Refers to '+Remote' and '-Remote' Pin -0.5 to 1.0 mA (Standby power source is always present)
Altitude During Operation		5'000 m max.
Switching Frequency		55 - 85 kHz (PFM)
Insulation System		Reinforced Insulation
Working Voltage (rated)		312 VAC
Isolation Test Voltage	- Input to Output, 60 s - Input to Case or PE, 60 s - Output to Case or PE, 60 s	4'000 VAC 2'500 VAC 2'500 VAC
Isolation Resistance	- Input to Output, 500 VDC	100 MΩ min.
Leakage Current (at 264 VAC)	- Touch Current	100 μA max.
Reliability	- Calculated MTBF	410'000 h (MIL-HDBK-217F, ground benign)
Environment	- Vibration - Mechanical Shock - Flammability	IEC 60068-2-6 IEC 60068-2-27 EN 45545-2 www.tracopower.com/info/en45545-declaration.pdf
Housing Type		Open Frame
Mounting Type		Chassis Mount
Connection Type		Pin Connector
Weight		462 g
Power OK Signal	- Trigger Threshold - Power OK - Power Off - Pin Specifications	Open collector output 12 VDC model: 9.8 - 11 VDC 15 VDC model: 12.3 - 13.8 VDC 24 VDC model: 19.7 - 22.1 VDC 28 VDC model: 23 - 25.8 VDC 36 VDC model: 29.5 - 33.1 VDC 48 VDC model: 39.4 - 44.2 VDC 53 VDC model: 43.5 - 48.8 VDC Low level High resistance (Refers to 'PG' and '-Vout' Pin) 50 VDC / 50 mA / 120 mW max.
Sense Function		8% max. of Vout nom. (If sense function is not used, sense pins should be connected to output pins.)

All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.

Environmental Compliance - REACH Declaration

www.tracopower.com/info/reach-declaration.pdf

- RoHS Declaration

REACH SVHC list compliant

REACH Annex XVII compliant

www.tracopower.com/info/rohs-declaration.pdf

- SCIP Reference Number

Exemptions: 7a, 7c-1

(RoHS exemptions refer to the component concentration only, not to the overall concentration in the product (O5A rule))


ebb80d8a-b994-4dd4-b470-9253df842d67

Supporting Documents

Overview Link (for additional Documents)

www.tracopower.com/overview/tpp450a

Outline Dimensions



Max. screw penetration: 1.3 (0.05)

All dimensions in mm (inch)

Tolerance: X.X ±0.5 (X.XX ±0.02)

X.XX ±0.25 (X.XXX ±0.01)

Screw locked torque: max. 5.2 kgfcm / 0.51 Nm

Input	
CON1	
Pin	Function
1	AC (L)
3	AC (N)

Output	
CON2	
Pin*2	Function
1-5	+Vout
6-10	-Vout

Auxiliary	
CON3	
Pin	Function
1	+Fan
2	+Sense
3	+Remote
4	PG
5	+Standby
6	-Fan*1
7	-Sense
8	-Remote*1
9	No pin
10	-Standby*1

*2 Terminal rated for 13 A max. (at higher current connection has to be split)

CON1:

Molex housing:
09-50-8031

Molex crimp terminals:
08500106 (2478),
08520112 (6838),
45570

CON2:

Molex housing:
39-01-2105

Molex crimp terminals:
5556,45750

CON3:

Molex housing:
90143-0010

Molex crimp terminals:
90119

*1 Internally connected with -Vout