



Click [here](#) for the 3D model.

Dimensions	
D	22mm +1mm
L	25mm +2mm
S	10mm +/-0.5mm
LL	5.8mm +/-1mm
F	1.5mm +/-0.1mm

Packaging Specifications	
Packaging	Bulk, Bag
Packaging Quantity	400

General Information	
Series	ELH
Dielectric	Aluminum Electrolytic
Description	Snap-In, Aluminum Electrolytic
RoHS	Yes
Lead	2 Pin
AEC-Q200	No

Specifications	
Capacitance	68 uF
Capacitance Tolerance	20%
Voltage DC	400 VDC, 450 VDC (Surge)
Temperature Range	-25/+85°C
Rated Temperature	85°C
Life	2000 Hrs
Dissipation Factor	15% 120Hz 20C
Resistance	2.9271 Ohms (120Hz 20C)
Ripple Current	0.6 Amps (120Hz 85C)
Leakage Current	0.5 mA (5min 20°C)