

Product Specification and Approval Sheet Version

1

Page 1/5

Surface Mountable PTC Resettable Fuse: FSMD2920 Series

1. Summary

- (a) RoHS Compliant & Halogen Free
- (b) Applications: All high-density boards
- (c) Product Features: 2920 Dimension, Surface mountable, Solid state, Faster time to trip than standard SMD devices
- (d) Operation Current: 0.30A~5.00A
- (e) Maximum Voltage: 6V~60V_{DC}
- (f) Temperature Range: -40°C to 85°C

2. Agency Recognition

- UL: File No. E211981
- C-UL: File No. E211981
- TÜV: File No. R50090556

3.	Electrical	Characteristics	(23℃)
----	------------	------------------------	--------------

Dert	Hold	Trip	Rated	Max.	Typical	Max. Tim	e to Trip	Resis	tance
Part	Current	Current	Voltage	Current	Power	Current	Time	R _{MIN}	R1 _{MAX}
Number	I _н , А	I _T , A	V_{MAX}, V_{DC}	I _{MAX} , A	Pd, W	Α	Sec	Ohm	Ohm
FSMD030-2920-R	0.30	0.60	60	100	1.5	1.5	3.0	1.000	4.800
FSMD050-2920-R	0.50	1.00	60	100	1.5	2.5	4.0	0.300	1.400
FSMD075-2920-R	0.75	1.50	33	100	1.5	8.0	0.3	0.180	1.000
FSMD075-60-2920-R	0.75	1.50	60	100	1.5	8.0	0.3	0.180	1.000
FSMD100-2920-R	1.10	2.20	33	100	1.5	8.0	0.5	0.090	0.410
FSMD110-60-2920R	1.10	2.20	60	100	1.5	8.0	0.5	0.090	0.410
FSMD125-2920-R	1.25	2.50	33	100	1.5	8.0	2.0	0.050	0.250
FSMD150-2920-R	1.50	3.00	33	100	1.5	8.0	2.0	0.050	0.230
FSMD185-2920-R	1.85	3.70	33	100	1.5	8.0	2.5	0.040	0.150
FSMD200-2920-R	2.00	4.00	16	100	1.5	8.0	4.5	0.035	0.120
FSMD200-24-2920-R	2.00	4.00	24	100	1.5	8.0	5.0	0.035	0.120
FSMD250-2920-R	2.50	5.00	16	100	1.5	8.0	16.0	0.025	0.085
FSMD260-2920-R	2.60	5.20	6	100	1.5	8.0	20.0	0.020	0.075
FSMD260-24-2920R	2.60	5.20	24	100	1.5	8.0	20.0	0.020	0.075
FSMD300-2920-R	3.00	5.20	6	100	1.5	8.0	25.0	0.010	0.048
FSMD300-15-2920R	3.00	5.20	15	100	1.5	8.0	20.0	0.010	0.048
FSMD300-24-2920R	3.00	5.20	24	100	1.5	8.0	20.0	0.010	0.048
FSMD330-2920R	3.30	5.50	24	100	1.5	8.0	20.0	0.010	0.048
FSMD400-16-2920R	4.00	8.00	16	100	1.5	20.0	4.0	0.010	0.040
FSMD500-16-2920R	5.00	10.00	16	100	1.5	20.0	5.0	0.005	0.025

I_H=Hold current-maximum current at which the device will not trip at 23° C still air.

IT=Trip current-minimum current at which the device will always trip at 23 $^\circ$ C still air.

V_{MAX}=Maximum voltage device can withstand without damage at it rated current (I_{MAX}).

IMAX= Maximum fault current device can withstand without damage at rated voltage (VMAX).


Pd=Typical power dissipated-type amount of power dissipated by the device when in the tripped state in 23°C still air environment.

R_{MIN}=Minimum device resistance at 23°C prior to tripping. R1_{MAX}=Maximum device resistance at 23°C measured 1 hour after tripping or reflow soldering of 260°C for 20 seconds. Termination pad characteristics

Termination pad materials: Pure Tin

RFE FUZETEC		PQ11-01ER		
Product Specification and Approval Sheet	Version	1	Page	2/5


4. FSMD Product Dimensions (Millimeters)



Part	Α		В		С		D		E	
Number	Min.	Max.								
FSMD030-2920-R	6.73	7.98	4.80	5.44	0.60	1.15	0.50	1.20	0.50	0.90
FSMD050-2920-R	6.73	7.98	4.80	5.44	0.60	1.15	0.50	1.20	0.50	0.90
FSMD075-2920-R	6.73	7.98	4.80	5.44	0.40	1.15	0.50	1.20	0.50	0.90
FSMD075-60-2920-R	6.73	7.98	4.80	5.44	0.60	1.15	0.50	1.20	0.50	0.90
FSMD100-2920-R	6.73	7.98	4.80	5.44	0.40	1.00	0.50	1.20	0.50	0.90
FSMD110-60-2920R	6.73	7.98	4.80	5.44	0.40	1.70	0.50	1.20	0.50	0.90
FSMD125-2920-R	6.73	7.98	4.80	5.44	0.40	0.90	0.50	1.20	0.50	0.90
FSMD150-2920-R	6.73	7.98	4.80	5.44	0.40	0.90	0.50	1.20	0.50	0.90
FSMD185-2920-R	6.73	7.98	4.80	5.44	0.30	0.90	0.50	1.20	0.50	0.90
FSMD200-2920-R	6.73	7.98	4.80	5.44	0.30	0.90	0.50	1.20	0.50	0.90
FSMD200-24-2920-R	6.73	7.98	4.80	5.44	0.20	0.80	0.50	1.20	0.50	0.90
FSMD250-2920-R	6.73	7.98	4.80	5.44	0.30	0.90	0.50	1.20	0.50	0.90
FSMD260-2920-R	6.73	7.98	4.80	5.44	0.30	0.90	0.50	1.20	0.50	0.90
FSMD260-24-2920R	6.73	7.98	4.80	5.44	0.65	1.15	0.50	1.20	0.50	0.90
FSMD300-2920-R	6.73	7.98	4.80	5.44	0.40	0.90	0.50	1.20	0.50	0.90
FSMD300-15-2920R	6.73	7.98	4.80	5.44	0.40	1.15	0.50	1.20	0.50	0.90
FSMD300-24-2920R	6.73	7.98	4.80	5.44	0.65	1.15	0.50	1.20	0.50	0.90
FSMD330-2920R	6.73	7.98	4.80	5.44	0.65	1.15	0.50	1.20	0.50	0.90
FSMD400-16-2920R	6.73	7.98	4.80	5.44	0.40	1.50	0.50	1.20	0.50	0.90
FSMD500-16-2920R	6.73	7.98	4.80	5.44	0.40	1.50	0.50	1.20	0.50	0.90


RFE FUZETEC	NO.	PQ11-01ER			
Product Specification and Approval Sheet	Version	1	Page	3/5	

5. Thermal Derating Curve



6. Typical Time-To-Trip at 23° C





RFE	FUZETEC	NO.
-----	---------	-----

1

Product Specification and Approval Sheet Version

7. Material Specification


Terminal pad material: Pure Tin

Soldering characteristics: Meets EIA specification RS 186-9E, ANSI/J-std-002 Category 3

8. Part Numbering and Marking System

Part Numbering System

Part Marking System



Warning: - Each product should be carefully evaluated and tested for their suitability of application.

- Operation beyond the specified maximum rating or improper use may result in damage and possible electrical arcing and/or flame.
- PPTC device are intended for occasional overcurrent protection. Application for repeated overcurrent condition and/or prolonged trip are not anticipated.
- Avoid contact of PPTC device with chemical solvent, including some inert material such as silicone based oil, lubricant and etc. Prolonged contact will damage the device performance.
- Additional protection mechanism are strongly recommended to be used in conjunction with the PPTC device for protection against abnormal or failure conditions.
- Avoid use of PPTC device in a constrained space such as potting material, housing and containers where have limited space to accommodate device thermal expansion and/or contraction.


EI(F) FUZETEC NO. **PQ11-01ER** 1 5/5

Product Specification and Approval Sheet Version

Page

9. Pad Layouts Solder Reflow and Rework Recommendations

The dimension in the table below provide the recommended pad layout for each FSMD2920 device



	1	1	
Device	A Nominal	B Nominal	C Nominal
All 2920 Series	5.10	2.30	5.60

Pb-Free Assembly		
3 ℃/second max.		
150 ℃		
200 ℃		
60-180 seconds		
217 ℃		
60-150 seconds		
260 ℃		
20-40 seconds		
6 ℃/second max.		
8 minutes max.		


Note 1: All temperatures refer to of the package, measured on the package body surface.

Solder reflow

- X Due to "Lead Free" nature, Temperature and Dwelling time for the soldering zone is higher than those for Regular. This may cause damage to other components.
- 1. Recommended max paste thickness is 0.25mm.(Nominal)
- 2. Devices can be cleaned using standard methods and aqueous solvent.
- 3. Rework use standard industry practices.
- 4. Storage Environment: < 30°C / 60%RH

Caution:

- 1. If reflow temperatures exceed the recommended profile, devices may not meet the performance requirements.
- 2. Devices are not designed to be wave soldered to the bottom side of the board.



Designed and manufactured by Fuzetec Technology Co., Ltd., offered by RFE International, Inc. NOTE: Specification subject to change without notice.

Reflow Profile