


Recommend PCB Layout

Specifications :
 Voltage ratings: 250V AC / DC
 Current rating: 7A AC / DC
 Withstanding voltage: 1500V AC/minute
 Temperature range: $-25^{\circ}\text{C}\sim+85^{\circ}\text{C}$
 Insulation resistance: $\geq 1000\text{M}\Omega$
 Contact resistance: $\leq 10\text{m}\Omega$
 After environmental testing: $\leq 20\text{m}\Omega$



Poles	Dimensions(mm)		Dimensions(mm)	
	A	B	A	B
02	3.96	7.92	31.68	35.64
03	7.92	11.88	35.64	39.60
04	11.88	15.84	39.60	43.56
05	15.84	19.80	43.56	47.52
06	19.80	23.76	47.52	51.48
07	23.76	27.72	51.48	55.44
08	27.72	31.68	55.44	59.40

APPROVALS		DATE	DRAWING NO.	
DRAWN	G.M.Chen	2015/5/29	EPCALON 德之隆® ELECTRONICS CO.,LTD	
CHECKED			TITLE: 3.96mm Crimp Style Connectors	
APPROVALS			PART NO.	X396WV-XXX
TOLERANCES ARE		30 ^{±0.15}	±0.30	ANGLE
		10 ^{±0.20}	±0.20	UNIT: mm
		5 ^{±0.15}	±0.15	SCALE: 1:1
		~ 5	±0.10	SHEET 1 OF 1
ECN NO.	REV.	DATE.	DESCRIPTION.	PROJ.
	A		NEW	